


UNLESS OTHERWISE NOTED
 DIMENSIONS ARE IN INCHES TOLERANCES ARE:
 ONE PLACE DECIMALS: ± .1 [3] THREE PLACE DECIMALS: ± .005 [.13]
 TWO PLACE DECIMALS: ± .01 [.3] FOUR PLACE DECIMALS: ± .0020 [.051]

TITLE: ASSEMBLY BOARD TO BOARD SPACING
 DWG NO: BXX-1XX-X-X-X
 SHEET 1 OF 1

DO NOT SCALE FROM THIS PRINT

ASSEMBLY INSTRUCTIONS



BXX-1XX-X-X-X

BODY SPECIFICATION (SEE TABLE 1)
BODY STYLE
 BBS: SINGLE
 BBD: DOUBLE
 BBL: SINGLE, LOW PROFILE
 BDL: DOUBLE, LOW PROFILE
 BHS: SINGLE, HI-TEMP
 FOR ALL PLATING STYLES
 FOR STANDARD (USE BODY SPECIFIED IN TABLE 1) (SEE TABLE 4)
TERMINAL SPECIFICATION (SEE TABLE 2)
PLATING SPECIFICATION (SEE TABLE 2)
 -G: SPECIFY -G IN TERMINAL SUFFIX -X
 -T: SPECIFY -T IN TERMINAL SUFFIX -X
 * = INVALID WITH D & G TERMINAL SPEC

BODY LENGTH SPECIFICATION
 *X: (No. OF POSITIONS X 100 ± .015)
 *A: BBS: XX-MAX 32 POSITION
 *A: BBL: XX-MAX 32 POSITION
 *A: BHS: XX-MAX 36 POSITION (MUST BE CUT ON MULTI-CUTTER)
 *BBD: XX-MAX 36 POSITION
 *BDL: XX-MAX 36 POSITION

- NOTES:
 1.) MIN. PUSHOUT FORCE: 5 lbs FOR ALL EXCEPT BBL, FOR BBL: 2 lbs. MIN.
 2.) MAX ALLOWABLE BOW:
 FOR STRIPS MOLDED IN VALOX = .009 IN/IN
 FOR STRIPS MOLDED IN ULTEM = .003 IN/IN
 (FOR BHS ONLY: .004 IN/IN TOP TO BOTTOM, .008 IN/IN SIDE TO SIDE.)
 (FOR BBL ONLY: .055 MAX.)
 3.) ⊕ REPRESENTS A CRITICAL DIMENSION.
 4.) ON BBD STYLE FILL WITH COUNTERBORE TOWARD TAILS, ALL OTHER STYLES FILL COUNTERBORE AWAY FROM TAILS.

ASSEMBLY OPERATION	IN-PROCESS INSPECTION
FILL	C3, C7
CUT	C2


CPCs INTENTIONALLY DELETED: C1, C4, C5, C6

TERMINAL SPEC.	"B"
-G	.320 [8.13]
-G-N	.290 [7.37]
-N	.410 [10.41]

BODY STYLE	BODY SPECIFICATION	
	STANDARD	-N OPTION
BBS-	TBS-32	SSB-XX
BBD-	DSB-36	DSB-XX
BBL-	SSL-XX	N/A
BDL-	HSDL-XX	N/A
BHS-G(PLATING)	HTS-36-G	SSB-XX-U

BODY	LEAD STYLE	PACKAGING TUBE	PLUG
BHS	A	PT-1-24-01-24	TP-24
	B	PT-1-24-02-03	TP-24
	D,H	PT-1-24-02-04	TP-07
BBS	C,G	PT-1-24-10-03	TP-03
	A	PT-1-24-01-24	TP-24
	B	PT-1-24-02-03	TP-24
BBD	D,H	PT-1-24-02-04	TP-07
	C,G	PT-1-24-10-03	TP-03
	A	PT-1-24-01-22	TP-03
BBL	B	PT-1-24-06-03	TP-07
	D,H	PT-1-24-08-03	TP-09
	C,G	PT-1-24-01-74	TP-07
BBL	ALL	PT-1-24-01-23	TP-12
BDL	ALL	PT-1-24-01-14	TP-03

PACKAGING



LEAD STYLE	BODY SPEC.		BODY SPEC.	
	BBS,BBD,BHS	"X"	"C"	"C"
A	T-1R14-1-X	.210 [5.35]	.460 [11.68]	N/A
B	T-1R14-2-X	.335 [8.51]	.585 [14.86]	N/A
C	T-1R14-3-X	.585 [14.86]	.835 [21.21]	N/A
D	T-1R14-4-X	.835 [21.21]	1.085 [27.56]	N/A
E	N/A		T-1R6-X	.070 2 .300 [7.62]
F	N/A		T-2R6-X	.085 3 .332 [8.43]
* G	T-1R14-5-X	.585 [14.86]	.835 [21.21]	N/A

* = SEE NOTE 4

PROPRIETARY NOTE
 THIS DOCUMENT CONTAINS INFORMATION CONFIDENTIAL AND PROPRIETARY TO SAMTEC INC. AND SHALL NOT BE REPRODUCED OR USED FOR ANY PURPOSE OTHER THAN THAT FOR WHICH IT WAS OBTAINED WITHOUT THE EXPRESSED WRITTEN CONSENT OF SAMTEC INC.

MATERIAL:
 INSULATOR: GLASS FILLED POLYESTER
 COLOR: BLACK

TERMINAL:
 PHOSPHOR BRONZE OR BRASS

520 PARK EAST BLVD. NEW ALBANY, INDIANA 47150
 PHONE (812) 944-6733 P.O. BOX 1147
 CODE 55322

MADE BY: TY 2-18-85
 CHECKED BY: L WILLIAMS 2-23-85

DIAGRAM APPROVAL

BXX-1XX-X-X-X
 SHEET 1 OF 1