

1734328-1 Product Details

Live Product Chat US Only
8:30am - 5pm ET, Mon - Fri



1734328-1

TE Part Number: 1734328-1

✓ Active

➤ Add to Part List

Universal Serial Bus (USB) Connectors

Always EU RoHS/ELV Compliant (Statement of Compliance)

Product Highlights:

- Connector
- Size = Mini
- AB Series
- Receptacle
- Without Locking Feature

[View all Features](#) | [Find Similar Products](#)

Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)
- ▶ [Request Samples](#)

NEW!

Documentation & Additional Information

Product Drawings:

- [MINI USB CONN., TYPE AB, RCPT, 5 POS., RIGHT ANGLE, SMT](#) (PDF, English)

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- [MINI USB SERIES.](#) (PDF, English)

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files: ([CAD Format & Compression Information](#))

- [2D Drawing](#) (DXF, Version A)
- [3D Model](#) (IGES, Version A)
- [3D Model](#) (STEP, Version A)

[List all Documents](#)

Additional Information:

- [Product Line Information](#)

Related Products:

- [Tooling](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- Product Type = Connector
- Size = Mini
- Gender = Receptacle
- Number of Ports = 1
- Orientation = Right Angle
- PCB Thickness (mm [in]) = 1.57 [0.062]
- Number of Positions = 5

Mechanical Attachment:

- Mount Location = Top

Termination Related Features:

- Termination Method = Solder to PC Board

Body Related Features:

- [Series](#) = AB
- Locking Feature = Without
- [Panel Ground](#) = Without
- PCB Retention Method = SMT Hold Down
- Shell Plating = Nickel over Copper
- Pick and Place Cover = Without
- Locating Posts = With

Contact Related Features:

- Contact Termination Type = Surface Mount
- [Contact Mating Area Plating Material](#) = Gold
- Contact Mating Area Plating Thickness = 30 Microinches

Housing Related Features:

- [Housing Color](#) = Black

Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Reflow solder capable to 245°C, Reflow solder capable to 260°C
- RoHS/ELV Compliance History = Always was RoHS compliant

Conditions for Usage:

- Terminate To = Printed Circuit Board

Packaging Related Features:

- [Packaging Method](#) = Tray

Other:

- Brand = AMP