



[CONNECTORS](#)

[RF CONNECTORS](#)



✓ Active

TE CONNECTIVITY (TE)

## MCX Str Plg Hex 50Ohm Gold Pltd RG174A/U

Subminiature Coax | OS , U

1-1337580-0

TE Internal Number: 1-1337580-0

[EU RoHS Compliant with Exemptions](#)

[EU ELV Compliant with Exemptions](#)

**Connector Interface** MCX

**Connector Style** Plug

**Impedance (Ω)** 50

**Cable Type** RG 174A, RG 188A, RG 316, URM 95

**Sealable** No

[↓ PRODUCT DRAWING](#)  
English

[↓ 3D PDF](#)

### DOCUMENTATION

Product Drawings

**MCX STRAIGHT PLUG CRIMP 50 OHMS RG174, 188, 316, URM95, KX3B, 22A**

PDF (TIFF AVAILABLE)

English

CAD Files

**3D PDF**

PDF

3D

**Customer View Model**

2D\_DXF.ZIP

English

## Customer View Model

3D\_IGS.ZIP

English

## Customer View Model

3D\_STP.ZIP

English

---

Catalog Pages/Data Sheets

### 1-1773725-8\_RF\_COAX\_QRG

PDF

English

---

Product Specifications

Product Specification

### MCX SERIES COAXIAL CONNECTORS - TYCO GREENPAR

PDF

English

Qualification Test Report

### MCX SERIES COAXIAL CONNECTORS - MAXIMUM CURRENT HANDLING

PDF

English

### MCX SERIES COAXIAL CONNECTORS FOR FLEXIBLE CABLES - CABLE RETENTION

TIF

English

### MCX SERIES COAXIAL CONNECTORS FOR FLEXIBLE CABLES - CABLE RETENTION

PDF

English

---

## FEATURES



Please review product documents or [contact us](#) for the latest agency approval information.

Please Note: Use the Product Drawing for all design activity.

---

Product Type Features

**Connector Interface** MCX

**Connector Style** Plug

**Sealable** No

**Connector & Contact Terminates To** Wire & Cable

---

Electrical Characteristics

**Impedance ( $\Omega$ )** 50

---

Body Features

**Cable Connector Orientation** Straight

**Body Material** Brass

**Body Plating Material** Gold

**Body Shape** Circular

---

#### Contact Features

**Crimp Type** Hex

**Ferrule Plating Material** Gold

**Center Contact Plating Material** Gold

**Center Contact Material** Brass

**Ferrule Material** Brass

---

#### Termination Features

**Termination Method to Wire & Cable** Crimp

---

#### Usage Conditions

**Cable Type** RG 174A, RG 188A, RG 316, URM 95

---

#### Packaging Features

**Packaging Method** Box

**Packaging Quantity** 50

---

#### Other

**Dielectric Material** PTFE

**Grade** Professional

---

## PRODUCT COMPLIANCE



Statement of Compliance

**Statement of Compliance**

PDF

---