

# DELPHI Connection Systems Catalog

[Customer Service](#)

[Comparison List \(0\)](#)

[Samples Request](#)

Find by Feature

Browse by Category

Browse by Application

Share

Search

Enter part number or keyword

Search Results (1)

Search

Options

1 Result(s): [ All ] - 12129484

Compare

**12129484 - Metri-Pack 150 Series**

Female Unsealed Tin Plating Terminal, Cable Range 0.80 - 1.00 mm2

Compare

## Metri-Pack 150 Series Female Unsealed Tin Plating Terminal, Cable Range 0.80 - 1.00 mm2



Part # 12129484

[Question about this product?](#)

Attributes

Documents (2)

Part # :	12129484
Part # :	12129484
Part # :	12129484
Part # :	✓ 12129484
Part # :	12129484
Part # :	12129484
Part # :	12129484
Part # :	12129484
Part # :	12129484
Part # :	12129484
Part # :	12129484
Part # :	12129484
Part # :	12129484
Part # :	12129484
Part # :	12129484
Part # :	12129484
Part # :	12129484
Part # :	12129484
Description :	Metri-Pack 150 Series Female Unsealed Tin Plating Terminal, Cable Range 0.80 - 1.00 mm2
Description :	Metri-Pack 150 Series Female Unsealed Tin Plating Terminal, Cable Range 0.80 - 1.00 mm2
Description :	Metri-Pack 150 Series Female Unsealed Tin Plating Terminal, Cable Range 0.80 - 1.00 mm2
Description :	✓ Metri-Pack 150 Series Female Unsealed Tin Plating Terminal, Cable Range 0.80 - 1.00 mm2
Description :	Metri-Pack 150 Series Female Unsealed Tin Plating Terminal, Cable Range 0.80 - 1.00 mm2
Description :	Metri-Pack 150 Series Female Unsealed Tin Plating Terminal, Cable Range 0.80 - 1.00 mm2
Description :	Metri-Pack 150 Series Female Unsealed Tin Plating Terminal, Cable Range 0.80 - 1.00 mm2
Description :	Metri-Pack 150 Series Female Unsealed Tin Plating Terminal, Cable Range 0.80 - 1.00 mm2










Weight [g] :	0
Weight [g] :	0
Weight [g] :	0
Weight [g] :	0
Weight [g] :	0
Weight [g] :	0
Weight [g] :	0
Weight [g] :	0
Plating :	Tin
Plating :	Tin
Plating :	Tin
Plating :	✔ Tin
Plating :	Tin
Plating :	Tin
Plating :	Tin
Plating :	Tin
Plating :	Tin
Plating :	Tin
Plating :	Tin
Plating :	Tin
Plating :	Tin
Plating :	Tin
Plating :	Tin
Plating :	Tin
Plating :	Tin
Plating :	Tin
Plating :	Tin
Minimum Cable Diameter [mm] :	2.03
Minimum Cable Diameter [mm] :	2.03
Minimum Cable Diameter [mm] :	2.03
Minimum Cable Diameter [mm] :	✔ 2.03
Minimum Cable Diameter [mm] :	2.03
Minimum Cable Diameter [mm] :	2.03
Minimum Cable Diameter [mm] :	2.03
Minimum Cable Diameter [mm] :	2.03
Minimum Cable Diameter [mm] :	2.03
Minimum Cable Diameter [mm] :	2.03
Minimum Cable Diameter [mm] :	2.03
Minimum Cable Diameter [mm] :	2.03
Minimum Cable Diameter [mm] :	2.03
Minimum Cable Diameter [mm] :	2.03
Minimum Cable Diameter [mm] :	2.03
Minimum Cable Diameter [mm] :	2.03
Minimum Cable Diameter [mm] :	2.03
Maximum Cable Diameter [mm] :	2.40
Maximum Cable Diameter [mm] :	2.40
Maximum Cable Diameter [mm] :	2.40
Maximum Cable Diameter [mm] :	✔ 2.40
Maximum Cable Diameter [mm] :	2.40
Maximum Cable Diameter [mm] :	2.40





<b>Voltage Drop :</b>	Less than 6.0
<b>Voltage Drop :</b>	Less than 6.0
<b>Voltage Drop :</b>	Less than 6.0
<b>Voltage Drop :</b>	Less than 6.0
<b>Voltage Drop :</b>	Less than 6.0
<b>Voltage Drop :</b>	Less than 6.0
<b>RoHs compliant :</b>	 Yes
<b>ELV compliant :</b>	 Yes

Certain products listed on this website may be subject to restricted usage or distribution or may not be available. For additional information, please contact your local sales office.



[Suppliers](#) | [Terms of Use](#) | [Privacy](#) | [Mexico Privacy Statement](#) | [Cookie Policy](#) | [Sitemap](#) | [European Safe Harbor](#) | [California Supply Chains Act](#)

© Delphi Automotive LLP. All rights reserved.