


144431 -1 Product Details

Live Product Chat US Only
8:30am - 5pm ET, Mon - Fri



144431 -1

✓ [Active](#)

Timer Contacts

[Always EU RoHS/ELV Compliant](#) ([Statement of Compliance](#))

Product Highlights:

- ? Contact
- ? Contact Type = Junior -Power -Timer
- ? Receptacle
- ? Wire Range = 0.30 -1.00² [22-17] mm [AWG]
- ? Insulation Diameter = 2.15 mm

[View all Features](#) | [Find Similar Products](#)

Quick Links

- [Check Pricing & Availability](#)
- [Search for Tooling](#)
- [Product Feature Selector](#)
- [Contact Us About This Product](#)

Documentation & Additional Information

Product Drawings:

- ? [CONTACT JUNIOR POWER TIMER](#) (PDF, English)

Catalog Pages/Data Sheets:

- ? None Available

Product Specifications:

- ? [Terminal, Timer Connector](#) (PDF, English)
- ? [Contacts Junior Power Timer](#) (PDF, English)

Application Specifications:

- ? [SERTISSAGE DU RECEPTACLE JUNIOR POWER TIMER SUR MACH...](#) (PDF, French)

Instruction Sheets:

- ? None Available

CAD Files:

- ? None Available

Additional Information:

- ? [Product Line Information](#)

Additional Product Images:

- ? [Line Drawing](#)

Related Products:

- ? [Tooling](#)

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- ? [Product Type](#) = Contact
- ? [Gender](#) = Receptacle
- ? [Insulation Diameter \(mm \[in\]\)](#) = 2.15 [0.084]
- ? Tab Fit (mm [in]) = 2.79 x 0.81 [.110 x .032]

Body Related Features:

- ? [Wire Range \(mm \[AWG\]\)](#) = 0.30 -1.00² [22-17]
- ? Single Wire Sealing System = No

Contact Related Features:

- ? [Contact Type](#) = Junior -Power -Timer
- ? [Contact Material](#) = CuSn4
- ? [Contact Mating Area Plating Material](#) = Pre -Tin

Industry Standards:

- ? [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- ? [Lead Free Solder Processes](#) = Not relevant for lead free process
- ? RoHS/ELV Compliance History = Always was RoHS compliant

Conditions for Usage:

- ? [Terminate To](#) = Wire

Packaging Related Features:

- ? [Packaging Method](#) = Strip

Other:

- ? GET 0.64 Connector System = No
- ? Brand = AMP