RoHS



Vishay General Semiconductor

High Current Density Surface Mount Schottky Rectifier



DO-214AC (SMA)

PRIMARY CHARACTERISTICS					
I _{F(AV)}	2.0 A				
V_{RRM}	30 V, 40 V				
I _{FSM}	60 A				
E _{AS}	11.25 mJ				
V _F	0.38 V, 0.42 V				
T _J max.	150 °C				
Package	DO-214AC (SMA)				
Diode variations	Single die				

FEATURES

- Low profile package
- · Ideal for automated placement
- Guardring for overvoltage protection
- Low power losses, high efficiency
- zow power loodes, riight em
- Low forward voltage drop
- · High surge capability
- Meets MSL level 1, per J-STD-020, LF maximum peak of 260 °C
- AEC-Q101 qualified
- Material categorization: For definitions of compliance please see <u>www.vishay.com/doc?99912</u>

TYPICAL APPLICATIONS

For use in low voltage high frequency inverters, freewheeling, DC/DC converters, and polarity protection applications.

MECHANICAL DATA

Case: DO-214AC (SMA)

Molding compound meets UL 94 V-0 flammability rating Base P/N-E3 - RoHS-compliant, commercial grade Base P/NHE3_X - RoHS-compliant and AEC-Q101 qualified ("_X" denotes revision code e.g. A, B,)

Terminals: Matte tin plated leads, solderable per J-STD-002 and JESD 22-B102

E3 suffix meets JESD 201 class 2 whisker test, HE3 suffix meets JESD 201 class 2 whisker test

Polarity: Color band denotes cathode end

PARAMETER	SYMBOL	SSA23L	SSA24	UNIT
Device marking code		23L	S24	V
Maximum repetitive peak reverse voltage	V_{RRM}	30	40	V
Maximum RMS voltage	V_{RMS}	21	28	V
Maximum DC blocking voltage	V_{DC}	30	40	V
Maximum average forward rectified currentat T _L (fig. 1)	I _{F(AV)}	2.0		Α
Peak forward surge current 8.3 ms single halfsine-wave superimposed on rated load	I _{FSM}	60		А
Non-repetitive avalanche energy at T _A = 25 °C, I _{AS} = 1.5 A, L = 10 mH	E _{AS}	11.25		mJ
Voltage rate of change (rated V _R)	dV/dt	10 000		V/µs
Operating junction temperature range	TJ	-65 to +150		°C
Storage temperature range	T _{STG}	-65 to	°C	



Vishay General Semiconductor

ELECTRICAL CHARACTERISTICS (T _A = 25 °C unless otherwise noted)								
PARAMETER	TEST CONDITIONS		SYMBOL	SSA23L		SSA24		UNIT
PANAIVIETEN				TYP.	MAX.	TYP.	MAX.	UNII
Maximum instantaneous forward voltage (1)	2.0 A	T _J = 25 °C	V _F	0.43	0.45	0.45	0.49	V
		T _J = 125 °C		0.32	0.38	0.36	0.42	
Maximum reverse current at rated V _R ⁽²⁾		T _J = 25 °C		-	0.5	-	0.2	mA
iviaximum reverse current at rated $v_R^{(e)}$		T _J = 125 °C	I _R	15	25	12	20	ША

Notes

(1) Pulse test: 300 µs pulse width, 1 % duty cycle

(2) Pulse test: Pulse width ≤ 40 ms

THERMAL CHARACTERISTICS (T _A = 25 °C unless otherwise noted)					
PARAMETER	SYMBOL	SSA23L	SSA24	UNIT	
Typical thermal resistance (1)	$R_{\theta JA}$	110		°C/W	
Typical thermal resistance (7)	$R_{\theta JL}$	2	8	C/VV	

Note


(1) Aluminum substrate mounted


ORDERING INFORMATION (Example)						
PREFERRED P/N	UNIT WEIGHT (g)	PREFERRED PACKAGE CODE	BASE QUANTITY	DELIVERY MODE		
SSA23L-E3/61T	0.064	61T	1800	7" diameter plastic tape and reel		
SSA23L-E3/5AT	0.064	5AT	7500	13" diameter plastic tape and reel		
SSA23LHE3_A/H (1)	0.064	Н	1800	7" diameter plastic tape and reel		
SSA23LHE3_A/I (1)	0.064	I	7500	13" diameter plastic tape and reel		

Note

(1) AEC-Q101 qualified

RATINGS AND CHARACTERISTICS CURVES ($T_A = 25$ °C unless otherwise noted)








Fig. 2 - Maximum Non-Repetitive Peak Forward Surge Current



Vishay General Semiconductor




Fig. 3 - Typical Instantaneous Forward Characteristics




Fig. 5 - Typical Junction Capacitance





Fig. 4 - Typical Reverse Characteristics

PACKAGE OUTLINE DIMENSIONS in inches (millimeters) DO-214AC (SMA)





Legal Disclaimer Notice

Vishay

Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Vishay: SSA23L-M3/5AT