


## 1825057-1 Product Details

**Have a Question?**

Chat with a Product Information Specialist



**1825057-1**  
(ADE0204)

TE Internal Number: 1825057-1

**Active**

### DIP, Rotary DIP, SIP Switches and DIP Shunts - Standard

[Always EU RoHS/ELV Compliant \(Statement of Compliance\)](#)

**Product Highlights:**

- Switch - Mechanical
- Switch Type = DIP
- PCB Mount Style = Through Hole
- Single Pole - Single Throw Configuration (Pole-Throw)
- Actuator Style = Extended, Slide

[View all Features](#)

**Quick Links**

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

[Add to My Part List](#) [Request Sample](#) [Find Similar Products](#) [Buy Product](#)

### Documentation & Additional Information

**Product Drawings:**

- [DIP SWITCH, ADE THRU HOLE](#) (PDF, English)

**Catalog Pages/Data Sheets:**

- [SWITCHES CORE PROGRAM CATALOG](#) (PDF, English)

**Product Specifications:**

- None Available

**Application Specifications:**

- None Available

**Instruction Sheets:**

- None Available

**CAD Files:**

- None Available

**Additional Information:**

- [Product Line Information](#)

**Related Products:**

- [Tooling](#)

[List all Documents](#)

### Product Features (Please use the Product Drawing for all design activity)

**Product Type Features:**

- Product Type = Switch - Mechanical
- PCB Mount Style = Through Hole
- [Configuration \(Pole-Throw\)](#) = Single Pole - Single Throw
- [Actuator Style](#) = Extended, Slide
- Sealed = No
- [Number of Switches](#) = 2

**Body Related Features:**

- Switch Type = DIP
- Series = AD
- Centerline (mm [in]) = 2.54 [0.100]

**Contact Related Features:**

- Auto-Insertable = Yes
- Contact Base Material = Copper Alloy
- Contact Plating, Mating Area, Material = Gold Flash

**Housing Related Features:**

- Housing Color = Black
- Housing Material = PPS
- UL Flammability Rating = UL 94V-0

**Industry Standards:**

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Wave solder capable to 240°C, Wave solder capable to 260°C, Wave solder capable to 265°C
- RoHS/ELV Compliance History = Always was RoHS compliant

**Other:**

- Brand = Tyco Electronics

BOOKMARK

**Corporate Information**

- [Who We Are](#)
- [Investors](#)
- [News Room](#)
- [Supplier Portal](#)
- [Careers](#)

**Quick Links**

- [Check Distributor Inventory](#)
- [Cross Reference](#)
- [Find Documents & Drawings](#)
- [Product Compliance Support Center](#)
- [Site Map](#)

**Customer Support**

- [Email or Chat with Us](#)
- [Find a Phone Number](#)
- [Search Knowledge Base](#)
- [Manage Your Account](#)

**Sign up for our eNewsletter**

Enter your email address

**Follow Us On:**



**Visit Us On:**

