

16300/16700

Rectangular or square caps • distinct tactile feel • many legend options




DISTINCTIVE FEATURES

Rectangular cap : 6 x 12.3 mm; h=16.9 mm

Square cap : 14.9 x 14.9 mm; h=14.6 mm




Many standard legends options

Many functions incl quiet with Unimec™ switches






SWITCH SPECIFICATIONS : see Unimec™ series.

UNIMEC™+16300



UNIMEC™+16700



16300/16700

Rectangular or square caps • distinct tactile feel • many legend options



BUILD YOUR PART NUMBER

NON-ILLUMINATED

15

SERIES

FUNCTION

CAP

COLOR

400	momentary quiet silver
401	momentary silver
402	momentary gold
420	momentary quiet gold
451	latching silver
452	latching gold

16300
16700

00	blue
02	green
03	grey
04	yellow
06	white
08	red
09	black



MOUNTING

- Panel cut-out :
16300 : min. 12.7 x 6.4 mm
16700 : min. 15.3 x 15.3 mm
- Switch spacing AxB :
16300 : min. 13 x 13 mm
16700 : min. 15.5 x 15.5 mm



MATERIALS

- Cap : ABS UL94HB

16310-15

Square solutions • distinct tactile feel • height 16 mm • illumination option



DISTINCTIVE FEATURES

Square solution 15.1 x 15.1 mm

h=16.0 mm

1-4 LED illumination option




Many standard legend options for 16300 cap

Many functions incl quiet with Unimec™ switches






SWITCH SPECIFICATIONS : see Unimec™ series.




UNIMEC™+16300 + 16310






UNIMEC™+16300 + 16311



UNIMEC™+16300 + 16312



UNIMEC™+16300 + 16315



The company reserves the right to change specifications without notice. All tolerance if not otherwise specified ±0.2mm.

16310-15

Square solutions • distinct tactile feel • height 16 mm • illumination option

BUILD YOUR PART NUMBER

ILLUMINATED

SERIES	FUNCTION	CAP	COLOR	BEZEL	COLOR	LED 1 - 4	COLOR
15		16300					
400	momentary quiet silver		00 blue	16311		16921	
401	momentary silver		02 green	16312		16920	
402	momentary gold		03 grey	16314			
420	momentary quiet gold		04 yellow	16315			
451	latching silver		06 white		03 grey		02 green
452	latching gold		08 red		08 red		04 yellow
			09 black		09 black		08 red


NON-ILLUMINATED

SERIES	FUNCTION	CAP	COLOR	BEZEL	COLOR
15		16300		16310	
400	momentary quiet silver		00 blue		00 blue
401	momentary silver		02 green		02 green
402	momentary gold		03 grey		03 grey
420	momentary quiet gold		04 yellow		04 yellow
451	latching silver		06 white		06 white
452	latching gold		08 red		08 red
			09 black		09 black

NOTICE : please note that not all combinations of above numbers are available. Contact APEM for further information.

MOUNTING

- Panel cut-out : min. 14.1 x 14.1 mm
- Switch spacing AxB : min. 15.24 x 15.24 mm



MATERIALS

- Cap & bezel : ABS UL94HB

16324-26

Square solutions • distinct tactile feel • height 20.5 mm • illumination option



DISTINCTIVE FEATURES


Square solution 15.1 x 15.1 mm

h=20.5 mm

1-2 lens illumination option




Many standard legend options for 16300 cap

Many functions incl quiet with Unimec™ switches






SWITCH SPECIFICATIONS : see Unimec™ series.




UNIMEC™+16300 + 16324



UNIMEC™+16300 + 16325



UNIMEC™+16300 + 16326



16324-26

Square solutions • distinct tactile feel • height 20.5 mm • illumination option

BUILD YOUR PART NUMBER

ILLUMINATED

SERIES	FUNCTION	CAP	COLOR	BEZEL	LENS 1 OR 2	LED 1 OR 2
15		16300			16927	16922
	400 momentary quiet silver		00 blue	16325 one lens		
	401 momentary silver		02 green	16326 two lenses		
	402 momentary gold		03 grey			
	420 momentary quiet gold		04 yellow			
	451 latching silver		06 white		03 grey	02 green
	452 latching gold		08 red		09 black	04 yellow
			09 black			08 red


NON-ILLUMINATED

SERIES	FUNCTION	CAP	COLOR	BEZEL	COLOR
15		16300		16324	
	400 momentary quiet silver		00 blue		03 grey
	401 momentary silver		02 green		09 black
	402 momentary gold		03 grey		
	420 momentary quiet gold		04 yellow		
	451 latching silver		06 white		
	452 latching gold		08 red		
			09 black		

NOTICE : please note that not all combinations of above numbers are available. Contact APEM for further information.

MOUNTING

- Panel cut-out : min. 14.1 x 14.1 mm
- Switch spacing AxB : min. 15.24 x 15.24 mm




MATERIALS

- Cap & bezel : ABS UL94HB
- Lens : polycarbonate UL94V2

Unimec™

8 contact functions •
2 pole • distinct tactile feel



DISTINCTIVE FEATURES

12.6 x 12.6 mm; h=15.7 mm

2 pole

Momentary, latching or quiet

8 contact functions

Up to 10,000,000 cycle lifetime



ENVIRONMENTAL SPECIFICATIONS

- Sealing : IP54 according to IEC 60529
- Working temperature : -40 °C/+160 °C
- Storage temperature : -65 °C/+160 °C
- Soldering : IEC 68-2-20



ELECTRICAL SPECIFICATIONS


- Recommended load :
 - Gold contacts : min. 0.5 μ A - max.250 mA - 120 V - 9 W AC - 6 W DC
 - Silver contacts : min. 0.5 mA - max.250 mA - 120 V - 9 W AC - 6 W DC
- Contact resistance : max. 100 m Ω (initially)
- Insulation resistance : >10 M Ω
- Contact bounce : max. 10 ms
- Dielectric strength between adjacent contacts : 1000 V for 2 min
- Insulation resistance between adjacent contacts : 5 X 10¹³ Ω
- Capacitance between adjacent contacts :0.5 pF



MECHANICAL SPECIFICATIONS

- Standard actuation force : 2.5 N
- Max. actuation force : 100 N for 10 sec
- Travel : 1.8 mm
- Lifetime :
 - momentary : >10,000,000 cycles
 - latching : 5,000,000 cycles

The company reserves the right to change specifications without notice.



MATERIALS




- Housing : LCP UL94V0
- Actuator : LCP UL94V0
- Switch spring : Stainless steel
- Key spring : Stainless steel
- Latch pin : Stainless steel
- Fixed contacts :
 - Silver : SnCu + 2 μ NI + 3 μ Ag
 - Gold : SnCu + 2 μ NI + 3 μ Au
- Moving contacts :
 - Silver : Stainless steel + 3 μ Ag
 - Gold : Stainless steel + 3 μ Ag + 1 μ Au
- Terminals : SnCu + 2 μ NI + 3 μ Sn100

All tolerance if not otherwise specified \pm 0.2mm.

Unimec™

8 contact functions •
2 pole • distinct tactile feel

UNIMEC





- TH
- momentary, latching or quiet
- 8 contact functions

All tolerances unless otherwise noted : ±0.2 mm




PCB LAYOUT


PCB MOUNTING HOLE DIMENSIONS



With 3 mm LED
16923 and 16924




With round LED
16920 and 16921





With square LED
16922

FUNCTIONAL DIAGRAM




- up
-- down

CIRCUIT DIAGRAM



With round LED
16920 and 16921




With rect LED
16922




WIRING


Select the contact function you require - and design your PC board accordingly




1 make contact




1 break contact




1 change over contact




2 make contact




2 break contact



2 change over contact




2 make & 2 break



reverse polarity



BUILD YOUR PART NUMBER



*quiet function has silver terminals, in case of gold terminals the part number is 15420



ABOUT THIS SERIES

- Notice** : please note that not all combinations of above numbers are available. Contact APEM for further information.
- Marking on the switch for identification** : 15400 A; 15420 H; 15401 E; 15402 F; 15451 I; 15452 J
- Accessories** : See www.apem.com for cap & bezel options.




Unimec™

8 contact functions •
2 pole • distinct tactile feel



VARIO SUPPORT MOUNTING


For all types of Unimec™ switches with bezels - 16310 - 16315 and 16324 - 16326.
More options available as custom.




16.410 (1x1)




16.412 (1x3)



16.414 (1x5)



16.416 (1x7)




16.418 (1x9)




16.411 (1x2)




16.413 (1x4)



16.415 (1x6)



16.417 (1x8)




16.419 (1x10)




16.420 (2x2)




16.430 (3x3)



16.440 (4x4)



16.450 (5x5)



16.460 (6x6)

LED COMPONENT SPECIFICATIONS

Part Nos.	16920/16921			16922			16923				16924				
	G	Y	R	G	Y	R	B	G	Y	W	R	G	Y	R	
Color (G=green, Y=yellow, R=red)	G	Y	R	G	Y	R	B	G	Y	W	R	G	Y	R	
Color Codes	02	04	08	02	04	08	00	20	40	65	80	23	45	88	
ABSOLUTE MAXIMUM RATINGS (Ta=25°C)															
Power	mW	100	100	100	135	135	135	105	70	60	120	60	150	130	300
Current forward	mA	30	30	30	30	30	30	30	20	20	25	20	40	40	90
Forward peak current	mA	50	50	50	90	90	90	200	60**	60**	100	60**	500	500	1000
Voltage reverse	V	5	5	5	5	5	5	5	3	3	5	3	12	12	5
Operating temperature	°C	-25 / +100			-55 / +100			-25 / +85				-55 / +100			
Storage temperature	°C	-25 / +100			-55 / +100			-30 / +100				-55 / +100			
Soldering temperature	°C	+245 for max. 3 sec			+300 for max. 3 sec			+260 for max. 5 sec				+300 for max. 3 sec			
ELECTRICAL-OPTICAL CHARACTERISTICS (Ta=25°C)															
Voltage forward	Typ. V	2.0	2.0	2.0	2.1	2.2	2.3	2.1	2.1	2.1	3.8	2.0	2.1*	2.3***	2.4***
	Max. V	3.0	3.0	3.0	3.0	3.0	3.0	3.0	2.8	3.0	3.0	4.3	3.0	2.5*	2.5***
Current reverse	µA	100	100	100	100	100	100	2	10	10	50	10	10	10	10
Wave length	nm	560	590	660	565	585	635	460	563	585	NA	650	570	587	635
Spread	Ønm	10	10	10	10	10	10	40	40	40	NA	40	25	45	45
Spread angle	degree	20	20	20	45	45	45	20	45	45	25	45	25	45	45
Luminous Intensity	Min. mcd	1	1	0.8	1.5	2.5	2.5	20	9.0	5.6	630	5.6	71****	71****	100****
	Typ. mcd	2	3	1.6	2.5	3.0	5.0	25	25	16	1000	16	112****	112****	160****
Orientation	The longer pin is the anode, the shorter is the cathode.														

*I_F=20mA, **Pulse width 1ms Duty cycle 1:5, ***I_F=50mA, ****Luminous Flux lm/m



USAGE GUIDELINES

HOW TO GET THE BEST RESULTS WITH MEC SWITCHES ?

These guidelines are offered to users of MEC Switches as an aid to ensure successful and reliable switch operation. Please see the technical specifications for details on operating and storage temperatures and soldering guidelines to make sure you select the best switch for your application. When wave soldering is taking place, MEC strongly recommends that the temperature profile is analyzed and compared with the temperature rating of the switch. It is also important to monitor the accumulated heat buildup from both the pre-heat zones and the solder zone.

All standard accessories for unimec™ switches are made from ABS plastic with a maximum operating temperature of 65°C. It is strongly recommended that accessories are mounted after soldering of the switch.

LEDs have their own temperature specifications. When fitted in a switch the LED will determine the max. operating temperature, i.e. 16923 has an upper temperature limit of 85°C!

MOUNTING AND DISMOUNTING

If switches are to be mounted in rows it is essential that the recommendations regarding spacing are followed. PC board thickness should be 1.4±0.2 mm and terminal hole diameter should be 0.9 mm.

All unimec™ caps and bezels are easily snapped onto the switch modules and can be changed at a later time with the exception of the unimec 16.700 cap. Once this cap is installed it is not designed to be removed. To do so may cause damage to the switch and the PC board if not done very carefully.

If the 16.300 or 16.700 cap must be removed from a unimec™ latching switch, make sure that the switch actuator is in the released, upper position before attempting to remove the cap. This will prevent possible damage to the internal latching pin.

SOLDERING AND CLEANING UNIMEC™ SERIES

Most assembly and field problems experienced by users of unsealed switches are caused by the contamination of the contacts during soldering and cleaning.

Contact contamination may be recognized by an increase in contact resistance and possible intermittent operation of the switch, especially in low power applications. Care must be taken not to submerge the switch in cleaning agents or

spray the switch during cleaning. The switch must be protected at all times to prevent contamination by flux or cleaning liquids.

For unimec™ latching versions we recommend to leave the actuator in the released upper position during soldering. This makes the switch more resistant to overheating.

SOLDERING - THROUGH HOLE VERSIONS

Hand soldering: Max. 350°C for max. 3 sec.

Wave soldering: Heat built up in the switch during pre-heating and soldering must not exceed the maximum operating temperature of the switch. Peak temperature must not exceed 260°C, and soldering time is max 10 sec. (IEC-68-2-20)

ROHS COMPLIANCE

As of 1 July 2006 MEC has completed the conversion to RoHS compliance. For more info please see our homepage www.apem.com

TEMPERATURE LIMITS:

Switch	160 °C
LEDs	85/100 °C
Accessories	65 °C

PACKAGING

Unimec™ switches are packed in rigid tubes of 50 pieces each.

A box contains 1.000 pcs.