



+ CONNECTORS

DISCRETE SOCKETS



✓ Active

TE CONNECTIVITY (TE)

SKT MS S4 BN SN-SN 10M W/SEAL

MINI-SPRING SOCKETS | Series 4

1-5645501-2

TE Internal Number: 1-5645501-2

EU RoHS Compliant

EU ELV Compliant

Hole Size (Recommended) 1.75 mm [.069 in]

Socket Length 6.6 mm [.26 in]

Sealant With

Sleeve Style Bullet Nose

Wire/Cable Size .653 mm² [19 AWG]

[↓](#) **PRODUCT DRAWING**
English

[↓](#) **3D PDF**

DOCUMENTATION

Product Drawings

MINIATURE SPRING SOCKET ASSY SERIES 4

PDF (TIFF AVAILABLE)

English

CAD Files

Customer View Model

3D_IGS.ZIP

English

Customer View Model

3D_STP.ZIP

English

Customer View Model

2D_DXF.ZIP

English

3D PDF

PDF

English

Product Environmental Compliance

TE Material Declaration

MD_1-5645501-2_072920151216_dmtec

PDF

English

FEATURES



Please review product documents or [contact us](#) for the latest agency approval information.

Please Note: Use the Product Drawing for all design activity.

Product Type Features

Sleeve Style Bullet Nose

Connector System Cable-to-Board

Sealable No

Connector & Contact Terminates To Printed Circuit Board

Product Type Contact

Profile Zero

Wire/Cable Type Discrete Wire

Body Features

Sealant With

Sleeve Plating Material Tin

Sleeve Material Copper

Contact Features

Contact Current Rating (Max) (A) 7.5

Contact Type Socket

Contact Spring Plating Material Tin

Contact Mating Area Plating Thickness (µm) 2.54

Contact Transmits (Typical) Signal (Data)/Power

Contact Base Material Beryllium Copper

Socket Type Discrete

Termination Features

Termination Method to PC Board Through Hole - Press-Fit

Termination Method to Wire/Cable Solder

Insertion Method Hand/Semi-Automatic/Automatic

Dimensions

Socket Length 6.6 mm [.26 in]

Hole Size (Recommended) 1.75 mm [.069 in]

Wire/Cable Size .653 mm² [19 AWG]

Mating Pin Diameter Range .94 – 1.04 mm [.037 – .041 in]

PCB Thickness (Recommended) .79 – 3.18 mm [.031 – .125 in]

Usage Conditions

Operating Temperature Range -65 – 125 °C [-85 – 257 °F]

Operation/Application

Circuit Application Power, Signal

Packaging Features

Packaging Method Carrier Tape, Reel

Packaging Quantity 10000

Other

Spring Material Beryllium Copper

PRODUCT COMPLIANCE



Statement of Compliance

Statement of Compliance

PDF
