

<p>0394</p> <p>0394-0-15-XX-07-XX-10-0 Solder mount in .120 min. mounting hole</p>	<p>0393</p> <p>0393-0-15-XX-07-XX-10-0 Solder mount in .144 min. mounting hole</p>	<p>0391</p> <p>0391-0-15-XX-07-XX-10-0 Solder mount in .159 min. mounting hole</p>	<p>9016</p> <p>9016-0-15-XX-07-XX-10-0 Press-fit in .131 mounting hole</p>
<p>0493</p> <p>0493-0-15-XX-07-XX-10-0 Press-fit in .144 mounting hole</p>	<p>0490</p> <p>0490-0-15-XX-07-XX-04-0 Press-fit in .144 mounting hole</p>	<p>0616</p> <p>0616-0-18-XX-07-XX-10-0 Press-fit in .144 mounting hole</p>	<p>0387</p> <p>0387-0-15-XX-07-XX-04-0 Solder mount in .063 min. mounting hole</p>
<p>0370</p> <p>0370-0-19-XX-07-XX-10-0 #18 Gage crimp barrel</p>	<p>4040</p> <p>4040-0-19-XX-07-XX-10-0 Wire Termination</p>	<p>0491</p> <p>0491-0-19-XX-07-XX-04-0 For use in stackable patch cords</p>	<p>9214</p> <p>9214-0-15-XX-07-XX-10-0 Solder mount in .083 min. mounting hole</p>

SPECIFICATIONS

SHELL MATERIAL:
Brass Alloy 360, 1/2 Hard

CONTACT MATERIAL:
Beryllium Copper Alloy 172, HT

DIMENSION IN INCHES
TOLERANCES ON:
LENGTHS: ±.005
DIAMETERS: ±.002
ANGLES: ± 2°

ORDER CODE: XXXX - X - 1X - XX - 07 - XX - XX - 0

BASIC PART #

SPECIFY SHELL FINISH:
01 200µ" TIN/LEAD OVER NICKEL
80 200µ" TIN OVER NICKEL
15 10µ" GOLD OVER NICKEL

SPECIFY CONTACT FINISH:
01 200µ" TIN/LEAD OVER NICKEL
80 200µ" TIN OVER NICKEL
27 30µ" GOLD OVER NICKEL



CONTACT

#07 CONTACT (DATA ON PAGE 214)