




Silicone Cover Stranded-Core Wire - 25ft 26AWG - Orange

PRODUCT ID: 2520

There are multiple versions of this item. Please select one from the options below:



There are multiple versions of this item. Please select one from the options below:

2m

25ft

18 IN STOCK

1

ADD TO CART

1-9

10-24

25-49

50+

ADD TO WISHLIST


DESCRIPTION


TECHNICAL DETAILS

DESCRIPTION

Silicone-sheathing wire is super-flexible and soft, and its also strong! Able to handle up to 200°C and up to 600V, it will do when PVC covered wire wimps out. We like this wire for being extremely supple and flexible, so it is great for wearables or projects where the wire-harness has to be able to deal with a lot of bending.

Comes with one 25ft spool of **orange** wire. The wire is 26AWG stranded with an outer diameter of 1.5mm.

New Products 7/1/2015 



TECHNICAL DETAILS

- Length: 25 feet / 7.6m
- Outer Diameter: 1.5mm / 0.06"
- Nominal Voltage: 600V
- Temperature Range: -60°C ~ 200°C
- OD Tolerance: $\pm 0.1\text{mm}$
- Resistance: 123 Ω/Km
- Current Handling Capability: $\sim 3.5\text{A}$ (depends on length!)



MAY WE ALSO SUGGEST...



"Wire Wrap" Thin




Solid-Core Wire Spool - 25ft



Silicone Cicoil Wire Cable -




Solid-Core Wire Spool - 25ft




Silicone Cover Stranded-




Solid-Core Wire Spool - 25ft



Silicone Cover Stranded-



Silicone Cover Stranded-




Silicone Cover Stranded-



Silicone Cover Stranded-



Silicone Cover Stranded-



Silicone Cover Stranded-

DISTRIBUTORS [EXPAND TO SEE DISTRIBUTORS](#)

[CONTACT](#)

[SUPPORT](#)

[DISTRIBUTORS](#)

[EDUCATORS](#)

[JOBS](#)

[FAQ](#)

[SHIPPING & RETURNS](#)

[TERMS OF SERVICE](#)

[PRIVACY & LEGAL](#)

[ABOUT US](#)

"By always thinking unto them. I keep the subject constantly before me and wait till the first dawnings open little by little into the full light" - Isaac Newton

ENGINEERED IN NYC Adafruit®



4.9 ★★★★★
Google
Customer Reviews