

Chip NTC Thermistors (Protection Device)

Product Top Page	Search by Part No.	Search by Characteristics	Cross Reference	Catalog	Tech Notes
------------------	--------------------	---------------------------	-----------------	---------	------------

NTCG163JX103DT1S



Applications Automotive Grade

Features
150°C 150°C
AEC-Q200 AEC-Q200

Series NTCG

Status Production

Brand TDK

PDF file of this page

Contact



Images are for reference only and show exemplary products.

Size	
Length(L)	1.60mm ±0.10mm
Width(W)	0.80mm ±0.10mm
Thickness(T)	0.80mm ±0.10mm
Terminal Width(B)	0.20mm Min.
Recommended Land Pattern (PA)	0.70mm ±0.10mm
Recommended Land Pattern (PB)	0.70mm ±0.10mm
Recommended Land Pattern (PC)	0.70mm ±0.10mm

Electrical Characteristics	
Resistance [at 25°C]	10kΩ
Resistance Tolerance	±0.5%
B value (Typ.) [25/50°C]	3380K
B value (Typ.) [25/85°C]	3435K
B value (Typ.) [25/100°C]	3453K
B value Tolerance	±0.7%
Max. Electric Power [at 25°C] ?	125mW
Permissible Operating Current [at 25°C] ?	310μA
Thermal Dissipation Constant [at 25°C] ?	1mW/°C 1mW/K

Other	
Max. Operating Temperature	150°C
Soldering Method	Reflow
UL File No.	
AEC-Q200	Yes
Packing	Punched (Paper)Taping [180mm Reel]
Package Quantity	4000pcs
Weight	0.005g



[Selection Guide](#) [Search by Part No.](#) [Search by Characteristics](#) [Distributor Inventory Check](#) [Cross Reference](#)

Products

- [Capacitors](#) >
- [Inductors \(Coils\)](#) >
- [EMC Components](#) >
- [RF Components and Modules](#) >
- [Voltage / Current / Temperature Protection Devices](#) >
- [Sensors and Sensor Systems](#) >
- [Ceramic Switching / Heating, Piezo Components, Buzzers and Microphones](#) >
- [Transformers](#) >
- [Ferrites and Accessories](#) >
- [Noise Suppressing / Magnetic Sheet](#) >
- [Anechoic Chambers and Radio Wave Absorbers](#) >
- [Power Supplies](#) >
- [Magnets](#) >
- [Flash Storages](#) >
- [Wireless Power Transfer](#) >
- [FA Systems](#) >
- [Transparent Conductive Film](#) >
- [Micro Modules \(Substrates with Built-in ICs, Products Utilizing with SESUB\)](#) >
- [Solar Cells](#) >
- [Biosensor](#) >
- [Application Specific IC \(ASIC\) Development and Supply](#) >

Application Guides

Technical Support

Tech Library

Environment

Contact

News

Home

About TDK

TDK Worldwide

[Terms of Use](#) [Privacy Policy](#) [Cookie Policy](#)

Copyright(c) 2018 TDK Corporation. All rights reserved.
TDK logo is a trademark or registered trademark of TDK Corporation.

