





**TOPJOB®S Rail-Mount Terminal Blocks**  
With Lever – Push-Button – Open Tool Slot





## CONTENTS

|   |         |
|---|---------|
| <b>3 Ways to Wire = 1 Family</b>  | 3 - 4   |
| <b>TOPJOB®S Terminal Blocks with Push-in CAGE CLAMP® - Levers and Open Tool Slot or Push-Button</b> | 5 - 6   |
| <b>TOPJOB®S Terminal Blocks with Push-in CAGE CLAMP® - Push-Button</b>                              | 7 - 8   |
| <b>TOPJOB®S Terminal Blocks with Push-in CAGE CLAMP® - Open Tool Slot</b>                           | 9 - 10  |
| <b>Accessories</b>  | 11 - 12 |
| <b>Clearly Mark Control Cabinets</b>  | 13      |
| <b>Application Solutions</b>  | 14      |

# 3 WAYS TO WIRE = 1 FAMILY

## TOPJOB®S Terminal Blocks

The TOPJOB®S family, with Push-in CAGE CLAMP®, was the first to introduce push-in wiring for rail mount terminal blocks. Since its introduction, new features and benefits have been added every year. Taking yet another leap forward, the family now offers levers and push-buttons for convenient and intuitive wire termination while maintaining the vibration-proof, gas-tight, corrosion and thermal-cycling resistant connection the industry has come to expect from us.

### One Family

All 3 operating versions share the same Push-in CAGE CLAMP® technology and profile, which allows accessories to be shared across the entire family.

### Same Jumper System

No matter which version of wiring operation, they all share the industry's broadest jumper offering, as well as the TOPJOB®S exclusive jumper retention spring.

### Built-in Test Ports


Simplifies testing and troubleshooting for the entire family.

### Push-in Wiring Technology

Push-in CAGE CLAMP®, invented by WAGO, is the universal connection technology for all conductor types. Offering fast, vibration-proof, gas-tight, corrosion and thermal-cycling resistant connection of solid and stranded conductors.

### Continuous, Multi-line Marking

Continuous strip marking and the **smart**PRINTER offer the fastest and most economical terminal block marking. Multi-line marking simplifies wiring identification and troubleshooting.



For More Information Visit:  
[www.wago.com/topjob-s/us](http://www.wago.com/topjob-s/us)

# TOPJOB®S TERMINAL BLOCKS


## With Push-in CAGE CLAMP® - Levers and Open Tool Slot or Push-Button

Levers have long been associated with simplifying an action and the TOPJOB®S terminal blocks with lever operation are no different. With a lever on one side and a open tool slot or push-button on the other, wiring tasks are not only easy but also intuitive.


Lever Advantages:

- Simple - lever up, insert conductor, lever down – done
- Intuitive - tool-free operation ideal for field wiring
- Secure – opened lever “clicks” securely into place for hands-free wiring
- Hands-free - means both hands are free to cut, strip and insert the conductor


All Conductor Types 22 - 4 AWG:




Push-in termination of solid conductors



Push-in termination of ferruled conductors



Lever up until it “clicks”, insert the conductor and lever down for all conductor types



# TOPJOB®S WITH LEVER

## Series 21XX

| Series  |       |  | 2102  |  | 2106   |  | 2116  |
|---|-------|--|---|--|--|--|---|
| Conductor Range<br>Electrical Specs<br>Terminal Block Width                           |       |  | 22 ... 12 AWG<br>600 V, 20 A <sup>(1)</sup><br>5.2 mm |  | 20 ... 8 AWG<br>600 V, 50 A <sup>(1)</sup><br>7.5 mm |  | 20 ... 4 AWG<br>600 V, 85 A <sup>(1)</sup><br>12 mm |
|   | Color |  | Item No.  |  | Item No.   |  | Item No.  |
| <b>2-Conductor Through or Ground Terminal Block, with a Lever and Open Tool Slots</b> |       |  |   |  |  |  |   |
|   | ○     |  | 2102-1201   |  | 2106-1201  |  | 2116-1201   |
|   | ●     |  | 2102-1204   |  | 2106-1204  |  | 2116-1204   |
|   | ◐     |  | 2102-1207   |  | 2106-1207  |  | 2116-1207   |
| <b>End and Intermediate Plate</b>   |       |  |   |  |  |  |   |
|   | ●     |  | 2102-1292   |  | 2106-1292  |  | 2116-1292   |
|   | ○     |  | 2102-1291   |  | 2106-1291  |  | 2116-1291   |
| <b>3-Conductor Through or Ground Terminal Block, with a Lever and Open Tool Slots</b> |       |  |   |  |  |  |   |
|   | ○     |  | 2102-1301   |  | 2106-1301  |  | 2116-1301   |
|   | ●     |  | 2102-1304   |  | 2106-1304  |  | 2116-1304   |
|   | ◐     |  | 2102-1307   |  | 2106-1307  |  | 2116-1307   |
| <b>End and Intermediate Plate</b>   |       |  |   |  |  |  |   |
|   | ●     |  | 2102-1392   |  | 2106-1392  |  | 2116-1392   |
|   | ○     |  | 2102-1391   |  | 2106-1391  |  | 2116-1391   |
| <b>2-Conductor Through or Ground Terminal Block, with a Lever and Push-Button</b>     |       |  |   |  |  |  |   |
|   | ○     |  | 2102-5201   |  | 2106-5201  |  | 2116-5201   |
|   | ●     |  | 2102-5204   |  | 2106-5204  |  | 2116-5204   |
|   | ◐     |  | 2102-5207   |  | 2106-5207  |  | 2116-5207   |
| <b>End and Intermediate Plate</b>   |       |  |   |  |  |  |   |
|   | ●     |  | 2102-1292   |  | 2106-1292  |  | 2116-1292   |
|   | ○     |  | 2102-1291   |  | 2106-1291  |  | 2116-1291   |
| <b>3-Conductor Through or Ground Terminal Block, with a Lever and Push-Buttons</b>    |       |  |   |  |  |  |   |
|   | ○     |  | 2102-5301   |  | 2106-5301  |  | 2116-5301   |
|   | ●     |  | 2102-5304   |  | 2106-5304  |  | 2116-5304   |
|   | ◐     |  | 2102-5307   |  | 2106-5307  |  | 2116-5307   |
| <b>End and Intermediate Plate</b>   |       |  |   |  |  |  |   |
|   | ●     |  | 2102-1392   |  | 2106-1392  |  | 2116-1392   |
|   | ○     |  | 2102-1391   |  | 2106-1391  |  | 2116-1391   |

1) VDE Approved

# TOPJOB®S TERMINAL BLOCKS

## With Push-in CAGE CLAMP® - Push-Button

Push-button operation has been part of the WAGO product offering since the founding of the company. Primarily used in PCB and chassis mount terminal blocks, it is now offered in our TOPJOB®S rail mount terminal block family.

### Push-button Advantages:

- Simple – press down orange push-button with tool, insert conductor, release – done
- Intuitive – orange push-button clearly distinguishes wire entry from tool entry
- Options – push-button for rail-mount, as well as PCB and chassis mount, terminal blocks
- Unique push-button design ensures operation integrity with positive feedback


All Conductor Types 24 - 4 AWG:




Push-in termination of solid and ferruled conductors



Terminate fine-stranded conductors via operating tool



Remove all conductors via operating tool



# TOPJOB®S WITH PUSH-BUTTON

## Series 22XX

| Series  |       | 2200  | 2201  | 2202  | 2204  | 2206   | 2210  | 2216  |
|---|-------|---|---|---|---|--|---|---|
| Conductor Range<br>Electrical Specs<br>Terminal Block Width     |       | 24 ... 16 AWG<br>600 V, 10 A <sup>(1)</sup><br>3.5 mm | 22 ... 14 AWG<br>600 V, 15 A <sup>(1)</sup><br>4.2 mm | 22 ... 12 AWG<br>600 V, 20 A <sup>(1)</sup><br>5.2 mm | 20 ... 10 AWG<br>600 V, 30 A <sup>(1)</sup><br>6.2 mm | 20 ... 8 AWG<br>600 V, 50 A <sup>(1)</sup><br>7.5 mm | 20 ... 6 AWG<br>600 V, 65 A <sup>(1)</sup><br>10 mm | 20 ... 4 AWG<br>600 V, 85 A <sup>(1)</sup><br>12 mm |
|   | Color | Item No.  | Item No.  | Item No.  | Item No.  | Item No.   | Item No.  | Item No.  |
| 2-Conductor Through or Ground Terminal Block, with Push-Buttons |       |   |   |   |   |  |   |   |
|   | ○     | 2200-1201   | 2201-1201   | 2202-1201   | 2204-1201   | 2206-1201  | 2210-1201   | 2216-1201   |
|   | ●     | 2200-1204   | 2201-1204   | 2202-1204   | 2204-1204   | 2206-1204  | 2210-1204   | 2216-1204   |
|   | ●     | 2200-1207   | 2201-1207   | 2202-1207   | 2204-1207   | 2206-1207  | 2210-1207   | 2216-1207   |
| End and Intermediate Plate                                      |       |   |   |   |   |  |   |   |
|   | ●     | 2000-1292   | 2001-1292   | 2002-1292   | 2004-1292   | 2006-1292  | 2010-1292   | 2016-1292   |
|   | ○     | 2000-1291   | 2001-1291   | 2002-1291   | 2004-1291   | 2006-1291  | 2010-1291   | 2016-1291   |
| 3-Conductor Through or Ground Terminal Block, with Push-Buttons |       |   |   |   |   |  |   |   |
|   | ○     | 2200-1301   | 2201-1301   | 2202-1301   | 2204-1301   | 2206-1301  | 2210-1301   | 2216-1301   |
|   | ●     | 2200-1304   | 2201-1304   | 2202-1304   | 2204-1304   | 2206-1304  | 2210-1304   | 2216-1304   |
|   | ●     | 2200-1307   | 2201-1307   | 2202-1307   | 2204-1307   | 2206-1307  | 2210-1307   | 2216-1307   |
| End and Intermediate Plate                                      |       |   |   |   |   |  |   |   |
|   | ●     | 2000-1392   | 2002-1392   | 2002-1392   | 2004-1392   | 2006-1392  | 2010-1392   | 2016-1392   |
|   | ○     | 2000-1391   | 2002-1391   | 2002-1391   | 2004-1391   | 2006-1391  | 2010-1391   | 2016-1391   |
| 4-Conductor Through or Ground Terminal Block, with Push-Buttons |       |   |   |   |   |  |   |   |
|   | ○     | 2200-1401   | 2201-1401   | 2202-1401   | 2204-1401   |  |   |   |
|   | ●     | 2200-1404   | 2201-1404   | 2202-1404   | 2204-1404   |  |   |   |
|   | ●     | 2200-1407   | 2201-1407   | 2202-1407   | 2204-1407   |  |   |   |
| End and Intermediate Plate                                      |       |   |   |   |   |  |   |   |
|   | ●     | 2000-1492   | 2001-1492   | 2002-1492   | 2004-1492   |  |   |   |
|   | ○     | 2000-1491   | 2001-1491   | 2002-1491   | 2004-1491   |  |   |   |

1) UL Approved

# TOPJOB®S TERMINAL BLOCKS

## With Push-in CAGE CLAMP® - Open Tool Slot

The first member of the TOPJOB®S family and the one that started the "push-in" wiring revolution for rail mount terminal blocks. It introduced direct push-in of solid or ferruled conductors while also allowing traditional tool operation for all conductor types, just like the original CAGE CLAMP®.

### Open Tool Slot Advantages:

- Simple – insert tool, insert conductor, remove tool – done
- Innovative – industry's first push-in wiring rail mount terminal block
- Secure – inserted tool is locked into place for hands-free wiring
- Hands-free - means both hands are free to cut, strip and insert the conductor

All Conductor Types 24 - 4 AWG:




Push-in termination of solid and ferruled conductors



Terminate fine-stranded conductors via operating tool



Remove all conductors via operating tool



# TOPJOB®S WITH OPEN TOOL SLOT

## Series 20XX

| Series  |       | 2000  | 2001  | 2002  | 2004  | 2006   | 2010  | 2016  |
|---|-------|---|---|---|---|--|---|---|
| Conductor Range<br>Electrical Specs<br>Terminal Block Width                           |       | 24 ... 16 AWG<br>600 V, 10 A <sup>(1)</sup><br>3.5 mm | 22 ... 14 AWG<br>600 V, 15 A <sup>(1)</sup><br>4.2 mm | 22 ... 12 AWG<br>600 V, 20 A <sup>(1)</sup><br>5.2 mm | 20 ... 10 AWG<br>600 V, 30 A <sup>(1)</sup><br>6.2 mm | 20 ... 8 AWG<br>600 V, 50 A <sup>(1)</sup><br>7.5 mm | 20 ... 6 AWG<br>600 V, 65 A <sup>(1)</sup><br>10 mm | 20 ... 4 AWG<br>600 V, 85 A <sup>(1)</sup><br>12 mm |
|   | Color | Item No.  | Item No.  | Item No.  | Item No.  | Item No.   | Item No.  | Item No.  |
| 2-Conductor Through or Ground Terminal Block  |       |   |   |   |   |  |   |   |
|    | ○     | 2000-1201   | 2001-1201   | 2002-1201   | 2004-1201   | 2006-1201  | 2010-1201   | 2016-1201   |
|   | ●     | 2000-1204   | 2001-1204   | 2002-1204   | 2004-1204   | 2006-1204  | 2010-1204   | 2016-1204   |
|   | ●     | 2000-1207   | 2001-1207   | 2002-1207   | 2004-1207   | 2006-1207  | 2010-1207   | 2016-1207   |
| End and Intermediate Plate  |       |   |   |   |   |  |   |   |
|    | ●     | 2000-1292   | 2002-1292   | 2002-1292   | 2004-1292   | 2006-1292  | 2010-1292   | 2016-1292   |
|   | ○     | 2000-1291   | 2002-1291   | 2002-1291   | 2004-1291   | 2006-1291  | 2010-1291   | 2016-1291   |
| 3-Conductor Through or Ground Terminal Block  |       |   |   |   |   |  |   |   |
|   | ○     | 2000-1301   | 2001-1301   | 2002-1301   | 2004-1301   | 2006-1301  | 2010-1301   | 2016-1301   |
|   | ●     | 2000-1304   | 2001-1304   | 2002-1304   | 2004-1304   | 2006-1304  | 2010-1304   | 2016-1304   |
|   | ●     | 2000-1307   | 2001-1307   | 2002-1307   | 2004-1307   | 2006-1307  | 2010-1307   | 2016-1307   |
| End and Intermediate Plate  |       |   |   |   |   |  |   |   |
|  | ●     | 2000-1392   | 2002-1392   | 2002-1392   | 2004-1392   | 2006-1392  | 2010-1392   | 2016-1392   |
|   | ○     | 2000-1391   | 2002-1391   | 2002-1391   | 2004-1391   | 2006-1391  | 2010-1391   | 2016-1391   |
| 4-Conductor Through or Ground Terminal Block  |       |   |   |   |   |  |   |   |
|  | ○     | 2000-1401   | 2001-1401   | 2002-1401   | 2004-1401   |  |   |   |
|   | ●     | 2000-1404   | 2001-1404   | 2002-1404   | 2004-1404   |  |   |   |
|   | ●     | 2000-1407   | 2001-1407   | 2002-1407   | 2004-1407   |  |   |   |
| End and Intermediate Plate  |       |   |   |   |   |  |   |   |
|  | ●     | 2000-1492   | 2002-1492   | 2002-1492   | 2004-1492   |  |   |   |
|   | ○     | 2000-1491   | 2002-1491   | 2002-1491   | 2004-1491   |  |   |   |

1) VDE Approved



# TOPJOB®S TERMINAL BLOCKS

## Accessories

Having the right accessories available is an important consideration when selecting the right terminal block for your application. With the broadest range of accessories in the industry, the TOPJOB®S family of accessories not only increases safety and functionality, but they also reduce assembly time, troubleshooting and costs.

### Advantages:

- Exclusive jumper retention spring securely holds the jumpers in place
- Industry's most comprehensive jumper offering simplifies complex wiring tasks
- Multi-line, continuous strip marking is fast, economical and clearly identified
- One family — accessories fit all TOPJOB®S terminal blocks in the same series




# TOPJOB®S TERMINAL BLOCKS

## Accessories

| Series   | Description                              | 2000<br>Item No. | 2001<br>Item No. | 2002<br>Item No. | 2004<br>Item No. | 2006<br>Item No. | 2010<br>Item No. | 2016<br>Item No. |
|--|--|------------------|------------------|------------------|------------------|------------------|------------------|------------------|
| Modular Connection for Jumper Contact Slot and Spacer Module, Snaps Together, Gray |  |                  |                  |                  |                  |                  |                  |                  |
|  | <input type="radio"/> Modular Connection | 2000-511         | 2001-511         | 2002-511         | 2004-511         | 2006-511         | 2010-511         | 2016-511         |
|  | <input type="radio"/> Spacer Module      | 2000-549         | 2001-549         | 2002-549         | 2004-549         | 2006-549         | 2010-549         | 2016-549         |
| Push-in Type Jumper, Insulated, Light Gray   |  |                  |                  |                  |                  |                  |                  |                  |
|  | <input type="radio"/> 2-way              | 2000-402         | 2001-402         | 2002-402         | 2004-402         | 2006-402         | 2010-402         | 2016-402         |
|  | <input type="radio"/> 3-way              | 2000-402         | 2001-402         | 2002-402         | 2004-402         | 2006-402         | 2010-402         | 2016-402         |
|  | <input type="radio"/> 4-way              | 2000-404         | 2001-404         | 2002-404         | 2004-404         | 2006-404         | 2010-404         | 2016-404         |
|  | <input type="radio"/> 10-way             | 2000-410         | 2001-410         | 2002-410         | 2004-410         |                  |                  |                  |
| Push-in Type Jumper, Insulated Light Gray  |  |                  |                  |                  |                  |                  |                  |                  |
|  | <input type="radio"/> 1 to 3             | 2000-433         | 2001-433         | 2002-433         | 2004-433         | 2006-433         | 2010-433         | 2016-433         |
|  | <input type="radio"/> 1 to 4             | 2000-434         | 2001-434         | 2002-434         | 2004-434         | 2006-434         | 2010-434         | 2016-434         |
|  | <input type="radio"/> 1 to 5             | 2000-435         | 2001-435         | 2002-435         | 2004-435         | 2006-435         | 2010-435         | 2016-435         |
|  | <input type="radio"/> 1 to 10            | 2000-440         | 2001-440         | 2002-440         | 2004-440         | 2006-440         | 2010-440         | 2016-440         |
| Step-Down Jumper, Insulated, Light Gray  |  |                  |                  |                  |                  |                  |                  |                  |
|  | <input type="radio"/> Step-Down          |                  | 2006-499         | 2006-499         | 2006-499         | 2006-499         | 2006-499         | 2016-499         |
| Insulation Stop, 5 pcs/strip, Light Gray, Dark Gray                                |  |                  |                  |                  |                  |                  |                  |                  |
|  | <input type="radio"/> Light Gray         |                  | 2001-171         | 2002-171         | 2004-171         |                  |                  |                  |
|  | <input type="radio"/> Dark Gray          |                  |                  | 2002-172         | 2004-172         |                  |                  |                  |
| <b>Accessories</b>   |  |                  |                  |                  |                  |                  |                  |                  |
| Staggered Jumper, Insulated, Light Gray  |  |                  |                  |                  |                  |                  |                  |                  |
|  | <input type="radio"/> 2-way              |                  |                  | 2002-472         |                  |                  |                  |                  |
|  | <input type="radio"/> 3-way              |                  |                  | 2002-473         |                  |                  |                  |                  |
|  | <input type="radio"/> 4-way              |                  |                  | 2002-474         |                  |                  |                  |                  |
|  | <input type="radio"/> 12-way             |                  |                  | 2002-482         |                  |                  |                  |                  |
| Customized Staggered Jumper, Insulated, Light Gray                                 |  |                  |                  |                  |                  |                  |                  |                  |
|  | <input type="radio"/> 1-3                |                  |                  | 2002-473/011-000 |                  |                  |                  |                  |
|  | <input type="radio"/> 1-3-5              |                  |                  | 2002-475/011-000 |                  |                  |                  |                  |
|  | <input type="radio"/> 1-3-5-7            |                  |                  | 2002-477/011-000 |                  |                  |                  |                  |
|  | <input type="radio"/> 1-3-5-7-9          |                  |                  | 2002-479/011-000 |                  |                  |                  |                  |
|  | <input type="radio"/> 1-3-5-7-9-11       |                  |                  | 2002-487/011-000 |                  |                  |                  |                  |
| Adjacent Jumper for Continuous Commoning, Insulated, Light Gray                    |  |                  |                  |                  |                  |                  |                  |                  |
|  | <input type="radio"/> 2-way              |                  |                  | 2002-400         |                  |                  |                  |                  |
|  | <input type="radio"/> 1 to 3             |                  |                  | 2002-423         |                  |                  |                  |                  |
| Push-In Type Wire Jumper, Insulated, Gray, Black                                   |  |                  |                  |                  |                  |                  |                  |                  |
|  | 60 mm                                    | 2009-402         | 2009-402         | 2009-402         |                  |                  |                  |                  |
|  | 110 mm                                   | 2009-404         | 2009-404         | 2009-404         |                  |                  |                  |                  |
|  | 250 mm                                   | 2009-406         | 2009-406         | 2009-406         |                  |                  |                  |                  |
| <b>Test Plug Accessories</b>   |  |                  |                  |                  |                  |                  |                  |                  |
|  | Adapter                                  |                  |                  | 2009-174         |                  |                  |                  |                  |
|  | Test Tap                                 |                  |                  | 2009-182         |                  |                  |                  |                  |
| <b>Screwless End Stops</b>   |  |                  |                  |                  |                  |                  |                  |                  |
|  | 6 mm Wide                                |                  |                  | 249-116          |                  |                  |                  |                  |
|  | 10 mm Wide                               |                  |                  | 249-117          |                  |                  |                  |                  |
| <b>Steel DIN Rail</b>  |  |                  |                  |                  |                  |                  |                  |                  |
|  | Solid, 2 m                               |                  |                  | 210-113          |                  |                  |                  |                  |
|  | Slotted, 2 m                             |                  |                  | 210-112          |                  |                  |                  |                  |
|  | Slotted, Tube of 40                      |                  |                  | 51266637         |                  |                  |                  |                  |
|  | Slotted, Crate of 500                    |                  |                  | 51266638         |                  |                  |                  |                  |
| <b>Wire Stripping Tools</b>  |  |                  |                  |                  |                  |                  |                  |                  |
|  | 34 - 8 AWG                               |                  |                  | 206-124          |                  |                  |                  |                  |
|  | 10 - 5 AWG                               |                  |                  | 206-125          |                  |                  |                  |                  |
| <b>Operating Tools, with Partially Insulated Shaft</b>                             |  |                  |                  |                  |                  |                  |                  |                  |
|  | 2.5 x 0.4 mm                             |                  |                  | 210-719          |                  |                  |                  |                  |
|  | 3.5 x 0.5 mm                             |                  |                  | 210-720          |                  |                  |                  |                  |
|  | 5.5 x 0.8 mm                             |                  |                  | 210-721          |                  |                  |                  |                  |
|  | Set of All of Above                      |                  |                  | 210-722          |                  |                  |                  |                  |

Accessories fit all TOPJOB®S terminal blocks (open tool slot, lever or push-button) in the same series. For example, 2002 Series accessories fit 2002, 2102 and 2202 Series terminal blocks




# TOPJOB®S TERMINAL BLOCKS


## Application Solutions

For more information visit – [www.wago.com/topjob-s/us](http://www.wago.com/topjob-s/us)


MULTI-LEVEL




TEST AND DISCONNECT



FUSE AND COMPONENT PLUG



DIODE AND LED



# CREATE ASSEMBLIES AND CLEARLY MARK CONTROL CABINETS

### smartDESIGNER

**smartDESIGNER** offers free online configuration of all electrical interconnect and automation components in full 3D. Create and save custom assemblies with all accessories and marking, before exporting into all standard CAD formats.

[configurator.wago.com](http://configurator.wago.com)

### smartPRINTER


The **smartPRINTER** is the industry's most versatile yet economical printer. Mark not only terminal blocks, relays, power supplies, and PLC's, but also quickly switch out the roll of material and mark control cabinet type plates, push-buttons, wire markers, and more.

[www.smartprinter.us](http://www.smartprinter.us)




Watch us go from 0 to 100 in 10 seconds  
[www.wago.us/smartprinter0to100](http://www.wago.us/smartprinter0to100)


CURRENT TRANSFORMER DISCONNECT




SENSOR/ACTUATOR



X-COM S PLUGGABLE WIRING SYSTEM



HIGH CURRENT – 310 AMPS



|  | Description                               | Item No. |   | Description                          | Item No. |
|--|---|----------|---|--------------------------------------|----------|
|  | WMB Inline Markers, On Reel, Plain, White |          |  | Thermal Transfer <i>smartPRINTER</i> |          |
|  | 5 ... 5.2 mm                              | 2009-115 |   | 330 dpi                              | 258-5000 |
|  | 4 ... 4.2 mm                              | 2009-114 |   | Print Width: 47 mm                   |          |
|  | 3.5 mm                                    | 2009-113 |   | Cutter                               | 258-5030 |
|  | Marking Strip, On Reel, Plain, White      |          |   | Thermal Transfer Ink Ribbon          | 258-5005 |
|  | 11 mm wide                                | 2009-110 |   |                                      |          |



WAGO Corporation  
N120 W19129 Freistadt Road  
Germantown, Wisconsin 53022  
Telephone: 800 / DIN-Rail (346-7245)  
Fax: 262 / 255-3232  
info.us@wago.com  
www.wago.us

WAGO Canada Inc.  
4145 North Service Rd., Unit 224  
Burlington, ON  
L7L 6A3  
Telephone: 888 / WAGO 221 (924-6221)  
info.ca@wago.com  
www.wago.ca

WAGO SA DE CV  
Carretera estatal 431 Km. 2+200. Lote 99 6  
Parque Industrial Tecnológico Innovación Querétaro  
El Marques, Qro. 76246  
Lada sin Costo: 01 800 288 WAGO (288-9246)  
Teléfono: 422 / 221-5946  
info.mx@wago.com  
www.wago.mx

WAGO is a registered trademark of WAGO Verwaltungsgesellschaft mbH.

"Copyright – WAGO Kontakttechnik GmbH & Co. KG – all rights reserved. The content and structure of the WAGO Websites, catalogs, videos, and other WAGO media are subject to copyright. The dissemination or changing of the content of these pages and videos is not permitted. Furthermore, the content may neither be copied nor made available to third parties for commercial purposes. Also subject to copyright are the images and videos that were made available to WAGO Kontakttechnik GmbH & Co. KG by third parties."