





[Home](#) > [Products](#) > [Cabled Power Connectors](#) > [Product Feature Selector](#) > [Product Details](#)

1744489-5 Product Details

[Share](#) | [Print](#) | [Email](#)


Economy Power Connectors

3.96 EP HDR ASY 05P NO PEG, GW

1744489-5

TE Internal Number: 1744489-5

Active

View 3D PDF

Product Highlights [View All](#)

- Economy Power Product Line
- Connector
- Wire-to-Board
- Applies To Printed Circuit Board
- 5 Positions

- [Pricing & Availability](#)
- [Request Sample](#)
- [Add to My Part List](#)
- [Buy Product through Distributor](#)

Feedback

[Documents](#) | [Features](#) | [Compliance](#)

Please Note:

Use the Product Drawing for all design activity

Product Type Features	
Product Line	Economy Power
Product Type [?]	Connector
Connector Type	Header
PCB Mounting Orientation	Vertical
PCB Mount Retention	Without
PCB Mount Alignment	Without
Sealed	No

Mechanical Attachment	
Mating Retention Type	Latch(ing)

Electrical Characteristics	
Contact - Rated Current (A)	7.5
Operating Voltage Reference	AC
Operating Voltage (VAC)	250

Termination Features	
Termination Method to PC Board	Through Hole - Solder

Dimensions	
Mating Post Length (mm [in])	7.70 [0.303]
PCB Thickness, Recommended (mm [in])	1.60 [0.063]
Tail Length (mm [in])	3.69 [0.145]
Length (X-Axis) (mm [in])	19.80 [0.7795]
Width (Z-Axis) (mm [in])	9.40 [0.370]
Profile Height (Y-Axis) (mm [in])	8.21 [0.323]

Body Features	
Selectively Loaded	No
Header Type	Unshrouded

Contact Features	
Contact Type	Pin
Contact Plating, Termination Area, Material	Tin
Contact Plating, Termination Area, Thickness (µm [µin])	0.003 [0.00012]
Contact Plating, Mating Area, Thickness (µm [µin])	0.003 [0.00012]
Contact Plating, Mating Area, Material	Tin
Contact Design	Square Post
Contact Base Material	Brass

Housing Features	
Centerline (mm [in]) [?]	3.96 [0.156]
Connector Style	Plug
Housing Color	Natural
Housing Material	Nylon - GF
Mating Alignment	With

Configuration Features	
Number of Positions [?]	5
Number of Rows	1
Tail Orientation	In-line

Industry Standards	
RoHS/ELV Compliance [?]	RoHS compliant, ELV compliant
Lead Free Solder Processes [?]	Wave solder capable to 240°C, Wave solder capable to 260°C, Wave solder capable to 265°C
RoHS/ELV Compliance History	Always was RoHS compliant
UL Flammability Rating	UL 94V-0

Environmental	
Operating Temperature (°C [°F])	-25 - +105 [-13 - +221]

Conditions for Usage	
Applies To	Printed Circuit Board
Glow Wire Rating	Glow Wire

Operation/Application	
Application Use	Wire-to-Board
Contact Transmits (Typical Application)	Power

Packaging Features	
Packaging Method	Bag/Box

Other	
Brand	TE Connectivity

Related Products

Not quite the product you're looking for?

[Find Similar Products](#)

[View Part in Product Feature Selector](#)

[Check for Tooling](#)

Corporate Information

- [About TE](#)
- [Investors](#)
- [News Room](#)
- [Supplier Portal](#)
- [Careers](#)
- [Terms & Conditions](#)
- [Privacy Policy](#)
- [Global Accessibility Statement](#)

Quick Links

- [Distributor Inventory](#)
- [Product Cross Reference](#)
- [Documents & Drawings](#)
- [Product Compliance Support Center](#)
- [Site Map](#)

Customer Support

- [Email or Chat With Us](#)
- [Find a Phone Number](#)
- [Knowledge Base](#)
- [Manage Your Account](#)

Keep Me Informed

