




What can we help you find?



Home > Products > Terminals & Splices > Product Feature Selector > Product Details

## 2-1703930-1 Product Details

Share | Print | Email



2-1703930-1

TE Internal Number: 2-1703930-1

Active

### Micro-Power & Power Quadlok System

Always EU RoHS/ELV Compliant (Statement of Compliance)

#### Product Highlights:

- Applies To Wire/Cable
- Contact
- Wire Range = 0.35 [28] mm [AWG]
- Wire/Cable Type = Discrete Wire
- Wire Type = Solid

[View all Features](#)

#### Quick Links

- ▶ Pricing & Availability
- ▶ Search for Tooling
- ▶ Product Feature Selector
- ▶ Contact Us About This Product

[Add to My Part List](#) | [Request Sample](#) | [Find Similar Products](#) | [Buy Product](#)

### Documentation & Additional Information

#### Product Drawings:

- [NanoMQS Buchsenkontakt SOCKET CONTACT \(PDF, English\)](#)

#### Catalog Pages/Data Sheets:

- None Available

#### Product Specifications:

- None Available

#### Application Specifications:

- [Allgemeine Crimpspezifikation / GENERAL CRIMP SPEC. \(PDF, German\)](#)

#### Instruction Sheets:

- None Available

#### CAD Files:

- None Available

#### Additional Information:

- [Product Line Information](#)

#### Related Products:

- [Tooling](#)

[List all Documents](#)

### Product Features (Please use the Product Drawing for all design activity)

#### Product Type Features:

- Product Type = Contact
- Wire/Cable Type = Discrete Wire
- Termination Method to Wire/Cable = Crimp
- Sealed = No
- Locking Lance = With
- Cable Type = FLR (Thin Walled Cable)

#### Body Features:

- Wire Range (mm [AWG]) = 0.35 [28]
- Wire Type = Solid

#### Contact Features:

- Contact Type = Receptacle
- Contact Style = Nano MQS
- Contact Finish = Tin
- Contact Shape = Straight

#### Configuration Features:

- GET 0.64 Connector System = No
- Dimple = Without

#### Industry Standards:

- RoHS/ELV Compliance = RoHS compliant, ELV compliant
- Lead Free Solder Processes = Not relevant for lead free process
- RoHS/ELV Compliance History = Always was RoHS compliant

#### Conditions for Usage:

- Applies To = Wire/Cable
- Accepts Wire Insulation Diameter, Range (mm [in]) = 1.20 [0.047]

#### Packaging Features:

- Packaging Method = Strip
- Packaging Quantity = 17,000

#### Other:

- Brand = TE Connectivity

### Corporate Information

- [About TE](#)
- [Investors](#)
- [News Room](#)
- [Supplier Portal](#)
- [Careers](#)
- [Terms & Conditions](#)
- [Privacy Policy](#)

### Quick Links

- [Distributor Inventory](#)
- [Product Cross Reference](#)
- [Documents & Drawings](#)
- [Product Compliance Support Center](#)
- [Site Map](#)

### Customer Support

- [Email or Chat With Us](#)
- [Find a Phone Number](#)
- [Knowledge Base](#)
- [Manage Your Account](#)

### Keep Me Informed

Receive TE News, Events & Technology Updates

Enter your email address

