

# POWER SUPPLIES S-30 Series



## Features

- Slim design
- High efficiency, up to 90%
- Low no load power consumption
- Class II, wide range input (85-265VAC)
- Protections: overheating, short circuit, overload, overvoltage, supply voltage interruption
- LED indicator for power on
- DIN rail mountable



## Technical data

MODEL		S-30-05	S-30-10	S-30-12	S-30-24
OUTPUT	DC VOLTAGE	5V	10V	12V	24V
	RATED CURRENT	6A	3A	2.5A	1.3A
	VOLTAGE TOLERANCE	+ - 2%	+ - 2%	+ - 2%	+ - 2%
	RATED POWER	30W	30W	30W	30W
	RIPPLE & NOISE	80mVp-p	120mVp-p	120mVp-p	150mVp-p

INPUT	VOLTAGE RANGE	85 ~ 265VAC 90 ~ 385VDC
	FREQUENCY RANGE	47 ~ 63Hz
	EFFICIENCY	90%
	AC CURRENT	0.88A/115VAC 0.48/230VAC
WORKING TEMP. / HUMIDITY		-20 ~ 60°C / 20 ~ 90% RH

## Dimensions

