Effective December 2015 Supersedes April 2014

BAF 13/32" x 1-1/2" 250Vac fast-acting supplemental fuses



1/4 to 30A

Catalog symbol – color code

• BAF

• Green (250Vac max, 1/4 to 30A)

Description:

Fast-acting, supplemental fuse.

For superior protection, Eaton recommends upgrading to Bussmann series Low-Peak[™] Class CC fuses. See data sheet No. 1023.

Specifications:

Ratings

	Interrupting rating at system voltage		Agency information	
Fuse amp range	250 Vac	125 Vac	UL®	CSA [®]
1/4 to 1	35A	10kA	-	х
1-1/2 to 2-1/2	100A	10kA	-	Х
3	100A	10kA	Х	х
4 to 10	200A	10kA	Х	х
12 to 15	750A	10kA	Х	х
20 to 30	200A	10kA	-	-

Agency information

· CE


- UL Listed, Std. 248-14, 250Vac (3 to 15A) Guide JDYX, File E19180
- CSA Certified, 250Vac (1/4 to 15A) Class 1422-01, File 53787

Catalog numbers (amps					
BAF-1/4	BAF-1-8/10	BAF-6	BAF-12		
BAF-1/2	BAF-2	BAF-6-1/4	BAF-15		
BAF-6/10	BAF-2-1/2	BAF-7	BAF-20		
BAF-8/10	BAF-3	BAF-8	BAF-25		
BAF-1	BAF-4	BAF-9	BAF-30		
BAF-1-1/2	BAF-5	BAF-10			

Carton quantity

Amps	Qty.	
1/4 to 30	10	

Dimensions - in (mm):



BUSSMANN

Features:

- Color coded green for 250Vac maximum voltage rating
- Fiber tube construction
- Nickel-plated endcaps.

Typical applications


- · General purpose circuits
- · Lighting circuit protection
- Meter circuits

Recommended fuse blocks/fuse holders

Catalog Description		Data sheet				
symbol	Blocks	No.				
ВММ	1-, 2- and 3-pole modular blocks with optional covers	10235				
DIN-Rail holders / switches						
CCP30M	1-, 2- and 3-pole switch	1157				
CHM	1-, 2- and 3-pole	3185				
Optima NG	3-pole protection module	1109				
Optima	3-pole holder	1102				
Optima	3-pole holder + switch	1103				
Panel mount holders						
HPM and HPM-D	1-pole holder	2112				
HPC-D	1-pole holder	2109				
HPS2	2-pole holder	2140				
HPF, HPF-C and HPF-WT	1-pole holder	2114				
HPS	1-pole holder	2113				
HPG and HPD	1-pole holder	2108				
In-line holders						
HEB	1-pole holder	2127				
HEX	2-pole holder	2126				
Fuseclips						
1A3400, 5956 and 5960	PCB fuseclips	2132				
Fuse covers						
CVR(I)-CCM(-QC)	Finger-safe fuse cover	10235				



Time-current characteristic curves - total clear:



The only controlled copy of this data sheet is the electronic read-only version located on the Eaton network drive. All other copies of this document are by definition uncontrolled. This bulletin is intended to clearly present comprehensive product data and provide technical information that will help the end user with design applications. Eaton reserves the right, without notice, to change design or construction of any products and to discontinue or limit distribution of any products. Eaton also reserves the right to change or update, without notice, any technical information contained in this bulletin. Once a product has been selected, it should be tested by the user in all possible applications.

Eaton 1000 Eaton Boulevard Cleveland, OH 44122 United States Eaton.com

Bussmann Division 114 Old State Road Ellisville, MO 63021 United States Eaton.com/bussmannseries

© 2015 Eaton All Rights Reserved Printed in USA Publication No. 1011 – BU-SB14288 December 2015 Eaton, Bussmann and Low-Peak are valuable trademarks of Eaton in the US and other countries. You are not permitted to use the Eaton trademarks without prior written consent of Eaton.

CSA is a registered trademark of the Canadian Standards Group. UL is a registered trademark of the Underwriters Laboratories, Inc. For Eaton's Bussmann series product information, call **1-855-287-7626** or visit: **Eaton.com/bussmannseries**

Follow us on social media to get the latest product and support information.



Powering Business Worldwide

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Eaton:

 BAF-9
 BAF-12
 BAF-5
 BAF-1/2
 BAF-8
 BAF-2-1/2
 BAF-3
 BAF-4
 BAF-6-1/4
 BAF-1
 BAF-7
 BAF-25
 BAF-6

 BAF-1/2
 BAF-20
 BAF-2
 BAF-6/10
 BAF-1/4
 BAF-1-8/10
 BAF-8/10
 BAF-8/10