



+ CONNECTORS

CONNECTOR HOUSINGS



✓ Active

TE CONNECTIVITY (TE)

JUN-POW-TIM GEH 9P

AMP | Junior Power Timer , Timer Connector System

1-967621-1

TE Internal Number: 1-967621-1

EU RoHS Compliant

EU ELV Compliant

Connector System Wire-to-Wire

Connector Style Housing for female terminals

Mating Tab Width 2.8 mm [.11 in]

Centerline (Pitch) (in) .197

Number of Positions 9

↓ **PRODUCT DRAWING**
English

↓ **3D PDF**

DOCUMENTATION

Product Drawings

JUNIOR POWER TIMER HOUSING, 9POS.

PDF (TIFF AVAILABLE)

English

PRODUCT GROUP DRAWING FOR: JUNIOR POWER TIMER HSG., 6-21POS. AND SECONDARY LOCKING DEVICE

PDF

English

CAD Files

Customer View Model

3D_IGS.ZIP

English

Customer View Model

3D_STP.ZIP

English

Customer View Model

2D_DXF.ZIP

English

3D PDF

PDF

English

FEATURES



Please review product documents or [contact us](#) for the latest agency approval information.

Please Note: Use the Product Drawing for all design activity.

Product Type Features

Connector System Wire-to-Wire

Connector Style Housing for female terminals

Sealed No

Hybrid Connector No

Primary Locking Feature On the terminal

Strain Relief No

Configuration Features

Number of Positions 9

Number of Rows 3

Body Features

Color Yellow

Connector Code A

Body Material PBT GF

Contact Features

Mating Tab Width 2.8 mm [.11 in]

Mechanical Attachment

Terminal Position Assurance Yes

Polarized Yes

Housing Features

Centerline (Pitch) (in) .197

Pitch (mm) 5

Dimensions

Width 16.2 mm [.638 in]

Height 26.5 mm [1.043 in]

Length 16.2 mm [.638 in]

Operation/Application

Circuit Application Signal

Packaging Features

Packaging Method Carton

Other

Connector Position Assurance Capable No

Serviceable No

Statement of Compliance

Statement of Compliance

PDF
