



**+** CONNECTORS

CONNECTOR HOUSINGS



✓ Active

TE CONNECTIVITY (TE)

## JUN-POW-TIM HOUSING 18POS

AMP | Junior Power Timer , Timer Connector System

1-967624-1

TE Internal Number: 1-967624-1

EU RoHS Compliant

EU ELV Compliant

**Connector System** Wire-to-Wire

**Connector Style** Housing for female terminals

**Mating Tab Width** 2.8 mm [.11 in]

**Centerline (Pitch) (in)** .197

**Number of Positions** 18

↓ **PRODUCT DRAWING**  
English

↓ **3D PDF**

### DOCUMENTATION

Product Drawings

**JUNIOR POWER TIMER HOUSING, 18POS. Junior Power Timer Gehaeuse, 18pol.**

PDF

English

**PRODUCT GROUP DRAWING FOR: JUNIOR POWER TIMER HSG., 6-21POS. AND SECONDARY LOCKING DEVICE**

PDF

English

CAD Files

**Customer View Model**

3D\_IGS.ZIP

English

**Customer View Model**

3D\_STP.ZIP

English

### Customer View Model

2D\_DXF.ZIP

English

### 3D PDF

PDF

English

## FEATURES



Please review product documents or [contact us](#) for the latest agency approval information.

Please Note: Use the Product Drawing for all design activity.

### Product Type Features

**Connector System** Wire-to-Wire

**Connector Style** Housing for female terminals

**Sealed** No

**Hybrid Connector** No

**Primary Locking Feature** On the terminal

**Strain Relief** No

### Configuration Features

**Number of Positions** 18

**Number of Rows** 3

### Body Features

**Connector Code** A

**Body Material** PBT GF

**Color** Gray

### Contact Features

**Mating Tab Width** 2.8 mm [.11 in]

### Mechanical Attachment

**Terminal Position Assurance** Yes

**Polarized** Yes

### Housing Features

**Centerline (Pitch) (in)** .197

**Pitch (mm)** 5

### Dimensions

**Length** 31.2 mm [ 1.228 in ]

**Height** 26.5 mm [ 1.043 in ]

Operation/Application

**Circuit Application** Signal

---

Packaging Features

**Packaging Method** Carton

---

Other

**Connector Position Assurance Capable** No

**Serviceable** No

Statement of Compliance

**Statement of Compliance**

PDF

---