



● SPECIFICATIONS

PARAMETER	VALUE
FREQUENCY RANGE	32.768 KHz
FREQUENCY TOLERANCE AT 25°C	±20 PPM MAXIMUM
TURNOVER TEMPERATURE	+25 ±5°C
TEMPERATURE COEFFICIENT	-0.04 x 10 <sup>-6</sup> / °C <sup>2</sup> MAX
SHUNT CAPACITANCE	1.5 pF TYPICAL
LOAD CAPACITANCE	6 pF
EQUIVALENT SERIES RESISTANCE	65 KΩ
DRIVE LEVEL	0.5 μW MAXIMUM
AGING	±3 PPM FIRST YEAR MAXIMUM
OPERATING TEMPERATURE RANGE	-40°C TO +85°C EXTENDED
STORAGE TEMPERATURE RANGE	-55°C TO +125°C
MOTIONAL CAPACITANCE	6.7 fF TYPICAL
INSULATION RESISTANCE	500 MΩ MAXIMUM

● MECHANICAL SPECIFICATION



● CARRIER TAPE DIMENSIONS



NOTE: REFER TO EIA-481 FOR DIMENSIONS

● PACKAGING

330 mm REEL DIAMETER  
 8 mm TAPE WIDTH, 4 mm PITCH  
 QUANTITY: 3000 PIECES PER REEL

IN ACCORDANCE WITH EIA-481

● REFLOW PROFILE



Reflow profile		
Temperature Min Preheat	$T_{SMIN}$	125°C
Temperature Max Preheat	$T_{SMAX}$	150°C
Time ( $T_{SMIN}$ to $T_{SMAX}$ )	$t_s$	30-60 sec.
Temperature	$T_L$	217°C
Peak Temperature	$T_P$	230°C
Ramp-up rate	$R_{UP}$	3°C/sec max.
Ramp-down rate	$R_{DOWN}$	6°C/sec max.
Time within 5°C of Peak Temperature	$t_p$	10 sec.
Time $t_{[25^\circ C]}$ to Peak Temperature	$t_{[25^\circ C]}$ to Peak	120 sec.
Time	$t_L$	60-150 sec.

● ENVIRONMENTAL

PARAMETER	VALUE
MOISTURE SENSITIVITY LEVEL	1
RoHS-2	6/6 COMPLIANT
REACH SVHC	COMPLIANT
HALOGEN-FREE	COMPLIANT
ESD CLASSIFICATION LEVEL	N/A
TERMINATION FINISH	Au



## ● MARKING

R3x6ym

x – Internal Production ID code

y – Year code

m – Month code

YEAR CODE	
Year	Code
2011	1
2012	2
2013	3
2014	4
2015	5
2016	6
2017	7
2018	8
2019	9

ALPHA MONTH CODE TABLE	
Month	Code
January	A
February	B
March	C
April	D
May	E
June	F
July	G
August	H
September	J
October	K
November	L
December	M

## ● APPROVAL

Drawn By:	KJackson, January 12, 2015
Approved By:	KJackson, January 12, 2015
Revision:	A, Initial Release