

HD16/14.FF5.21.3



Products Low Voltage Products and Systems Connection Devices Terminal Blocks Railway Terminal Blocks

General Information

| | |
|-------------------------------|---|
| Extended Product Type: | HD16/14.FF5.21.3 |
| Product ID: | 1SNA295012R1700 |
| EAN: | 3472592950129 |
| Catalog Description: | HD16/14.FF5.21.3 - Stud terminal blocks - 2 studs M5 - Beige |
| Long Description: | - 2 stud terminals M5 x 19.5 mm 0.768 in, - Equipment: self locking nut + spring washer + washer, - 18 mm 0.709 in spacing adding SCH6 or INH3, - Two jumpering options: 14 mm 0.551 in spacing with BJH14 and 18 mm 0.709 in spacing (adding INH3) with BJH18, - NF F 61-017 designation: BE0018-FF5 (1SNA295012R1700 + SCH6 or INH3). |

Additional Information

| | |
|---|--|
| ABB Industrial IT Suite: | Control IT |
| Ambient Air Temperature: | Operation -55 ... +110 °C Storage -55 ... +110 °C |
| Ambient Temperature: | -5 ... +40 °C |
| Color: | Beige |
| Connecting Capacity UL/CSA: | Stranded 6 AWG |
| Connecting Capacity Main Circuit: | Stud / Flexible 1x 0.5 ... 16 mm ² |
| Connection Type: | Stud |
| Country of Origin: | France (FR) |
| Customs Tariff Number: | 85369010 |
| Data Sheet, Technical Information: | 1SNC001003C0302 |
| Declaration of Conformity - CE: | 1SND225049U1000 |
| EAC Certificate: | 1SND161009A1100 |
| EAN: | 3472592950129 |
| ETIM 4: | EC000897 - Feed-through terminal block |
| ETIM 5: | EC000897 - Feed-through terminal block |
| ETIM 6: | EC000897 - Feed-through terminal block |
| Environmental Information: | 1SND220039E1002 |
| Function: | Feed-through |
| IT Publishing Status: | Level 0 - Information enabled |
| Industrial IT Certification Level: | 0 |
| Instructions and Manuals: | 1SNC001003C0302 |
| Insulation Material: | Polyamide |
| Invoice Description: | HD16/14.FF5.21.3 - Stud terminal blocks - 2 studs M5 - Beige |
| Minimum Order Quantity: | 25 piece |
| Mounting Type: | The use of a jumper bar requires to use a spacer instead of a circuit separator. |
| Mounting on DIN Rail: | Type 2 (21.8 x 8.2 mm Mounting Rail) acc. to NFC 93461 TH35-7.5 (35 x 7.5 mm Mounting Rail) acc. to IEC 60715 TH35-15 (35 x 15 mm Mounting Rail) acc. to IEC 60715 |
| Number of Connections: | 2 |
| Number of Levels: | 1 |
| Object Classification Code: | X |
| Order Multiple: | 25 piece |
| Package Level 1 EAN: | 3472592950129 |
| Package Level 1 Gross Weight: | 0.6 kg |
| Package Level 1 Height: | 51 mm |

| | |
|----------------------------------|---|
| Package Level 1 Length: | 250 mm |
| Package Level 1 Units: | 25 piece |
| Package Level 1 Width: | 86 mm |
| Package Level 2 Height: | 300 mm |
| Package Level 2 Length: | 500 mm |
| Package Level 2 Units: | 600 piece |
| Package Level 2 Width: | 300 mm |
| Package Level 3 Units: | 14400 piece |
| Product Main Type: | HD16/14.FF5 |
| Product Name: | Terminal Block |
| Product Net Depth: | 36 mm |
| Product Net Height: | 54 mm |
| Product Net Weight: | 24 g |
| Product Net Width: | 14 mm |
| Product Packing Type: | Box |
| Rated Cross-Section: | 16 mm ² |
| Rated Current (I _n): | Main Circuit 71 A |
| RoHS Information: | 1SND230014F0201 |
| Selling Unit of Measure: | piece |
| Short Description: | beige Railway Terminal Blocks HD16/14.FF5 |
| Spacing: | 14 mm |
| Sub-Function: | 2 studs M5 |
| Tightening Torque: | acc. IEC 60947-1 2.5 N·m |
| Number of Potentials: | 1 |

