

Search within category **GO**



PLT1M-M76

Pan-Ty® locking cable tie, miniature cross section, 4.0 (102mm) length, TEFZEL, aqua, 1000 pc.

BUY NOW

DESIGN / INSTALL

- Specs**
- Packaging Details
- Tools
- Documents

★ Add to Favorites Add to BOM

Material	TEFZEL
Color	Aqua
Minimum Loop Tensile Strength (N)	80
Minimum Loop Tensile Strength (lb)	18
Environment	Indoor
Maximum Installation Temperature (°F)	32
Minimum Operating Temperature (°C)	-60
Minimum Operating Temperature (°F)	-76
Maximum Operating Temperature (°C)	170
Maximum Operating Temperature (°F)	338
Cross Section	Miniature
Locking Style	Locking
Continuous Use Temperature Range	-76°F (-60°C) - 338°F (170°C)
Plenum-Rated	No
Tool	GTS-E, GS2B, PTS, PPTS, STS2
Thickness In (mm)	0.04 (1.1)
Bundle Diameter Range In. (mm)	0.13 (3.3) - 0.87 (22.0)
CE Compliant	Yes
CSA Certified	Yes
Mil. Std. Part Number	MS3367-4-15
UL 62275 Compliant (Type 1, 11)	Yes
UL 62275 Compliant (Type 2, 21)	No
UL Listed (File #E56854)	No
UL Recognized (File #E56854)	Yes
Application	Radiation Resistant
Material Flammability Rating	UL 94V-0
Maximum Bundle Diameter (In.)	0.87
Operating Temperature	-76°F (-60°C) - 338°F (170°C)

Part Features

One-piece locking wedge for consistent performance and reliability. Low thread force and high loop tensile strength.

Thickness (mm)	1.1
Width In (mm)	0.09 (2.5)
RoHS Compliancy Status	Compliant
Min. Order Qty.	1,000

[LEGAL INFORMATION](#) | [PRIVACY POLICY](#) | [CONTACT US](#) | [SITE MAP](#) | [WHERE TO BUY](#) | [JOBS](#) | [UNSUBSCRIBE](#)