

### **DEMO MANUAL DC1817B**

## LT3798 Isolated No Opto-Coupler Flyback Controller with PFC

### DESCRIPTION

Demonstration circuit 1817B is an off-line isolated flyback converter featuring the LT®3798. The demo board provides a single constant-voltage output of 24V at 2A. It is optimized to operate over a wide AC input voltage range (90VAC to 265VAC, 47Hz to 63Hz). Output voltage accuracy stays within ±5% over the whole input voltage and load range. It provides a high power factor (>0.95) enabling the design to be used worldwide. It is also designed to comply with the IEC 61000-3-2 Class D harmonics standard and the EN55015B conducted EMI standard.

The LT3798 controls an isolated flyback converter in boundary mode, suitable for applications with voltage or current regulation. Its novel sensing scheme delivers a well regulated output voltage or current to the secondary side without the use of an opto-coupler.

The LT3798 is available in a low profile, thermally enhanced 16-lead MSOP package.

The LT3798 data sheet gives a complete description of the part, operation and application information. The data sheet must be read in conjunction with this quick start guide for demo circuit 1817B.

Design files for this circuit board are available at http://www.linear.com/demo/DC1817B

 $\sigma$ , LT, LTC, LTM, Linear Technology and the Linear logo are registered trademarks of Linear Technology Corporation. All other trademarks are the property of their respective owners.

### **PERFORMANCE SUMMARY** (T<sub>A</sub> = 25°C)

PARAMETER	CONDITIONS	MIN	TYP	MAX
Input Range	Line Frequency, 47Hz to 63Hz	90VAC	120VAC	265VAC
Output Voltage			24V	
Efficiency	90VAC to 265VAC, 2A I <sub>OUT</sub>		87%	
Power Factor	24V/2A Output, 90VAC to 265VAC	0.99	0.98	0.95



### **QUICK START PROCEDURE**

#### **IMPORTANT NOTE TO CUSTOMERS:**

HIGH VOLTAGES ARE PRESENT ON THE DEMO CIRCUIT, AND CAN LEAD TO LETHAL INJURIES TO HUMAN BODY. ONLY QUALIFIED PERSONNEL SHOULD OPERATE IT. IT IS STRONGLY RECOMMENDED TO USE SAFETY GLASSES AND AN ISOLATION TRANSFORMER.

NOTE: Improper components replacement on the demo circuit can cause performance deteriorations, circuit malfunction, property damage, and even life threatening injuries. Contact Linear Technology applications engineers for proper component replacement.

Demonstration circuit 1817B is easy to set up to evaluate the performance of the LT3798. Refer to Figure 1 for proper measurement equipment setup and follow this procedure:

- 1. Connect an adjustable load between + and output terminals.
- 2. With power off, connect the input power supply to Line (L) input and Neutral (N) input.
- 3. Turn on the power at the input.

NOTE. Make sure that the input voltage does not exceed the maximum input voltage (265VAC).

4. Check for the proper output voltage.

Once the proper output voltage is established, adjust the input voltage and/or the load and observe the output voltage regulation, efficiency, power factor and other parameters.




Figure 1. Proper Measurement Equipment Setup



### **QUICK START PROCEDURE**




Figure 2. Efficiency vs Input Voltage




Figure 3. V<sub>OUT</sub> vs Load Current




Figure 4. Power Factor vs Input Voltage

#### **Input Line Voltage and Current**

I<sub>IN(AC)</sub> (1A/DIV)

V<sub>IN(AC)</sub> (200V/DIV)




Figure 5. 120VAC (PF = 0.99)




Figure 6. 230VAC (PF = 0.97)

dc1817bfa



### **QUICK START PROCEDURE**

#### **Switch Node Voltage**

 $\mathsf{V}_{\mathsf{SW}}$ (100V/DIV)




Figure 7. 120VAC (V<sub>SW</sub> = 450V)




Figure 8. 230VAC (V<sub>SW</sub> = 630V)

#### **Output Current and Switch Node Voltage During Output Short**




Figure 9. 120VAC



 $V_{OUT}$ (1V/DIV)




Figure 10. 230VAC




Figure 11. Output Ripple at 120VAC, 2A Load




Figure 12. Output Ripple at 230VAC, 2A Load

dc1817bfa

### **PARTS LIST**

ITEM	QTY	REFERENCE	PART DESCRIPTION	MANUFACTURER/PART NUMBER			
Required	Required Circuit Components						
1	1	B1	RECTIFIER, BRIDGE 600V 0.8A	DIODES INC. HD06-T			
2	1	CAC1	CAP, 0.1µF 20% 250V/275VAC ECQ-UL	PANASONIC, ECQUAAF104M			
3	1	C2	CAP, FILM, 0.22μF 20% 400V	PANASONIC ECQE4224KF			
4	1	C3	CAP, 10μF 20% 50V ALUM	RUBYCON 50YXJ10M 5X11			
5	1	C6	CAP, 0805 0.1µF 10% 50V X7R	TDK, C2012X7R1H104K			
6	1	C7	CAP, 0805 2.2µF 10% 50V X5R	TDK, C2012X5R1H225K			
7	1	C8	CAP, 0805 4.7μF 20% 16V X5R	AVX 0805YD475MAT2A			
8	2	C10, C11	CAP, 1000μF 20% 35V ELEC	NIPPON CHEMI-CON ELXV350ETD102MK30S			
9	1	C13	CAP, 1210 2.2nF, 5% 630V U2J	MURATA, GRM32A7U2J222JW31D			
10	1	C20	CAP, 2.2nF 20% 400V, Y5U TYPE "Y1"	VISHAY, 440LD22-R			
11	2	C12, C21	CAP, 0805 22pF ±0.25pF 50V NP0	AVX, 08055A220CAT2A			
12	2	C23, C25	CAP, 1210 10μF 20% 35V X5R	MURATA, GRM32ER7YA106KA12L			
13	1	C24	CAP, 1206 47pF 10% 630V NPO	AVX, 1206CA470KAT1A			
14	1	D1	DIODE, ULTRA FAST RECTIFIER	CENTRAL SEMI, CMR1U-10M			
15	1	D2	DIODE, FAST SWITCHING	DIODES INC, BAV20W-7-F			
16	1	D5	DIODE, SUPER BARRIER RECIFIER 20A	DIODES INC SBR20A200CTB			
17	1	D8	DIODE, SWITCH 100V 400MW SOD123	DIODES INC, 1N4148W-7-F			
18	1	F1	FUSE, 2.5A, FAST ACTING	COOPER BUSSMAN, SS-5F-3.15A			
19	1	L2	CHOKE, D CODE DOUBLE CHOKE	TDK/EPCOS, B82731H2701A030			
20	1	L1	INDUCTOR, 1mH, 0.78A RADIAL 1000µH	TDK, TSL1315RA-102JR78-PF			
21	1	Q1	MOSFET, N-CH 650V 21A D2PAK	INFINEON, IPB60R165CP			
22	2	R1, R2	RES, 1206 100k 1% 1/4W	VISHAY CRCW1206100KFKEA			
23	1	R3	RES, 0805 100k 1% 1/8W	VISHAY, CRCW0805100KFKEA			
24	1	R4	RES, 0805 5.49k 1% 1/8W	VISHAY, CRCW08055K49FKEA			
25	1	R5	RES, 0805 68Ω 5% 1/8W	VISHAY, CRCW080568R0JKEA			
26	1	R25	RES, 0805 20Ω 1% 1/8W	VISHAY, CRCW080520R0FKEA			
27	1	R7	RES, 0805 33k 5% 1/8W	VISHAY, CRCW080533K0JNEA			
28	1	R8	RES, 0.03Ω 1/4W 1% 1206 SMD	VISHAY, WSL1206R0300FEA			
29	1	R9	RES, 1210 510Ω 5% 1/2W	VISHAY, CRCW1210510RJNEA			
30	2	R10, R11	RES, 1206 499k 1% 1/4W	VISHAY CRCW1206499KFKEA			
31	1	R18	RES, 0805 10k 1% 1/8W	VISHAY, CRCW080510K0FKEA			
32	1	R19	RES, 0805 40.2k 1% 1/8W	VISHAY, CRCW080540K2FKEA			
33	1	R20	RES, 0805 31.6k 1% 1/8W	VISHAY, CRCW080531K6FKEA			
34	1	R37	RES, 0805 0Ω 5% 1/8W	VISHAY, CRCW08050000Z0EA			
35	2	R27, R28	RES, 1206 510Ω 5% 1/4W	VISHAY CRCW1206510KJKEA			
36	1	R32	RES, 1210 51k 5% 1/2W	VISHAY, CRCW121051KOJNEA			
37	1	R35	RES, 0805 2.4M 5% 1/8W	VISHAY, CRCW08052M40JNEA			
38	1	R36	RES, 0805 301k 1% 1/8W	VISHAY, CRCW0805301KFKEA			
39	1	R38	RES, 0805 24.9k 1% 1/8W	VISHAY, CRCW080524K9FKEA			



# DEMO MANUAL DC1817B

## **PARTS LIST**

ITEM	QTY	REFERENCE	PART DESCRIPTION	MANUFACTURER/PART NUMBER		
40	1	T1	XFMR, FLYBACK	WÜRTH ELECTONIK, 750811248		
41	1	U1	IC, ISOLATED FLYBACK CONTROLLER	LINEAR TECHNOLOGY LT3798EMSE#PBF		
42	1	V1	VARISTOR, 320V RMS 13.5MM RADIAL	VISHAY VDRS10P320BSE		
Additional Circuit Components						
1	0	R23	RES, 0805, OPTION	OPTION		
Hardware/Components (For Demo Board Only)						
1	2	J1, J2	TERMINAL BLOCK, 2 POSITION	WEIDMULLER, 1715250000		
2	4	MH1 TO MH4	STAND-OFF, NYLON, 0.25"	KEYSTONE, 8831 (SNAP-ON)		

### **SCHEMATIC DIAGRAM**




Figure 13. DC1817B Demo Circuit Schematic

dc1817bfa

### DEMO MANUAL DC1817B

#### DEMONSTRATION BOARD IMPORTANT NOTICE

Linear Technology Corporation (LTC) provides the enclosed product(s) under the following AS IS conditions:

This demonstration board (DEMO BOARD) kit being sold or provided by Linear Technology is intended for use for **ENGINEERING DEVELOPMENT OR EVALUATION PURPOSES ONLY** and is not provided by LTC for commercial use. As such, the DEMO BOARD herein may not be complete in terms of required design-, marketing-, and/or manufacturing-related protective considerations, including but not limited to product safety measures typically found in finished commercial goods. As a prototype, this product does not fall within the scope of the European Union directive on electromagnetic compatibility and therefore may or may not meet the technical requirements of the directive, or other regulations.

If this evaluation kit does not meet the specifications recited in the DEMO BOARD manual the kit may be returned within 30 days from the date of delivery for a full refund. THE FOREGOING WARRANTY IS THE EXCLUSIVE WARRANTY MADE BY THE SELLER TO BUYER AND IS IN LIEU OF ALL OTHER WARRANTIES, EXPRESSED, IMPLIED, OR STATUTORY, INCLUDING ANY WARRANTY OF MERCHANTABILITY OR FITNESS FOR ANY PARTICULAR PURPOSE. EXCEPT TO THE EXTENT OF THIS INDEMNITY, NEITHER PARTY SHALL BE LIABLE TO THE OTHER FOR ANY INDIRECT, SPECIAL, INCIDENTAL, OR CONSEQUENTIAL DAMAGES.

The user assumes all responsibility and liability for proper and safe handling of the goods. Further, the user releases LTC from all claims arising from the handling or use of the goods. Due to the open construction of the product, it is the user's responsibility to take any and all appropriate precautions with regard to electrostatic discharge. Also be aware that the products herein may not be regulatory compliant or agency certified (FCC, UL, CE, etc.).

No License is granted under any patent right or other intellectual property whatsoever. LTC assumes no liability for applications assistance, customer product design, software performance, or infringement of patents or any other intellectual property rights of any kind.

LTC currently services a variety of customers for products around the world, and therefore this transaction is not exclusive.

**Please read the DEMO BOARD manual prior to handling the product**. Persons handling this product must have electronics training and observe good laboratory practice standards. **Common sense is encouraged**.

This notice contains important safety information about temperatures and voltages. For further safety concerns, please contact a LTC application engineer.

Mailing Address:

Linear Technology 1630 McCarthy Blvd. Milpitas, CA 95035

Copyright © 2004, Linear Technology Corporation



## **Mouser Electronics**

**Authorized Distributor** 

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Analog Devices Inc.:

DC1817B