


PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [2026542021](#)
Status: **Active**
Overview: Pico-EZmate and Pico-EZmate Slim Wire-to-Board Connector Systems
Description: Pico-EZmate Slim Receptacle Housing, Friction Lock, 2 Circuits, Black

Documents:

3D Model	Application Specification 2026540000-A00 (PDF)
3D Model (PDF)	Packaging Specification 2026549200-200 (PDF)
Drawing (PDF)	RoHS Certificate of Compliance (PDF)
Product Specification 2026540000-000 (PDF)	Product Literature (PDF)



General

Product Family	Crimp Housings
Series	202654
Application	Signal, Wire-to-Board
Overview	Pico-EZmate and Pico-EZmate Slim Wire-to-Board Connector Systems
Product Name	Pico-EZmate Slim
UPC	191128182041

Physical

Circuits (maximum)	2
Color - Resin	Black
Gender	Receptacle
Glow-Wire Capable	No
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Resin	Nylon
Net Weight	8.160/mg
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	1.20mm
Pitch - Termination Interface	1.20mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-25° to +85°C

Material Info

Reference - Drawing Numbers

Application Specification	2026540000-A00
Packaging Specification	2026549200-200
Product Specification	2026540000-000
Sales Drawing	2026540000-000

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
ECHA_01_2020 (16
January 2020

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[202654](#) Series

Mates With

Pico-EZmate Slim Header [202656](#)

Use With

Pico-EZmate Slim Crimp Terminal
[2026555000](#)