



+ RELAYS, CONTACTORS & SWITCHES

STANDARD POWER RELAYS



✓ Active

TE CONNECTIVITY (TE)

EW60-1A3-BL12D04,00000

EW60-1A3-BL12D04,00000

TE Internal Number: 2071366-1

EU RoHS Compliant

EU ELV Compliant

Contact Current Rating (A) 60

Coil Power Rating (DC) (mW) 1500

Insulation Clearance Class 5 – 8

Insulation Creepage Class 8

Terminal Type PCB-THT

↓ 3D PDF

## DOCUMENTATION

CAD Files

**3D PDF**

PDF

3D

**Customer View Model**

2D\_DXF.ZIP

English

**Customer View Model**

3D\_IGS.ZIP

English

**Customer View Model**

3D\_STP.ZIP

English

Catalog Pages/Data Sheets

## Lighting Relays Guide

PDF

English

## EW60 Relay Flyer

PDF

English

## EW60 Relay Datasheet

PDF

English

---

Product Specifications

Product Specification

## Definitions Relays

PDF

English

---

## FEATURES



Please review product documents or [contact us](#) for the latest agency approval information.

---

Product Type Features

**Product Type** Relay

**Relay Type** PCB Relay

---

Electrical Characteristics

**Coil Power Rating (DC) (mW)** 1500

**Insulation Creepage Class** 8

**Coil Voltage Rating (VDC)** 12

**Contact Voltage Rating (VAC)** 277

**Coil Magnetic System** Bistable, 1 Coil, Polarized

**Coil Special Features** Magnetic Latching

---

Contact Features

**Contact Current Rating (A)** 60

**Terminal Type** PCB-THT

**Contact Arrangement** 1 Form A (NO)

**Contact Number of Poles** 1

**Contact Material** AgSnO2

---

Dimensions

**Insulation Clearance Class** 5 – 8

---

Usage Conditions

**Environmental Category of Protection** RTI

Statement of Compliance

## Statement of Compliance

PDF

---