

Side element - UM108-SEFE/R - 2959683

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)

Side element with foot, 5 mm wide (right), for mounting on NS 32 or NS 35/7.5. PCB width: 107.5 mm



Your advantages

- ✓ Lateral elements with potential ground contact available from the PCB to the DIN rail (EMC)
- ✓ Fast assembly on standard NS 35 or NS 32 DIN rails
- ✓ Flexible size and shape
- ✓ Wide range of options for external conductor connection
- ✓ Inexpensive as a result of reducing the number of separate housing parts
- ✓ High degree of mechanical stability by screwing the lateral elements to the profile
- ✓ The modules can be marked with Phoenix Contact marking material using the marking grooves in the press-drawn section



Key Commercial Data

Packing unit	1 pc
Minimum order quantity	10 pc
GTIN	
GTIN	4017918086336
Weight per Piece (excluding packing)	8.990 g
Custom tariff number	85389099
Country of origin	Poland

Technical data

Product properties

Brief article description	Side element
Type	UM108-SEFE/R

Side element - UM108-SEFE/R - 2959683

Technical data

Product properties

Order No.	2959683
Housing type	Press-drawn section housings
Type	Lateral element (right)

Dimensions

Profile PCB width (selectable):	108 mm [UM108]
---------------------------------	----------------

Material specifications

Housing material	PA
Color (RAL)	green
Flammability rating according to UL 94	V0

Packaging specifications


Pieces per package	10
Denomination packing units	Pcs.

Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

Drawings

Dimensional drawing



Classifications

eCl@ss

eCl@ss 10.0.1	27182701
eCl@ss 11.0	27182701
eCl@ss 4.0	27180400
eCl@ss 4.1	27180400
eCl@ss 5.0	27180500
eCl@ss 5.1	27180500
eCl@ss 6.0	27180800

Side element - UM108-SEFE/R - 2959683

Classifications

eCl@ss

eCl@ss 7.0	27182701
eCl@ss 8.0	27182701
eCl@ss 9.0	27182701

ETIM

ETIM 2.0	EC001031
ETIM 3.0	EC001031
ETIM 4.0	EC001031
ETIM 5.0	EC002779
ETIM 6.0	EC002779
ETIM 7.0	EC002779

UNSPSC

UNSPSC 6.01	31261501
UNSPSC 7.0901	31261501
UNSPSC 11	31261501
UNSPSC 12.01	31261501
UNSPSC 13.2	31261501
UNSPSC 18.0	31261501
UNSPSC 19.0	31261501
UNSPSC 20.0	31261501
UNSPSC 21.0	31261501

Approvals

Approvals

Approvals

EAC / UL Recognized

Ex Approvals

Approval details

EAC		B.01687
-----	--	---------

Side element - UM108-SEFE/R - 2959683

Approvals

UL Recognized



<http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm>

FILE E 240868