


Pxxx0S3N Series


High Surge Current SIDACtor® - D0214AB



Agency Approvals

| Agency | Agency File Number |
|--------|--------------------|
| | E133083 |

Schematic Symbol



Description

The Pxxx0S3N Series DO-214AB protection thyristors are components designed to protect equipment located in hostile environments from overvoltage transients.

The Pxxx0S3N Series protect exposed interfaces in industrial and ICT applications, such as RS-485 data interfaces, AC or DC power supplies. These components' switching voltage V_s are much lower than alternative Gas Discharge Tubes (GDT), and on-state voltage V_T are much lower than alternative GDTs, Metal Oxide Varistors (MOV) and TVS Diodes.

This Pxxx0S3N series are rated 3000A 8/20 μ s, enabling equipment compliance with regulatory and customer surge requirements.

Features and Benefits

- Low voltage overshoot
- Low on-state voltage
- Component properties do not degrade after multiple surge events within its limits
- Fails short circuit when surged in excess of ratings
- Fast response in nanoseconds
- 3000A 8/20 μ s Surge Rating
- RoHS Compliant and Halogen-Free
- Pb-free E3 means 2nd level interconnect is Pb-free and the terminal finish material is tin (Sn) (IPC/JEDEC J-STD609A.01)

Applicable Global Standards

- TIA-968-A
- TIA-968-B
- ITU K.20/21 Enhanced Level
- ITU K.20/21 Basic Level
- GR 1089 Inter-building
- GR 1089 Intra-building
- IEC 61000-4-5, 2nd Ed
- YD/T 1082
- YD/T 993
- YD/T 950

Electrical Characteristics

| Part Number | Marking | V_{DRM} | V_s | I_H | I_s | I_T | V_T | Capacitance | |
|-------------|---------|--------------------|-----------------|--------|--------|-------|--------------|-----------------|--------|
| | | @ $I_{DRM}=5\mu A$ | @ 100V/ μs | | | | @ $I_T=2.2A$ | @ 1MHz, 2V bias | |
| | | V min | V max | mA min | mA max | A max | V max | pF min | pF max |
| P0080S3NLRP | P-8N | 6 | 25 | 50 | 800 | 2.2 | 4 | 80 | 150 |
| P0300S3NLRP | P03N | 30 | 45 | 50 | 800 | 2.2 | 4 | 80 | 150 |
| P0640S3NLRP | P06N | 58 | 77 | 50 | 800 | 2.2 | 4 | 150 | 550 |
| P0720S3NLRP | P07N | 65 | 88 | 50 | 800 | 2.2 | 4 | 150 | 550 |
| P0900S3NLRP | P09N | 75 | 98 | 50 | 800 | 2.2 | 4 | 150 | 550 |
| P1100S3NLRP | P11N | 90 | 130 | 50 | 800 | 2.2 | 4 | 150 | 450 |
| P1300S3NLRP | P13N | 120 | 160 | 50 | 800 | 2.2 | 4 | 150 | 450 |
| P1500S3NLRP | P15N | 140 | 180 | 50 | 800 | 2.2 | 4 | 150 | 450 |
| P1900S3NLRP | P19N | 155 | 220 | 50 | 800 | 2.2 | 4 | 150 | 450 |
| P2300S3NLRP | P23N | 180 | 260 | 50 | 800 | 2.2 | 4 | 150 | 450 |
| P2600S3NLRP | P26N | 220 | 300 | 50 | 800 | 2.2 | 4 | 150 | 450 |
| P3100S3NLRP | P31N | 275 | 350 | 50 | 800 | 2.2 | 4 | 150 | 450 |
| P3500S3NLRP | P35N | 320 | 400 | 50 | 800 | 2.2 | 4 | 150 | 450 |
| P3800S3NLRP | P38N | 350 | 430 | 50 | 800 | 2.2 | 4 | 150 | 450 |

Notes:

- Absolute maximum ratings measured at $T_A=25^\circ C$ (unless otherwise noted).
- Components are bi-directional (unless otherwise noted).

Pxxx0S3N Series

High Surge Current SIDACtor® - D0214AB

Surge Ratings


| Series | I_{PP} | I_{TSM} 50 / 60 Hz | di/dt |
|--------|--|-------------------------|-------|
| | 8/20 ¹ 1.2/50 ² | | |
| | A min | | |
| N | 2500/3000 | 250 | 420 |

Notes:


1. Current waveform in μs
2. Voltage waveform in μs
3. Surge Rating 2500A for P0080S3NLRP and P0300S3NLRP

- Peak pulse current rating (I_{PP}) is repetitive and guaranteed for the life of the product.
- I_{PP} ratings applicable over temperature range of -40°C to +85°C
- The device must initially be in thermal equilibrium with -40°C ≤ T_J ≤ +150°C


Thermal Considerations

| Package | Symbol | Parameter | Value | Unit |
|---|-----------|---|-------------|------|
| DO-214AB  | T_J | Operating Junction Temperature Range | -65 to +150 | °C |
| | T_S | Storage Temperature Range | -65 to +150 | °C |
| | $R_{θJA}$ | Thermal Resistance: Junction to Ambient | 75 | °C/W |


V-I Characteristics




tr x td Pulse Waveform



Normalized V_S Change vs. Junction Temperature



Normalized DC Holding Current vs. Case Temperature




Pxxx0S3N Series

High Surge Current SIDACtor® - D0214AB

Soldering Parameters

| | | |
|--|------------------------------------|--------------|
| Reflow Condition | Pb-Free assembly (see Fig. 1) | |
| Pre Heat | - Temperature Min ($T_{s(min)}$) | +150°C |
| | - Temperature Max ($T_{s(max)}$) | +200°C |
| | - Time (Min to Max) (t_s) | 60-120 secs. |
| Average ramp up rate (Liquidus Temp (T_L) to peak) | 3°C/sec. Max. | |
| $T_{s(max)}$ to T_L - Ramp-up Rate | 3°C/sec. Max. | |
| Reflow | - Temperature (T_L) (Liquidus) | +217°C |
| | - Temperature (t_l) | 60-150 secs. |
| Peak Temp (T_p) | +260(+0/-5)°C | |
| Time within 5°C of actual Peak Temp (t_p) | 30 secs. Max. | |
| Ramp-down Rate | 6°C/sec. Max. | |
| Time 25°C to Peak Temp (T_p) | 8 min. Max. | |
| Do not exceed | +260°C | |




Physical Specifications

| | |
|------------------------|---|
| Lead Material | Copper Alloy |
| Terminal Finish | 100% Matte-Tin Plated |
| Body Material | UL Recognized epoxy meeting flammability classification UL94-V0 |


Environmental Specifications

| | |
|---|---|
| High Temp Voltage Blocking | 80% Rated V_{DRM} (V_{AC} Peak) +125°C or +150°C, 504 or 1008 hrs. MIL-STD-750 (Method 1040) JEDEC, JESD22-A-101 |
| Temp Cycling | -65°C to +150°C, 15 min. dwell, 10 up to 100 cycles. MIL-STD-750 (Method 1051) EIA/JEDEC, JESD22-A104 |
| Biased Temp & Humidity | 52 V_{DC} (+85°C) 85%RH, 504 up to 1008 hrs. EIA/JEDEC, JESD22-A-101 |
| High Temp Storage | +150°C 1008 hrs. MIL-STD-750 (Method 1031) JEDEC, JESD22-A-101 |
| Low Temp Storage | -65°C, 1008 hrs. |
| Thermal Shock | 0°C to +100°C, 5 min. dwell, 10 sec. transfer, 10 cycles. MIL-STD-750 (Method 1056) JEDEC, JESD22-A-106 |
| Autoclave (Pressure Cooker Test) | +121°C, 100%RH, 2atm, 24 up to 168 hrs. EIA/JEDEC, JESD22-A-102 |
| Resistance to Solder Heat | +260°C, 30 secs. MIL-STD-750 (Method 2031) |
| Moisture Sensitivity Level | 85%RH, +85°C, 168 hrs., 3 reflow cycles (+260°C Peak). JEDEC-J-STD-020, Level 1 |

Part Numbering




Part Marking



Pxxx0S3N Series

High Surge Current SIDACtor® - D0214AB

Dimensions – DO-214AB




| Dimensions | Inches | | Millimeters | |
|------------|--------|-------|-------------|-------|
| | Min | Max | Min | Max |
| A | 0.114 | 0.126 | 2.900 | 3.200 |
| B | 0.260 | 0.280 | 6.600 | 7.110 |
| C | 0.220 | 0.245 | 5.590 | 6.220 |
| D | 0.079 | 0.103 | 2.060 | 2.620 |
| E | 0.030 | 0.060 | 0.760 | 1.520 |
| F | - | 0.008 | - | 0.203 |
| G | 0.305 | 0.320 | 7.750 | 8.130 |
| H | 0.006 | 0.012 | 0.152 | 0.305 |
| I | 0.129 | - | 3.300 | - |
| J | 0.094 | - | 2.400 | - |
| K | - | 0.165 | - | 4.200 |
| L | 0.094 | - | 2.400 | - |

Packing Options

| Package Type | Description | Quantity | Added Suffix | Industry Standard |
|--------------|-----------------------------|----------|--------------|---------------------------------------|
| S3 | DO-214AB Tape and Reel Pack | 3000 | RP | EIA-481-D tape and reel specification |

Tape and Reel Specification – DO-214AB



Disclaimer Notice - Littelfuse products are not designed for, and shall not be used for, any purpose (including, without limitation, automotive, military, aerospace, medical, life-saving, life-sustaining or nuclear facility applications, devices intended for surgical implant into the body, or any other application in which the failure or lack of desired operation of the product may result in personal injury, death, or property damage) other than those expressly set forth in applicable Littelfuse product documentation. Warranties granted by Littelfuse shall be deemed void for products used for any purpose not expressly set forth in applicable Littelfuse documentation. Littelfuse shall not be liable for any claims or damages arising out of products used in applications not expressly intended by Littelfuse as set forth in applicable Littelfuse documentation. The sale and use of Littelfuse products is subject to Littelfuse Terms and Conditions of Sale, unless otherwise agreed by Littelfuse. "Littelfuse" includes Littelfuse, Inc., and all of its affiliate entities. <http://www.littelfuse.com/disclaimer-electronics>.