


# Thick Film Chip Resistors, Industrial, High Power, **Aluminum Nitride Substrate**



Aluminum nitride over 3 x more power - same size

MATERIAL SPECIFICATIONS				
Resistive element	Ruthenium oxide			
Encapsulation	Ероху			
Substrate	Aluminum nitride			
Termination	Solder-coated nickel barrier			
Solder finish	Pure tin or tin / lead solder alloy			

#### **FEATURES**





 Very high thermal conductivity in a small package size



 Termination: tin / lead wraparound termination RoHS over nickel barrier. Also available lead (Pb)-free wraparound terminations.




- Capability to develop specific reliability programs designed to customer requirements
- Operating temperature range: -65 °C to +155 °C
- High frequency performance to 6 GHz
- Material categorization: for definitions of compliance please see www.vishay.com/doc?99912

This datasheet provides information about parts that are RoHS-compliant and / or parts that are non RoHS-compliant. For example, parts with lead (Pb) terminations are not RoHS-compliant. Please see the information / tables in this datasheet for details

STANDARD ELECTRICAL SPECIFICATIONS							
GLOBAL MODEL	CASE SIZE	POWER RATING (1) (Standard Board Mount)  P <sub>25°C</sub> W	POWER RATING (1) (Active Temperature Control) W	MAXIMUM WORKING VOLTAGE V	RESISTANCE RANGE Ω	TOLERANCE ± %	TEMPERATURE COEFFICIENT ± ppm/°C
RCP0505	0505	1.4	5.0	$\sqrt{P \times R}$	10 to 2K	1, 2, 5	150
RCP0603	0603	1.5	3.9	√P x R	10 to 2K	1, 2, 5	150
RCP1206	1206	2.4	11	√P x R	10 to 2K	1, 2, 5	150
RCP2512	2512	3.5	22	$\sqrt{P \times R}$	10 to 2K	1, 2, 5	150

### Notes

- Consult factory for availability of additional case sizes
- (1) The power rating depends on the maximum temperature of the resistive element. The temperature of the resistive element and adjacent materials will rise due to the power dissipation of the resistor. The majority of this heat/energy is dissipated by conduction through the substrate, terminations, solder joints, and printed circuit board. The maximum power rating in a particular application only applies if the temperature of the resistive element is maintained at or below 155 °C



Revision: 10-Mar-17


For additional information on packaging, refer to the Surface Mount Resistor Packaging document (<u>www.vishay.com/doc?31543</u>)




PERFORMANCE				
TEST		CONDITIONS OF TEST	TEST RESULTS (TYPICAL TEST LOTS)	
Resistance to soldering he	at	2 cycles; > 183 °C for 90 s to 120 s	$\leq \pm 0.20 \%$ $\leq \pm 120 \text{ ppm}$ $\leq \pm 0.02 \%$	
Resistance temperature ch	aracteristic	-55 °C to +125 °C		
Low temperature operation	ı	-65 °C at rated voltage		
	RCP0505	3.1 W applied for 5 s		
Short time overload	RCP0603	4.4 W applied for 5 s	≤ ± 0.10 %	
	RCP1206	4.7 W applied for 5 s		
	RCP2512	7.7 W applied for 5 s		
High temperature exposure		+150 °C for 100 h	≤ ± 0.10 %	
Moisture resistance		240 h at ≥ 80 % RH	≤ ± 0.15 %	
Life		1000 h at +70 °C		
Solderability		J-STD-202, test B	95 % coverage	
		Per MIL-PRF-55342:		
Solder mounting integrity	RCP0505	1 kg force applied	7	
	RCP0603	2 kg force applied	No evidence of mechanical damage	
	RCP1206	2 kg force applied	7	
	RCP2512	3 kg force applied		

### **DIMENSIONS** in inches (millimeters)








WIDE BOTTOM TERMINAL (W)

TRADITIONAL TERMINAL (B)

GLOBAL	A	B	C	D	E
MODEL	(LENGTH)	(WIDTH)	(HEIGHT)	(TOP TERM)	(BOTTOM TERM)
RCP0505W	0.055 ± 0.005	0.050 ± 0.005	0.020 ± 0.005	0.010 ± 0.005	0.020 ± 0.005
	(1.40 ± 0.13)	(1.27 ± 0.13)	(0.51 ± 0.13)	(0.25 ± 0.13)	(0.51 ± 0.13)
RCP0505B	0.055 ± 0.005	0.050 ± 0.005	0.020 ± 0.005	0.010 ± 0.005	0.015 ± 0.005
	(1.40 ± 0.13)	(1.27 ± 0.13)	(0.51 ± 0.13)	(0.25 ± 0.13)	(0.38 ± 0.13)
RCP0603W	0.063 ± 0.005	0.032 ± 0.005	0.018 ± 0.005	0.012 ± 0.005	0.023 ± 0.005
	(1.60 ± 0.13)	(0.81 ± 0.13)	(0.46 ± 0.13)	(0.30 ± 0.13)	(0.58 ± 0.13)
RCP0603B	0.063 ± 0.005	0.032 ± 0.005	0.018 ± 0.005	0.012 ± 0.005	0.015 ± 0.005
	(1.60 ± 0.13)	(0.81 ± 0.13)	(0.46 ± 0.13)	(0.30 ± 0.13)	(0.38 ± 0.13)
RCP1206W	0.122 ± 0.005	0.060 ± 0.005	0.020 ± 0.005	0.015 ± 0.005	0.048 ± 0.005
	(3.10 ± 0.13)	(1.52 ± 0.13)	(0.51 ± 0.13)	(0.38 ± 0.13)	(1.22 ± 0.13)
RCP1206B	0.122 ± 0.005	0.060 ± 0.005	0.020 ± 0.005	0.015 ± 0.005	0.015 ± 0.005
	(3.10 ± 0.13)	(1.52 ± 0.13)	(0.51 ± 0.13)	(0.38 ± 0.13)	(0.38 ± 0.13)
RCP2512W	0.250 ± 0.005	0.124 ± 0.005	0.020 ± 0.005	0.020 ± 0.005	0.113 ± 0.005
	(6.35 ± 0.13)	(3.15 ± 0.13)	(0.51 ± 0.13)	(0.51 ± 0.13)	(2.87 ± 0.13)
RCP2512B	0.250 ± 0.005	0.124 ± 0.005	0.020 ± 0.005	0.020 ± 0.005	0.020 ± 0.005
	(6.35 ± 0.13)	(3.15 ± 0.13)	(0.51 ± 0.13)	(0.51 ± 0.13)	(0.51 ± 0.13)







## **Legal Disclaimer Notice**

Vishay

## **Disclaimer**

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.

# **Mouser Electronics**

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

# Vishay:

RCP1206W2K00JTP	RCP1206W12R0JTP	RCP0603W100RGEB	RCP0603W50R0GEB	RCP0603W100RGS3
RCP0505W100RGEB	RCP0603W75R0GS3	RCP2512W50R0GEB	RCP1206W75R0GS3	RCP1206W75R0GEB
RCP0505W75R0GEB	RCP0505W50R0GEB	RCP1206W50R0GEB	RCP2512W100RGS3	RCP0603W75R0GEB
RCP0603W50R0GS3	RCP0603W25R0GS3	RCP1206W25R0GEB	RCP2512W25R0GEB	RCP0603W25R0GEB
RCP0505W100RGS3	RCP2512W75R0GS3	RCP2512W50R0GS3	RCP1206W50R0GS3	RCP0505W25R0GS3
RCP1206W25R0GS3	RCP0505W25R0GEB	RCP2512W25R0GS3	RCP2512W75R0GEB	RCP0505W50R0GS3
RCP0505W75R0GS3	RCP1206W100RGS3	RCP1206W100RGEB	RCP2512W100RGEB	RCP0603W120RGEB
RCP0603W12R0GEB	RCP2512W120RGEB	RCP1206W1K00GEB	RCP1206W10R0GEB	RCP0603W2K00GEB
RCP0603W1K00GEB	RCP0603W200RGEB	RCP2512W2K00GEB	RCP1206W2K00GEB	RCP1206W200RGEB
RCP2512W200RGEB	RCP2512W1K00GEB	RCP2512W10R0GEB	RCP0603W10R0GEB	RCP0603B10R0GET
RCP0603B2K00GET	RCP0603B22R0JS6			