

Metal Film Resistors, Industrial, ± 2 % and ± 5 % Tolerance



FEATURES


Dual power rating:
 P₇₀ = 0.25 W with 1.5 % stability
 P₇₀ = 0.50 W with 2.0 % stability



- ± 2 % and ± 5 % tolerance
- Temperature coefficient: ± 100 ppm/K and ± 200 ppm/K
- Tape and reel packaging for automatic insertion (52.4 mm inside tape spacing per EIA-296-E)
- Flame retardant epoxy conformal coating (red brown color)
- Standard 4 band color code marking for ease of identification after mounting
- Pure tin plating provides compatibility with lead (Pb)-free and lead containing soldering processes
- Material categorization: for definitions of compliance please see <u>www.vishay.com/doc?99912</u>

STANDARD ELECTRICAL SPECIFICATIONS						
PRODUCT	POWER RATING P ₇₀ W	LIMITING ELEMENT VOLTAGE MAX. V≅	TEMPERATURE COEFFICIENT ± ppm/K	TOLERANCE ± %	RESISTANCE RANGE Ω	E-SERIES
CCF07	0.25	250	100	2, 5	10 to 1M	E24
CCF07	0.5	250	100	2, 5	10 to 1M	E24
CCF07	0.25	250	200	5	1.1M to 2M	E24
CCF07	0.5	250	200	5	1.1M to 2M	E24


TECHNICAL SPECIFICATIONS				
PARAMETER	UNIT	CCF07		
Rated Dissipation, P ₇₀	W	0.25/0.5		
Maximum Working Voltage, U _{max.}	V≅	≤ 250		
Insulation Voltage (1 min)	V _{eff}	500		
Dielectric Strength	V _{AC}	450		
Insulation Resistance	Ω	≥ 10 ¹¹		
Operating Temperature Range	°C	-65 to +150		
Terminal Strength (pull test)	lb	2		
Weight	g	0.35 max.		



Revision: 18-Dec-14 1 Document Number: 31013




DIMENSIONS in inches (millimeters)



PRODUCT	Α	В	C (Max.)	D	E
CCF07	0.245 ± 0.020	0.090 ± 0.008	0.295	0.022 ± 0.002	1.100 ± 0.040
	(6.22 ± 0.51)	(2.29 ± 0.20)	(7.5)	(0.58 ± 0.05)	(27.94 ± 1.02)

DERATING



MARKING

The nominal resistance and tolerance are marked on the resistor using four colored bands in accordance with IEC 60062, marking codes for resistors and capacitors.

RESISTANCE VALUES

Vishay CCF07 is available in the standard 24 resistance values per decade. Values are obtained from the following decade table by multiplying by powers of 10. As an example: 24 can represent 24 Ω , 240 Ω , 2.4 k Ω , 24 k Ω or 240 k Ω .

10	18	33	56
11	20	36	62
12	22	39	68
13	24	43	75
15	27	47	82
16	30	51	91

PERFORMANCE		
TEST (1)	MAX. ΔR (Typical Test Lots)	
Thermal Shock	± 1.0 %	
Short Time Overload	± 0.5 %	
Low Temperature Operation	± 0.5 %	
Moisture Resistance	± 1.5 %	
Resistance to Soldering Heat	± 0.5 %	
Shock/Bump	± 0.5 %	
Vibration	± 0.5 %	
Terminal Strength	± 0.5 %	
Dielectric Withstanding Voltage	± 0.5 %	
Life	± 1.5 % ⁽²⁾	

Notes

⁽¹⁾ Test specifications as per IEC 60115-1

⁽²⁾ Life ΔR is ± 2.0 % for 1/2 W rating



Legal Disclaimer Notice

Vishay

Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Vishay:

```
CCF071K50JNR36 CCF078K20GKR36 CCF07220RGKR36 CCF076K80JKR36 CCF07200RGKR36
CCF07430KGKR36 CCF07270KGKR36 CCF07270RGKR36 CCF072K40GKR36 CCF072K20GKR36
CCF0747R0JNR36 CCF0768R0JKR36 CCF0710R0JKR36 CCF0775R0JKR36 CCF0727R0JKR36
CCF0722R0JKR36 CCF0720R0JKR36 CCF0739R0JKR36 CCF0751R0JKR36 CCF07330KJKR36
CCF07470RGKR36 CCF071K60JKR36 CCF07620RGKR36 CCF071K80JNR36 CCF07680RGKR36
CCF07510RGKR36 CCF073K00JKR36 CCF071M00JKR36 CCF07560RGKR36 CCF07300RGKR36
CCF07240KGKR36 CCF07390RGKR36 CCF07330RGKR36 CCF075K10JKR36 CCF077K50GKR36
CCF0715K0GKR36 CCF07200KGKR36 CCF075K10GKR36 CCF075K60GKR36 CCF0718K0GKR36
CCF0711K0GKR36 CCF0710K0GKR36 CCF071K00GKR36 CCF071M00GKR36 CCF072K40JKR36
CCF074K70GNR36 CCF073K00GKR36 CCF072K20JKR36 CCF072K00GKR36 CCF0733R0GKR36
CCF0713R0GKR36 CCF0718R0GKR36 CCF0756R0GKR36 CCF0710R0GKR36 CCF0775R0GKR36
CCF0756K0GKR36 CCF0751K0JKR36 CCF07330KGKR36 CCF07110KGKR36 CCF071K00JNR36
CCF072K00JKR36 CCF07910RGKR36 CCF0743K0GKR36 CCF074K70GKR36 CCF074K40GKR36
CCF07120RGKR36 CCF07390RJKR36 CCF076K20GKR36 CCF076K80GKR36 CCF0733K0GKR36
CCF07270KJKR36 CCF0730K0GKR36 CCF0712K0GKR36 CCF07100KJKR36 CCF0720K0GKR36
CCF0722K0GKR36 CCF0718K5%TR CCF07625%TR CCF07 180K 5%TR CCF07100KJKE36 CCF0710R0JKE36
CCF07180KJNR36 CCF071M50JKR36 CCF0720R0GKE36 CCF0720R0JKE36 CCF07220RJKE36
CCF07240RJKE36 CCF0727K0GKE36 CCF072K20JKE36 CCF072K40JKE36 CCF07330KJKE36
CCF073K30JKE36 CCF07470KGKE36 CCF07470KJKE36 CCF07470RJKE36 CCF0747K0JKE36
CCF0751K0JKE36 CCF075K10JKE36 CCF075K60JKE36 CCF07620RGKE36
```