SURFACE MOUNT DISPLAY

Part Number: ACSA56-51SURKWA

Hyper Red


Features

- 0.56 inch digit height.
- Low current operation.
- Excellent character appearance.
- Mechanically rugged.
- Gray face, white segment.
- Package: 400pcs/ reel.
- Moisture sensitivity level : level 2a.
- RoHS compliant.

Description

The Hyper Red source color devices are made with Al-GaInP on GaAs substrate Light Emitting Diode.

Package Dimensions& Internal Circuit Diagram



SPEC NO: DSAM7137 **APPROVED: WYNEC**

REV NO: V.4A CHECKED: Joe Lee

DATE: JAN/08/2015 DRAWN: L.Q.Xie

PAGE: 1 OF 5 ERP: 1351000713

Selection Guide						
Part No.	Dice	Lens Type	lv (ucd) [1] @ 10mA		Description	
			Min.	Тур.		
ACSA56-51SURKWA	Hyper Red (AlGaInP)	White Diffused	21000	76000	Common Anodo	
			*9000	*22000	Common Anode	

Note:

Luminous intensity/ luminous Flux: +/-15%.
* Luminous intensity value is traceable to the CIE127-2007 compliant national standards.

Electrical / Optical Characteristics at TA=25°C

Symbol	Parameter	Device	Тур.	Max.	Units	Test Conditions
λpeak	Peak Wavelength	Hyper Red	645		nm	I⊧=20mA
λD [1]	Dominant Wavelength	Hyper Red	630		nm	I⊧=20mA
Δλ1/2	Spectral Line Half-width	Hyper Red	28		nm	I⊧=20mA
С	Capacitance	Hyper Red	35		pF	VF=0V;f=1MHz
VF [2]	Forward Voltage	Hyper Red	1.95	2.5	V	I⊧=20mA
IR	Reverse Current	Hyper Red		10	uA	VR=5V

Notes:

1.Wavelength: +/-1nm.

2.Forward Voltage: +/-0.1V.


3.Wavelength value is traceable to the CIE127-2007 compliant national standards.

4.Excess driving current and/or operating temperature higher than recommended conditions may result in severe light degradation or premature failure.


Absolute Maximum Ratings at TA=25°C

Parameter	Hyper Red	Units
Power dissipation	75	mW
DC Forward Current	30	mA
Peak Forward Current [1]	185	mA
Reverse Voltage	5	V
Operating / Storage Temperature	-40°C To +85°C	

Note: 1. 1/10 Duty Cycle, 0.1ms Pulse Width.




SPEC NO: DSAM7137 APPROVED: WYNEC REV NO: V.4A CHECKED: Joe Lee DATE: JAN/08/2015 DRAWN: L.Q.Xie PAGE: 3 OF 5 ERP: 1351000713



CHECKED: Joe Lee

DRAWN: L.Q.Xie



Terms and conditions for the usage of this document

- 1. The information included in this document reflects representative usage scenarios and is intended for technical reference only.
- 2. The part number, type, and specifications mentioned in this document are subject to future change and improvement without notice. Before production usage customer should refer to the latest datasheet for the updated specifications.
- 3. When using the products referenced in this document, please make sure the product is being operated within the environmental and electrical limits specified in the datasheet. If customer usage exceeds the specified limits, Kingbright will not be responsible for any subsequent issues.
- 4. The information in this document applies to typical usage in consumer electronics applications. If customer's application has special reliability requirements or have life-threatening liabilities, such as automotive or medical usage, please consult with Kingbright representative for further assistance.
- 5. The contents and information of this document may not be reproduced or re-transmitted without permission by Kingbright.
- 6.All design applications should refer to Kingbright application notes available at http://www.KingbrightUSA.com/ApplicationNotes

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Kingbright: ACSA56-51SURKWA