
# **Data Sheet**


# EMIFIL® (Capacitor type) Single Circuit Type for Signal Lines

# NFM3DC Series (1205 Size)


### Dimensions



# ■ Insertion Loss Characteristics (Main Items)



# ■ Equivalent Circuit



# Packaging

| Code | Packaging           | Minimum Quantity |  |
|------|---------------------|------------------|--|
| L    | 180mm Embossed Tape | 4000             |  |
| В    | Bulk(Bag)           | 500              |  |

## ■ Rated Value (□: packaging code)

| Part Number     | Capacitance     | Rated Current | Rated Voltage | Insulation Resistance (min.) | Operating<br>Temperature Range |
|-----------------|-----------------|---------------|---------------|------------------------------|--------------------------------|
| NFM3DCC220U1H3□ | 22pF 50/-20%    | 300mA         | 50Vdc         | 1000M ohm                    | -55 to +125°C                  |
| NFM3DCC470U1H3□ | 47pF 50/-20%    | 300mA         | 50Vdc         | 1000M ohm                    | -55 to +125°C                  |
| NFM3DCC101U1H3  | 100pF 50/-20%   | 300mA         | 50Vdc         | 1000M ohm                    | -55 to +125°C                  |
| NFM3DCC221R1H3□ | 220pF 50/-20%   | 300mA         | 50Vdc         | 1000M ohm                    | -55 to +125°C                  |
| NFM3DCC471R1H3□ | 470pF 50/-20%   | 300mA         | 50Vdc         | 1000M ohm                    | -55 to +125°C                  |
| NFM3DCC102R1H3□ | 1000pF 50/-20%  | 300mA         | 50Vdc         | 1000M ohm                    | -55 to +125°C                  |
| NFM3DCC222R1H3□ | 2200pF 50/-20%  | 300mA         | 50Vdc         | 1000M ohm                    | -55 to +125°C                  |
| NFM3DCC223R1H3□ | 22000pF 50/-20% | 300mA         | 50Vdc         | 1000M ohm                    | -55 to +125°C                  |

Number of Circuit: 1

Continued on the following page.  $\nearrow$ 



This data sheet is applied for CHIP EMIFIL® used for General Electronics equipment for your design.

- 1. This datasheet is downloaded from the website of Murata Manufacturing co., Itd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.
- 2. This datasheet has only typical specifications because there is no space for detailed specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

# **Data Sheet**

Continued from the preceding page.

## ■ ①Caution/Notice

## 

Do not use products beyond the rated current and rated voltage as this may create excessive heat and deteriorate the insulation resistance.

### Notice

Solderability of Tin plating termination chip might be deteriorated when low temperature soldering profile where peak solder temperature is below the Tin melting point is used. Please confirm the solderability of Tin plating termination chip before use.

This data sheet is applied for CHIP EMIFIL® used for General Electronics equipment for your design.

- 1. This datasheet is downloaded from the website of Murata Manufacturing co., Itd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.
- 2. This datasheet has only typical specifications because there is no space for detailed specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

# **Mouser Electronics**

**Authorized Distributor** 

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

# Murata: