

# HellermannTyton

## RT40R

Article number: 115-06219



The RELK and RLT cable ties can be re-opened and re-used.

The extended pawl allows for the quick and simple release of the ties. Manufactured in various grades of PA66 these products are suitable for indoor, outdoor and high temperature applications.

Used in a wide range of industries these releasable and reusable ties are ideal where temporary installation or the addition or removal of cables is required, for example: theatres, outdoor events and harness work.



### Base Data

Colour	Natural (NA)
EDP Text 1 Germany	Wiederöffnungsbinder 217x3,9
EDP Text 2 Germany	RT40R Natur 100 ST ME
Fixation Method (FF)	None
Identification Plate Position	none
Releasable Closure (Yes/No)	Yes
Short Description	8.46", 34 lb., releasable cable tie, natural, 100/bag
Tie Closure	plastic pawl
Type	RT40R.NN3P
Variant	Inside Serrated

### Product Dimensions

Bundle $\varnothing$ max.	51 mm
Bundle $\varnothing$ max. (imperial)	2 "
Bundle $\varnothing$ min.	1.5 mm
Bundle $\varnothing$ min. (imperial)	0.06 "
Length (L)	215 mm
Length (L) (imperial)	8.46 "
Min. Tensile Strength (N)	180 N
Min. Tensile Strength (lbs)	40 lbs
Thickness (T)	1.2 mm
Width (W)	4 mm
Width (W) (imperial)	0.16 "

### Logisitic and Packaging

Carton Quantity	5000 pcs.
EAN code	4031026108407
Pack Cont.	100
Quantity of Europallet	100000 pcs.
Quantity per	Bag
UPC	89306044260
Weight (Kg)	1.2 kg

**Material and Specifications**

CSA Certified	FALSE
Flammability	UL94 V2
Material	Polyamide 6.6 (PA66)
Material	PA66
Operating Temperature	-40 °C to +85 °C, intermittent +105 °C (for 500 h)
Specification	UL

**More Information**

UNSPSC Key 39121703

© HellermannTyton 2012