

## Mechanical Encoders

## **SERIES 25L**


## Hex, Gray and Quadrature Code

## **FEATURES**

- Price Competitive to Similar Designs
- Quality Construction and Contact Materials
- Multiple Code and Indexing Choices
- 100,000 Life Cycles
- Less than 1.0" Square
- Manufactured to ISO 9001 Standards




## **DIMENSIONS** in inches (and millimeters)



### **TRUTH TABLES**

Clockwise Rotation						
	4-Bit Gray Code-16 Position					
Switch Position	Code Position	Output 1 2 4 8			8	
1	0					
2	1	•				
3	2	•	•			
4	3		•			
5	4		•	•		
6	5	•	•	•		
7	6	•		•		
8	7			•		
9	8			•	•	
10	9	•		•	•	
11	10	•	•	•	•	
12	11		•	•	•	
13	12		•		•	
14	13	•	•		•	
15	14	•			•	
16	15				•	

<ul> <li>Indicates closed</li> </ul>	circuit;	blank	indicates
open circuit.			



Clockwise Rotation					
	4-Bit Binary C	ode Hex	adecimal-1	6 Position	
Switch Position	Code Position	1	2 Ou	tput 4	8
1	0				
2	1	•			
3	2		•		
4	3	•	•		
5	4			•	
6	5	•		•	
7	6		•	•	
8	7	•	•	•	
9	8				•
10	9	•			•
11	10		•		•
12	11	•	•		•
13	12			•	•
14	13	•		•	•
15	14		•	•	•
16	15	•	•	•	•

Indicates closed circuit; blank indicates open circuit.

Quadrature 2-Bit Code 1/4 Cycle per Detent				
Switch Position	"A" Output "B"			
1				
2	•			
3	•	•		
3 4		•		
5				
6	•			
7	•	•		
8		•		
9				
10	•			
11	•	•		
12		•		
13				
14	•			
15	•	•		
16		•		
17				
18	•			
19	•	•		
20		•		
21				
22	•			
23	•	•		
24		•		
25				
26	•			
27	•	•		
28		•		
29				
30	•			
31	•	•		
32		•		
33				
34	•			
35	•	•		
36		•		

**Clockwise Rotation** 

 Indicates closed circuit; blank indicates open circuit. Code repeats every 4 positions.

#### Mechanical Encoders



#### **SPECIFICATIONS**

#### **Electrical Ratings**

Switching Loads: 1.5 mA at 115 Vac, resistive;

150 mA at 14 Vdc. resistive

Current Carrying Capacity: 250 mA maximum

at 28 Vdc, resistive load

Contact Resistance: 75 m $\Omega$ , typical

Insulation Resistance: 1000 m $\Omega$  minimum

between terminals

Voltage Breakdown: 1000 Vac minimum between

Life Expectancy: 100,000 cycles of operation at rated loads. One cycle of operation is a rotation through all of the active positions and a return to the starting position.

#### **Mechanical Ratings**

Rotational Torque: 2 to 6 in-oz

Operating Temperature Range: -40 C° to +85 C° Storage Temperature Range: -65 C° to +85 C° Continuous Rotation: All standard switches are continuous rotation. Desired stop locations supplied upon request.

Anti-Rotation Device: Integral non-turn tab, flatted bushing, .375" diameter, .320 double "D" across flats.

Termination: Standard is PC style, parallel to shaft, facing rear. Options include PC, parallel to shaft, facing front.

Panel Mounting Torque: 10 in-lbs maximum

## **Materials and Finishes**

Bushing/Housing and Shaft/Rotor: Reinforced thermoplastic

Detent Ball: Stainless steel, nickel-plated **Detent Spring:** Tinned music wire


Contacts: Beryllium copper, gold plate over

Terminals: Copper alloy, #725, 100% tin plate


over nickel plate

Output Board: FR-4, copper/nickel-plated Mounting Nut: Brass, tin/zinc-plated hex nut Mounting Bracket: Stainless Steel, tin-plated

# QUADRATURE CODE TERMINAL I.D. OUTPUT "B" OUTPUT "A" OUTPUT (COMMON)




#### PCB MOUNTING PATTERN



- 1. MOUNTING BRACKET POSTS: .035±.002 WIDE X .020±.004 THICK (4 PLACES).
- 2. TERMINAL PINS: .025±.002 SQUARE (3 OR 5 PLACES).

# RECOMMENDED PANEL CUTOUT



#### ORDERING INFORMATION

25LB10-Q-Z

Series: 25L = Economical, single deck encoder

Housing Color: B = Black housing; R = Red housing

**Angle of Throw:**  $10 = 10^{\circ}$ , 36 positions;  $11 = 11.25^{\circ}$ , 32 positions;

 $15 = 15^{\circ}$ , 24 positions;  $18 = 18^{\circ}$ , 20 positions;

 $22 = 22.5^{\circ}$ , 16 positions;  $30 = 30^{\circ}$ , 12 positions;

 $45 = 45^{\circ}$ , 8 positions

Mounting Bracket: Z = with bracket, Blank = no bracket Code Output: H = Hexadecimal available only in 22.5°

G = Gray available only in 22.5°

Q = Quadrature (2-bit)

Custom materials, styles, color and markings are available. Custom knobs available.

Available from your local Grayhill Distributor. For prices and discounts, contact a local Sales Office, an authorized Distributor or Grayhill. For Custom codes. Termination, Torque, Angles of Throw, call Grayhill for more information.