



STRIPPING DIMENSIONS

NOTES:

1. MATERIAL: COPPER ALLOY

2. PLATING:

(b) ITEM 1+2: GOLD FLASH over NICKEL

ITEM 3: NICKEL PLATED

3. CRIMPING: USE CRIMP TOOL 360X10409X

WITH TOOL INSERT 360X20029X

SELECTOR SETTINGS: 3 FOR AWG 16

2 FOR AWG 18

2 FOR AWG 20

Directive 2002/95/EC RoHS compliant

(b)

THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH

DO NOT ALTER CAD DRAWING BY HAND

finish:				tolerance		scale:	
see notes				ISO 2768-m		5:1	
				dim. in mm		material:	
						see notes	
				date		title:	
				name		HIGH POWER CONTACT FEMALE	
				drawn 26.07.06		CRIMP VERSION 10A	
				appd. 26.07.06		D-SUB COMBINATION	
				norm		dwg no:	
				d-old		Inventor 10	
2 x b		Ä3854		19.01.2011		DIN-A4	
a		Origin				sh: 1	
rev.		description		date		name	



material:		see notes	
title:			
HIGH POWER CONTACT FEMALE			
CRIMP VERSION 10A			
D-SUB COMBINATION			
dwg no:		Inventor 10	
part no:		132A11019X	
13K1A1835		DIN-A4	
		sh: 1	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[CONEC:](#)

[132A11019X](#)