

Rev. A

Features

- High Efficiency (Up to 90%)
- Full Power at 70-100% Max Current (Constant Power)
- Thermal Sensing and Protection for LED Panel/Strings
- DALI Dimmable and Dim off
- Low Dimming Level to 1% with Good Accuracy
- Standby Power ≤0.5 W
- Output Lumen Compensation
- All-Around Protection: OVP, SCP, OTP
- Class II, SELV and Class 2
- Complies with DALI protocol IEC62386-101,102 and part of 207





Description

The *LUD-060SxxxBSF* series is a 60W, constant-current, programmable indoor LED driver that operates from 90-305 Vac input with excellent power factor. Created for dimmable panel lights and linear lights, it provides good dimming accuracy down to 1% output, plus a dim-off mode with low standby power. The high efficiency of these drivers and slim metal case enables them to run cooler, significantly improving reliability and extending product life. To ensure trouble-free operation, protection is provided against over voltage, short circuit, and over temperature of both the driver and the external LED array.

Models

Output Current	Full-Power Current	Default Output	Input Voltage	Output Voltage	Max. Output	Typical Efficiency	Power	Factor	Model Number
Range	Range (1)	Current	•	Range	Power	(3)	120Vac	220Vac	
3.85-550mA	385-550 mA	530mA	90 ~ 305 Vac 127~300 Vdc		60 W	90%	0.99	0.96	LUD-060S055BSF
5.46-780mA	546-780 mA	700mA	90 ~ 305 Vac 127~300 Vdc	22~110 Vdc	60 W	90%	0.99	0.96	LUD-060S078BSF (SELV)
7.7-1100mA	770-1100 mA	1050mA	90 ~ 305 Vac 127~300 Vdc	16 ~78 Vdc	60 W	90%	0.99	0.96	LUD-060S110BSF (SELV)
10.5-1500mA	1050-1500mA	1400mA	90 ~ 305 Vac 127~300 Vdc	177 ~6 / 1/00	60 W	90%	0.99	0.96	LUD-060S150BSF (Class2 & SELV)
14.7-2100mA	1470-2100mA	2100mA	90 ~ 305 Vac 127~300 Vdc	8 ~40 Vdc	60 W	89%	0.99	0.96	LUD-060S210BSF (Class2 & SELV)


Notes: (1) Output current range with constant power at 60W


⁽²⁾ UL, FCC certified input voltage range: 100-277Vac or 127-300Vdc; other certified input voltage range except UL & FCC: 100-240Vac /127-250Vdc

⁽³⁾ Measured at a 220Vac input with 70% maximum output current and 100% maximum output voltage.

Rev. A

I-V Operating Curve





Input Specifications

Parameter	Min.	Тур.	Max.	Notes
Input Voltage	90 V - 305 V 127~300 Vdc		127~300 Vdc	
Input Frequency	47 Hz	-	63 Hz	
Leakage Current	-	-	0.75 mA	At 277Vac 60Hz input
	-	-	0.8 A	Measured at full load and 100 Vac input.
Input AC Current	-	-	0.36 A	Measured at full load and 220 Vac input.
Inrush Current(I ² t)	-	-	2 A ² s	At 220Vac input, 25°C Cold Start, Duration =0.44 mS, 10%lpk-10%lpk. See Inrush Current Waveform for the details.
PF	0.90	-	-	At 100-277Vac, 65%-100% load(39-60W)
THD	-	-	20%	At 100-211 vac, 05 %-100% load(59-0000)

Output Specifications

utput opecinications								
Parameter	Min.	Тур.	Max.	Notes				
Output Current Tolerance	-5%loset	-	5%loset	At full load condition				
Output Current Setting(loset) Range	0.7%lomax	-	100%lomax					
Output Current Setting Range with Constant Power	70%lomax	-	100%lomax					
Output Current Ripple(pk-pk)	-	5%lomax	10%lomax	At full load condition				
Startup Overshoot Current	-	-	10%lomax	At full load condition				



Rev. A

Output Specifications (Continued)

Surpur Opcomoditions (Continued)							
Parameter	Min.	Тур.	Max.	Notes			
No Load Output Voltage							
LUD-060S055BSF	-	-	180 V				
LUD-060S078BSF	-	-	120 V				
LUD-060S110BSF	-	-	90 V				
LUD-060S150BSF	-	-	59.5 V				
LUD-060S210BSF	-	1	50 V				
Line Regulation	-	-	$\pm 0.5\%$	Measured at full load			
Load Regulation	-	-	±1.5%				
Turn-on Delay Time	-	0.8 s	1.2 s	Measured at 120Vac input.			
Turn-on Delay Time	-	0.6 s	1.0 s	Measured at 220Vac input.			
Temperature Coefficient of loset	-	-	0.02%/°C	Case temperature = 0°C ~Tc max			
12V Auxiliary Output Voltage	10.8 V	12 V	13.2 V				
12V Auxiliary Output Source Current	0 mA	-	200 mA	Return terminal is "Return"			

Note: All specifications are typical at 25°C unless otherwise stated.

General Specifications

Paramet	er	Min.	Тур.	Max.	Notes
Efficiency at 120 Vac input:					
LUD-060S055BSF		00.00/	00.00/		
	lo=385 mA	86.0%	88.0%	-	
LUD-060S078BSF	lo=550 mA	85.0%	87.0%	-	
LUD-0003070B3F	Io=546 mA	86.0%	88.0%		
	lo=780 mA	85.0%	87.0%	_	Measured at full load and steady-state
LUD-060S110BSF	10-700 1117	00.070	07.070	_	temperature in 25°C ambient;
200 0000110001	Io=770 mA	86.0%	88.0%	_	(Efficiency will be about 2.0% lower if
	Io=1100 mA	84.0%	86.0%	_	measured immediately after startup.)
LUD-060S150BSF					measured ininiculatory after startup.)
	Io=1050 mA	86.0%	88.0%	-	
	Io=1500 mA	84.0%	86.0%	-	
LUD-060S210BSF					
	Io=1470 mA	85.0%	87.0%	-	
	lo=2100 mA	83.0%	85.0%	-	
Efficiency at 220 Va	ac input:				
LUD-060S055BSF		00.00/	00.00/		
	lo=385 mA	88.0%	90.0%	-	
LUD 0000070D0F	lo=550 mA	86.5%	88.5%	-	
LUD-060S078BSF	lo=546 mA	88.0%	90.0%		
	lo=780 mA	87.0%	89.0%	-	Measured at full load and steady-state
LUD-060S110BSF	10-700 1117	07.070	03.070	_	temperature in 25°C ambient;
200 0000110001	Io=770 mA	88.0%	90.0%	_	(Efficiency will be about 2.0% lower if
	Io=1100 mA	86.0%	88.0%	_	measured immediately after startup.)
LUD-060S150BSF					incasarea ininediately after startup.)
	Io=1050 mA	88.0%	90.0%	_	
	Io=1500 mA	87.0%	89.0%	-	
LUD-060S210BSF					
	Io=1470 mA	87.0%	89.0%	-	
	lo=2100 mA	85.0%	87.0%	-	

3/13

Specifications are subject to changes without notice.



Rev. A

General Specifications (Continued)

Paramet	Min.	Тур.	Max.	Notes	
Efficiency at 277 Va LUD-060S055BSF	ic input:				
	lo=385 mA	88.0%	90.0%	-	
LUD-060S078BSF	lo=550 mA	86.5%	88.5%	-	
LUD-0003070B3F	Io=546 mA	88.0%	90.0%	_	
	Io=780 mA	87.0%	89.0%	-	Measured at full load and steady-state
LUD-060S110BSF		00.00/	00.00/		temperature in 25°C ambient;
	lo=770 mA lo=1100 mA	88.0% 86.0%	90.0% 88.0%	-	(Efficiency will be about 2.0% lower if
LUD-060S150BSF	10-1100111A	00.070	00.070	_	measured immediately after startup.)
	Io=1050 mA	88.0%	90.0%	-	
	Io=1500 mA	87.0%	89.0%	-	
LUD-060S210BSF	lo=1470 mA	87.0%	89.0%		
	lo=2100 mA	85.0%	87.0%	-	
Standby Power		-	-	0.5 W	Measured at 230Vac/50Hz; Dimming off
MTBF		-	204,000 Hours	-	Measured at 220Vac input, 80%Load and 25°C ambient temperature (MIL-HDBK-217F)
Lifetime		-	120,000 Hours	-	Measured at 120Vac input, 80%Load and 60°C case temperature; See lifetime vs. Tc curve for the details
Case Temperature		-	-	90°C	
Dimensions Inches (L × W × H) Millimeters (L × W ×H)		_	.46×1.18×0. 418 ×30×21		
Net Weight		-	380 g	-	

Note: All specifications are typical at 25°C unless otherwise stated.

Dimming Specifications

Parameter	Min.	Тур.	Max.	Notes
DA1,DA2 High Level	9.5V	16V	22.5V	
DA1,DA2 Low Level	-6.5V	0V	6.5V	
DA1,DA2 Current	0mA	-	2mA	
Dimming Output Bango	1%loset	-	loset	70%Iomax ≤ loset ≤ 100%Iomax
Dimming Output Range	0.7%Iomax	-	loset	0.7%Iomax ≤loset < 70%Iomax

Note: All specifications are typical at 25 °C unless stated otherwise.



Rev. A

Environmental Specifications


Parameter	Min.	Тур.	Max.	Notes
Operating Ambient Temperature	-30°C	-	+70°C	Humidity: 10% RH to 90% RH; No Condensation See Derating Curve for more details
Storage Temperature	-40°C	-	+85°C	Humidity: 5% RH to 90% RH

Safety &EMC Compliance


Safety Category	Standard
UL/CUL	UL 8750,UL1310,CAN/CSA-C22.2 No. 250.13-12,CAN/CSA-C22.2 No. 223-M9
CE	EN61347-1, EN61347-2-13
EMI Standards	Notes
EN 55015	Conducted emission Test &Radiated emission Test
EN 61000-3-2	Harmonic current emissions Class C
EN 61000-3-3	Voltage Fluctuations & Flicker
	ANSI C63.4:2009 Class B
FCC Part 15	This device complies with Part 15 of the FCC Rules. Operation is subject to the following two conditions: (1) this device may not cause harmful interference, and (2) this device must accept any interference received, including interference that may cause undesired Operation.
EMS Standards	Notes
EN 61000-4-2	Electrostatic Discharge(ESD): 8 kV air discharge, 4 kV contact discharge
EN 61000-4-3	Radio-Frequency Electromagnetic Field Susceptibility Test-RS
EN 61000-4-4	Electrical Fast Transient/Burst-EFT
EN 61000-4-5	Surge Immunity Test: AC Power Line: line to line 1 kV
EN 61000-4-6	Conducted Radio Frequency Disturbances Test-CS
EN 61000-4-8	Power Frequency Magnetic Field Test
EN 61000-4-11	Voltage Dips
EN 61547	Electromagnetic Immunity Requirements Applies to Lighting Equipment

Rev. A


Derating



Lifetime vs. Case Temperature



Inrush Current Waveform Tek Prevu




Fax: 86-571-86601139

6/13

Specifications are subject to changes without notice.

Rev. A



20%

40%

Fax: 86-571-86601139

60%


Normalized Output Voltage

80%


Normalized Output Voltage

100%

Rev. A




Power Factor



Rev. A

Total Harmonic Distortion




Protection Functions

Parameter	Min.	Тур.	Max.	Notes	
Over Temperature Protection	Decreases output current, returning to normal after over temperature is removed.				
External Thermal Protection NTC	-	- 4.26 kOhm - is lower than 4.26 kOhm,		The default of NTC is 4.26 kOhm. When NTC is lower than 4.26 kOhm, External Thermal Protection will be triggered.	
Short Circuit Protection	Auto Recovery. No damage will occur when any output is short circuited. The output shall return to normal when the fault condition is removed.				
Over Voltage Protection	Limits output voltage at no load and in case the normal voltage limit fails.				


Dimming

DALI Dimming

The recommended implementation of the dimming control is provided below.




Rev. A



Output Lumen Compensation


Output Lumen Compensation (OLC) may be used to maintain constant light output over the life of the LEDs by driving them at a reduced current when new, then gradually increasing the drive current over time to counteract LED lumen degradation.






Rev. A

Wire Connection Diagram



Programming Connection Diagram



Note: The driver needs to be powered on during the programming process.

Please refer to DALI-PROGRAM (Programmer) datasheet for details.


http://www.inventronics-

co.com/cp det.aspx?c kind=2&c kind2=177&c kind3=179&id=232&productName=DALI-PROGRAM

Rev. A

60W Programmable Indoor Driver with DALI

Mechanical Outline





PROJ:

Unspecified tolerance:±1

RoHS Compliance

Our products comply with the European Directive 2011/65/EC, calling for the elimination of lead and other hazardous substances from electronic products.



Rev. A

60W Programmable Indoor Driver with DALI

Revision History

Change	Rev.	Description of Change					
Date		Item	From	То			
2014-10-10	Α	Datasheets Release	/	/			