

1410142-1 ✓ ACTIVE

MULTIGIG RT | MULTIGIG RT 2

TE Internal #: 1410142-1

MULTIGIG RT 2, High Speed Backplane Connectors, Board-to-Board, 144 Position, Mating Alignment, Polarization Mating Alignment Type, 9 Row, 16 Column

[View on TE.com >](#)



Connectors > PCB Connectors > Backplane Connectors > High Speed Connectors



Connector System: **Board-to-Board**

Number of Positions: **144**

Row-to-Row Spacing: **1.8 mm [.071 in]**

Mating Alignment: **With**

Mating Alignment Type: **Polarization**

Features

Product Type Features

Applied to Printed Circuit Board Type	Backplane
Connector System	Board-to-Board
PCB Connector Assembly Type	PCB Mount Receptacle
Shroud Style	Unshrouded
Connector & Contact Terminates To	Printed Circuit Board

Configuration Features

Card Slot Centerline	20.3 mm [.8 in]
Number of Positions	144
Number of Rows	9
Number of Columns	16
Backplane Architecture	Traditional Backplane
PCB Mount Orientation	Vertical
Guide Location	Right

Contact Features

Contact Current Rating (Max)	1 A
------------------------------	-----

Mechanical Attachment

Mating Alignment	With
Mating Alignment Type	Polarization



Connector Mounting Type	Board Mount
-------------------------	-------------

Housing Features

Number of Shrouded Sides	0
Centerline (Pitch)	1.8 mm[.071 in]

Dimensions

Row-to-Row Spacing	1.8 mm[.071 in]
--------------------	-----------------

Usage Conditions

Operating Temperature Range	-55 – 105 °C[-67 – 221 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Power & Signal
---------------------	----------------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)


EU RoHS Directive 2011/65/EU	Not Compliant
EU ELV Directive 2000/53/EC	Not Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUL 2021 (219) Candidate List Declared Against: JUL 2021 (219) SVHC > Threshold: Pb (13% in Component Part) Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer


This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>



Compatible Parts




TE Part # 1410139-1
MULTIGIG RT T2 .8" DC DF F-RGT



TE Part # 1410139-2
MULTIGIG RT T2 .8 DC DF F-RGT

Also in the Series | MULTIGIG RT 2



High Speed Backplane Connectors(42)

Customers Also Bought



TE Part #1-6450869-4
V/R 2ACP+1LP+32S+3HDP+1LP+1P



TE Part #1410188-3
MULTIGIG RT T2 7RW DC DF F-RGT



TE Part #1410964-1
MULTIGIG RT T2 .8" BP FULL CNT



TE Part #1410189-3
MULTIGIG RT T2 7RW H-LFT,ET2



TE Part #1-1469491-3
MULTIGIG RT GUIDEPIN, 9MM 4.20



TE Part #1410186-1
MULTIGIG RT T2 .8" BP H-LFT



TE Part #1410140-1
MULTIGIG RT T2 .8" BP FULL CNT



TE Part #1410187-3
MULTIGIG RT T2 7RW DC DF CT



Documents

Product Drawings

[MULTIGIG RT T2 .8" BP FULL RGH](#)

English

CAD Files

[3D PDF](#)

3D

[Customer View Model](#)

[ENG_CVM_CVM_1410142-1_D.2d_dxf.zip](#)

English

[Customer View Model](#)

[ENG_CVM_CVM_1410142-1_D.3d_igs.zip](#)

English

[Customer View Model](#)

[ENG_CVM_CVM_1410142-1_D.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[High Speed Backplane Connectors catalog - MULTIGIG RT Connector](#)

English

[SOSA Aligned Interconnect Solutions](#)

English

[High Speed Backplane Interconnect Solutions Brochure 1654263-1](#)

English

[MULTIGIG RT Connector Products for VITA 46 \(VPX\) Standard](#)

English

Product Specifications

[Electrical Performance Report](#)

English

Product Environmental Compliance

[TE Material Declaration](#)

English

1410142-1

MULTIGIG RT 2, High Speed Backplane Connectors, Board-to-Board, 144 Position,
Mating Alignment, Polarization Mating Alignment Type, 9 Row, 16 Column

