## **ON Semiconductor**

## Is Now



To learn more about onsemi™, please visit our website at www.onsemi.com

onsemi and ONSEMI. and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "onsemi" or its affiliates and/or subsidiaries in the United States and/or other countries. onsemi owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of onsemi product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. onsemi reserves the right to make changes at any time to any products or information herein is provided "as-is" and onsemi makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using onsemi products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by onsemi. "Typical" parameters which may be provided in onsemi data sheets and/ or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. onsemi does not convey any license under any of its intellectual property rights nor the rights of others. onsemi products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use onsemi products for any such unintended or unauthorized application,




# 2N4403 / MMBT4403 PNP General-Purpose Amplifier

## **Description**

This device is designed for use as a general-purpose amplifier and switch for collector currents to 500 mA.








Figure 2. MMBT4403 Device Package

## **Ordering Information**

| Part Number | Marking | Package   | Packing Method |
|-------------|---------|-----------|----------------|
| 2N4403BU    | 2N4403  | TO-92 3L  | Bulk           |
| 2N4403TF    | 2N4403  | TO-92 3L  | Tape and Reel  |
| 2N4403TFR   | 2N4403  | TO-92 3L  | Tape and Reel  |
| 2N4403TA    | 2N4403  | TO-92 3L  | Ammo           |
| 2N4403TAR   | 2N4403  | TO-92 3L  | Ammo           |
| MMBT4403    | 2T      | SOT-23 3L | Tape and Reel  |

### **Absolute Maximum Ratings**(1),(2)

Stresses exceeding the absolute maximum ratings may damage the device. The device may not function or be operable above the recommended operating conditions and stressing the parts to these levels is not recommended. In addition, extended exposure to stresses above the recommended operating conditions may affect device reliability. The absolute maximum ratings are stress ratings only. Values are at  $T_A = 25^{\circ}\text{C}$  unless otherwise noted.

| Symbol           | Parameter  | Value       | Unit |
|------------------|--|-------------|------|
| V <sub>CEO</sub> | Collector-Emitter Voltage                        | -40         | V    |
| V <sub>CBO</sub> | Collector-Base Voltage                           | -40         | V    |
| V <sub>EBO</sub> | Emitter-Base Voltage                             | -5.0        | V    |
| I <sub>C</sub>   | Collector Current - Continuous                   | -600        | mA   |
| $T_{J_i}T_{STG}$ | Operating and Storage Junction Temperature Range | -55 to +150 | °C   |

#### Notes:

- 1. These ratings are based on a maximum junction temperature of 150°C.
- 2. These are steady-state limits. ON Semiconductor should be consulted on applications involving pulsed or lowduty cycle operations.

#### **Thermal Characteristics**

Values are at  $T_A = 25$ °C unless otherwise noted.

| Symbol          | Parameter                               | Ma                    | Unit                    |       |
|-----------------|---|-----------------------|-------------------------|-------|
|                 | raiailletei                             | 2N4403 <sup>(3)</sup> | MMBT4403 <sup>(4)</sup> | Oilit |
| P <sub>D</sub>  | Total Device Dissipation                | 625                   | 350                     | mW    |
|                 | Derate Above 25°C                       | 5.0                   | 2.8                     | mW/°C |
| $R_{\theta JC}$ | Thermal Resistance, Junction to Case    | 83.3                  |                         | °C/W  |
| $R_{\theta JA}$ | Thermal Resistance, Junction to Ambient | 200                   | 357                     | °C/W  |

#### Notes:

- 3. PCB size: FR-4, 76 mm x 114 mm x 1.57 mm (3.0 inch x 4.5 inch x 0.062 inch) with minimum land pattern size.
- 4. Device mounted on FR-4 PCB 1.6 inch x 1.6 inch x 0.06 inch.

#### **Electrical Characteristics**

Values are at  $T_A = 25$ °C unless otherwise noted.

| Symbol                | Parameter   | Conditions   | Min.  | Max.  | Unit              |
|-----------------------|---|--|-------|-------|-------------------|
| Off Charact           | eristics  |  |       | •     | •                 |
| V <sub>(BR)CEO</sub>  | Collector-Emitter Breakdown<br>Voltage <sup>(5)</sup> | I <sub>C</sub> = -1.0 mA, I <sub>B</sub> = 0                     | -40   |       | V                 |
| V <sub>(BR)CBO</sub>  | Collector-Base Breakdown<br>Voltage                   | I <sub>C</sub> = -0.1 mA, I <sub>E</sub> = 0                     | -40   |       | V                 |
| $V_{(BR)EBO}$         | Emitter-Base Breakdown Voltage                        | $I_E = -0.1 \text{ mA}, I_C = 0$                                 | -5.0  |       | V                 |
| I <sub>BL</sub>       | Base Cut-Off Current                                  | $V_{CE} = -35 \text{ V}, V_{EB} = -0.4 \text{ V}$                |       | -0.1  | μΑ                |
| I <sub>CEX</sub>      | Collector Cut-Off Current                             | $V_{CE} = -35 \text{ V}, V_{EB} = -0.4 \text{ V}$                |       | -0.1  | μΑ                |
| On Charact            | eristics  |  |       |       |                   |
|                       |   | I <sub>C</sub> = -0.1 mA, V <sub>CE</sub> = -1.0 V               | 30    |       |                   |
|                       |   | $I_C = -1.0 \text{ mA}, V_{CE} = -1.0 \text{ V}$                 | 60    |       |                   |
| $h_{FE}$              | DC Current Gain                                       | $I_C = -10 \text{ mA}, V_{CE} = -1.0 \text{ V}$                  | 100   |       |                   |
|                       |   | $I_C = -150 \text{ mA}, V_{CE} = -2.0 \text{ V}^{(5)}$           | 100   | 300   |                   |
|                       |   | $I_C = -500 \text{ mA}, V_{CE} = -2.0 \text{ V}^{(5)}$           | 20    |       |                   |
| \/ (aat)              | Collector-Emitter Saturation                          | $I_C = -150 \text{ mA}, I_B = -15 \text{ mA}$                    |       | -0.40 | V                 |
| V <sub>CE</sub> (sat) | Voltage <sup>(5)</sup>                                | $I_C = -500 \text{ mA}, I_B = -50 \text{ mA}$                    |       | -0.75 |                   |
| \/                    | Base-Emitter Saturation Voltage                       | $I_C = -150 \text{ mA}, I_B = -15 \text{ mA}^{(5)}$              | -0.75 | -0.95 | V                 |
| V <sub>BE</sub> (sat) |   | $I_C = -500 \text{ mA}, I_B = -50 \text{ mA}$                    |       | -1.30 |                   |
| Small Signa           | al Characteristics                                    | <u> </u>   |       | •     | •                 |
| f <sub>T</sub>        | Current Gain - Bandwidth Product                      | $I_C = -20 \text{ mA}, V_{CE} = -10 \text{ V},$<br>f = 100  MHz  | 200   |       | MHz               |
| C <sub>cb</sub>       | Collector-Base Capacitance                            | $V_{CB} = -10 \text{ V}, I_{E} = 0,$<br>f = 140 kHz              |       | 8.5   | pF                |
| C <sub>eb</sub>       | Emitter-Base Capacitance                              | $V_{BE} = -0.5 \text{ V}, I_{C} = 0,$<br>f = 140 kHz             |       | 30    | pF                |
| h <sub>ie</sub>       | Input Impedance                                       | $I_C = -1.0 \text{ mA}, V_{CE} = -10 \text{ V},$<br>f = 1.0  kHz | 1.5   | 15.0  | kΩ                |
| h <sub>re</sub>       | Voltage Feedback Ratio                                | $I_C = -1.0 \text{ mA}, V_{CE} = -10 \text{ V},$<br>f = 1.0  kHz | 0.1   | 8.0   | x10 <sup>-4</sup> |
| h <sub>fe</sub>       | Small-Signal Current Gain                             | $I_C = -1.0 \text{ mA}, V_{CE} = -10 \text{ V},$<br>f = 1.0 kHz  | 60    | 500   |                   |
| h <sub>oe</sub>       | Output Admittance                                     | $I_C = -1.0 \text{ mA}, V_{CE} = -10 \text{ V},$<br>f = 1.0  kHz | 1     | 100   | μmhos             |
| Switching (           | Characteristics                                       | <u> </u>   |       |       |                   |
| t <sub>d</sub>        | Delay Time  | $V_{CC} = -30 \text{ V}, I_{C} = -150 \text{ mA},$               |       | 15    | ns                |
| t <sub>r</sub>        | Rise Time   | I <sub>B1</sub> = -15 mA   |       | 20    | ns                |
| t <sub>s</sub>        | Storage Time  | $V_{CC} = -30 \text{ V}, I_{C} = -150 \text{ mA},$               |       | 225   | ns                |
| t <sub>f</sub>        | Fall Time   | I <sub>B1</sub> = I <sub>B2</sub> = -15 mA                       |       | 30    | ns                |

#### Note:

5. Pulse test: pulse width  $\leq 300~\mu s,$  duty cycle  $\leq 2.0\%.$ 

## **Typical Performance Characteristics**




Figure 3. Typical Pulsed Current Gain vs. Collector Current




Figure 4. Collector-Emitter Saturation Voltage vs. Collector Current




Figure 5. Base-Emitter Saturation Voltage vs. Collector Current




Figure 6. Base-Emitter On Voltage vs. Collector Current




Figure 7. Collector Cut-Off Current vs. Ambient Temperature




Figure 8. Input and Output Capacitance vs. Reverse Bias Voltage

## **Typical Performance Characteristics (Continued)**




Figure 9. Switching Times vs. Collector Current




Figure 10. Turn-On and Turn-Off Times vs. Collector Current




Figure 11. Rise Time vs. Collector and Turn-On Base Currents




Figure 12. Power Dissipation vs. Ambient Temperature





Figure 13. Common Emitter Characteristics



**Figure 14. Common Emitter Characteristics** 

## **Typical Performance Characteristics** (Continued)





Figure 15. Common Emitter Characteristics

## **Physical Dimensions**

## TO-92 3L (Tape and Reel, Ammo)



NOTES: UNLESS OTHERWISE SPECIFIED

- DRAWING CONFORMS TO JEDEC MS-013, VARIATION AC.
  ALL DIMENSIONS ARE IN MILLIMETERS. DRAWING CONFORMS TO ASME Y14.5M-2009. DRAWING FILENAME: MKT-ZAO3FREV3.
- ON SEMICONDUCTOR

Figure 16. 3-LEAD, TO-92, MOLDED 0.200 IN LINE SPACING LD FORM (J61Z OPTION) (ACTIVE)

Package drawings are provided as a service to customers considering ON Semiconductor components. Drawings may change in any manner without notice. Please note the revision and/or date on the drawing and contact a ON Semiconductor representative to verify or obtain the most recent revision. Package specifications do not expand the terms of ON Semiconductor's worldwide terms and conditions, specifically the warranty therein, which covers ON Semiconductor products.

#### Physical Dimensions (Continued)

# TO-92 3L (Bulk)




Figure 17. 3-LEAD, JEDEC TO-92 COMPLIANT STRAGHIT LEAD CONFIGURATION (OLD TO92AM3)

Package drawings are provided as a service to customers considering ON Semiconductor components. Drawings may change in any manner without notice. Please note the revision and/or date on the drawing and contact a ON Semiconductor representative to verify or obtain the most recent revision. Package specifications do not expand the terms of ON Semiconductor's worldwide terms and conditions, specifically the warranty therein, which covers ON Semiconductor products.

#### Physical Dimensions (Continued)

## **SOT-23 3L**




Figure 18. 3-LEAD, SOT23, JEDEC TO-236, LOW PROFILE (ACTIVE)

Package drawings are provided as a service to customers considering ON Semiconductor components. Drawings may change in any manner without notice. Please note the revision and/or date on the drawing and contact a ON Semiconductor representative to verify or obtain the most recent revision. Package specifications do not expand the terms of ON Semiconductor's worldwide terms and conditions, specifically the warranty therein, which covers ON Semiconductor products.

ON Semiconductor and III) are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of ON Semiconductor's product/patent coverage may be accessed at <a href="www.onsemi.com/site/pdf/Patent-Marking.pdf">www.onsemi.com/site/pdf/Patent-Marking.pdf</a>. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages.

Buyer is responsible for its products and applications using ON Semiconductor products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by ON Semiconductor. "Typical" parameters which may be provided in ON Semiconductor data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. ON Semiconductor does not convey any license under its patent rights nor the rights of others. ON Semiconductor products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use ON Semiconductor products for any such unintended or unauthorized application, Buyer shall indemnify and hold ON Semiconductor and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that ON Semiconductor was negligent regarding the design or manufacture of the part. ON Semiconductor is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

#### **PUBLICATION ORDERING INFORMATION**

#### LITERATURE FULFILLMENT:

Literature Distribution Center for ON Semiconductor 19521 E. 32nd Pkwy, Aurora, Colorado 80011 USA Phone: 303-675-2175 or 800-344-3860 Toll Free USA/Canada Fax: 303-675-2176 or 800-344-3867 Toll Free USA/Canada Email: orderlit@onsemi.com

N. American Technical Support: 800-282-9855 Toll Free USA/Canada Europe, Middle East and Africa Technical Support:

Phone: 421 33 790 2910 Japan Customer Focus Center Phone: 81-3-5817-1050

ON Semiconductor Website: www.onsemi.com

Order Literature: http://www.onsemi.com/orderlit

For additional information, please contact your local Sales Representative