# Medium-Power Plastic PNP Silicon Transistors

These medium–power, high–performance plastic devices are designed for driver circuits, switching, and amplifier applications.

#### Features

- Low Saturation Voltage
- Excellent Power Dissipation Due to Thermopad<sup>™</sup> Construction
- Excellent Safe Operating Area
- Complement to NPN 2N4921G, 2N4922G, 2N4923G
- This Device is Pb-Free and is RoHS Compliant\*

#### MAXIMUM RATINGS

Rating	Symbol	Value	Unit
Collector – Emitter Voltage	V <sub>CEO</sub>	80	Vdc
Collector – Base Voltage	V <sub>CBO</sub>	80	Vdc
Emitter – Base Voltage	V <sub>EBO</sub>	5.0	Vdc
Collector Current – Continuous (Note 1)	۱ <sub>C</sub>	1.0	Adc
Collector Current – Peak	I <sub>CM</sub>	3.0	Adc
Base Current	Ι <sub>Β</sub>	1.0	Adc
Total Power Dissipation @ T <sub>A</sub> = 25°C Derate above 25°C	P <sub>D</sub>	30 0.24	W W/°C
Operating and Storage Junction Temperature Range	T <sub>J</sub> , T <sub>stg</sub>	-65 to +150	°C

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.

1. The 1.0 A max  $I_C$  value is based upon JEDEC current gain requirements. The 3.0 A max value is based upon actual current–handling capability of the device (See Figure 5).

#### THERMAL CHARACTERISTICS (Note 2)

Characteristic	Symbol	Max	Unit
Thermal Resistance, Junction-to-Case	$R_{\theta JC}$	4.16	°C/W


2. Recommend use of thermal compound for lowest thermal resistance.



## **ON Semiconductor®**


http://onsemi.com

## 3.0 A, 40–80 V, 30 W GENERAL PURPOSE POWER TRANSISTORS





#### MARKING DIAGRAM



Y = Year WW = Work Week 2N4920 = Specific Device Code G = Pb-Free Package

#### **ORDERING INFORMATION**

Device	Package	Shipping
2N4920G	TO-225 (Pb-Free)	500 Unit / Bulk

\*For additional information on our Pb–Free strategy and soldering details, please download the ON Semiconductor Soldering and Mounting Techniques Reference Manual, SOLDERRM/D.

#### **ELECTRICAL CHARACTERISTICS** ( $T_C = 25^{\circ}C$ unless otherwise noted)

Characteristic	Symbol	Min	Max	Unit
OFF CHARACTERISTICS				
Collector–Emitter Sustaining Voltage (Note 3) $(I_C = 0.1 \text{ Adc}, I_B = 0)$	V <sub>CEO(sus)</sub>	80	-	Vdc
Collector Cutoff Current ( $V_{CE} = 40 \text{ Vdc}, I_B = 0$ )	I <sub>CEO</sub>	_	0.5	mAdc
$      Collector Cutoff Current \\ (V_{CE} = Rated V_{CEO}, V_{BE(off)} = 1.5 Vdc) \\ (V_{CE} = Rated V_{CEO}, V_{BE(off)} = 1.5 Vdc, T_C = 125^{\circ}C $	I <sub>CEX</sub>	-	0.1 0.5	mAdc
Collector Cutoff Current ( $V_{CB}$ = Rated $V_{CB}$ , $I_E$ = 0)	I <sub>CBO</sub>	_	0.1	mAdc
Emitter Cutoff Current ( $V_{BE} = 5.0 \text{ Vdc}, I_C = 0$ )	I <sub>EBO</sub>	_	1.0	mAdc
ON CHARACTERISTICS			·	
DC Current Gain (Note 3) ( $I_C = 50 \text{ mAdc}, V_{CE} = 1.0 \text{ Vdc}$ ) ( $I_C = 500 \text{ mAdc}, V_{CE} = 1.0 \text{ Vdc}$ ) ( $I_C = 1.0 \text{ Adc}, V_{CE} = 1.0 \text{ Vdc}$ )	h <sub>FE</sub>	40 30 10	- 150 -	-
Collector–Emitter Saturation Voltage (Note 3) $(I_C = 1.0 \text{ Adc}, I_B = 0.1 \text{ Adc})$	V <sub>CE(sat)</sub>	_	0.6	Vdc
Base–Emitter Saturation Voltage (Note 3) ( $I_C = 1.0 \text{ Adc}, I_B = 0.1 \text{ Adc}$ )	V <sub>BE(sat)</sub>	_	1.3	Vdc
Base-Emitter On Voltage (Note 3) ( $I_C = 1.0 \text{ Adc}, V_{CE} = 1.0 \text{ Vdc}$ )	V <sub>BE(on)</sub>	_	1.3	Vdc
SMALL-SIGNAL CHARACTERISTICS				
Current–Gain – Bandwidth Product ( $I_C = 250 \text{ mAdc}, V_{CE} = 10 \text{ Vdc}, f = 1.0 \text{ MHz}$ )	f <sub>T</sub>	3.0	_	MHz
Output Capacitance ( $V_{CB} = 10 \text{ Vdc}, I_E = 0, f = 100 \text{ kHz}$ )	C <sub>ob</sub>	_	100	pF
Small–Signal Current Gain ( $I_C = 250 \text{ mAdc}, V_{CE} = 10 \text{ Vdc}, f = 1.0 \text{ kHz}$ )	h <sub>fe</sub>	25	_	-

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions. 3. Pulse Test: PW  $\approx$  300 µs, Duty Cycle  $\approx$  2.0%





Figure 1. Power Derating








Figure 3. Turn-On Time




Figure 4. Thermal Response




Figure 5. Active-Region Safe Operating Area

 $I_C/I_B = 10$ 

 $t_{s}' = t_{s} - 1/8 t_{f}$ 

30

50 70 100

IC, COLLECTOR CURRENT (mA)

Figure 6. Storage Time

20

 $I_{\rm C}/I_{\rm B} = 20$ 

 $\begin{array}{l} T_J=25^\circ C\\ T_J=150^\circ C \end{array}$ 

 $I_{B1} = I_{B2}$ 

200 300

5.0

3.0

2.0

1.0

0.7

0.5

0.3

0.2

0.1

0.07

0.05

10

ts', STORAGE TIME (µs)

There are two limitations on the power handling ability of a transistor: average junction temperature and second breakdown. Safe operating area curves indicate  $I_C-V_{CE}$  operation i.e., the transistor must not be subjected to greater dissipation than the curves indicate.

The data of Figure 5 is based on  $T_{J(pk)} = 150^{\circ}$ C;  $T_{C}$  is variable depending on conditions. Second breakdown pulse limits are valid for duty cycles to 10% provided  $T_{J(pk)} \le 150^{\circ}$ C. At high case temperatures, thermal limitations will reduce the power that can be handled to values less than the limitations imposed by second breakdown.





Figure 7. Fall Time




500 700 1000




#### **TYPICAL DC CHARACTERISTICS**

#### PACKAGE DIMENSIONS

TO-225 CASE 77-09 **ISSUE AC** 





NOTES: 1. DIMENSIONING AND TOLERANCING PER

ASME Y14.5M, 1994. 2. CONTROLLING DIMENSION: MILLIMETERS. 3. NUMBER AND SHAPE OF LUGS OPTIONAL.

	MILLIMETERS		
DIM	MIN	MAX	
Α	2.40	3.00	
A1	1.00	1.50	
b	0.60	0.90	
b2	0.51	0.88	
C	0.39	0.63	
D	10.60	11.10	
Е	7.40	7.80	
е	2.04	2.54	
L	14.50	16.63	
L1	1.27	2.54	
Ρ	2.90	3.30	
Q	3.80	4.20	
STYLE 1: PIN 1. EMITTER 2., 4. COLLECTOR 3. BASE			

Thermopad is a trademark of Semiconductor Components Industries, LLC (SCILLC).

ON Semiconductor and 🕕 are registered trademarks of Semiconductor Components Industries, LLC (SCILLC). SCILLC owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of SCILLC's product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent–Marking.pdf. SCILLC reserves the right to make changes without further notice to any products herein. SCILLC makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does SCILLC assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without the particular purpose. imitation special, consequential or incidental damages. "Typical" parameters which may be provided in SCILLC data sheets and/or specifications can and ovary in different applications and actual performance may vary over time. All operating parameters, including "Typical" must be validated for each customer application by customer's technical experts. SCILLC does not convey any license under its patent rights nor the rights of others. SCILLC products are not designed, intended, or authorized for use as components in systems intended for surgical implant into the body, or other applications intended to support or sustain life, or for any other application in which the failure of the SCILLC product could create a situation where personal injury or death may occur. Should Buyer purchase or use SCILLC products for any such unintended or unauthorized application, Buyer shall indemnify and hold SCILLC and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that SCILLC was negligent regarding the design or manufacture of the part. SCILLC is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

#### PUBLICATION ORDERING INFORMATION

#### LITERATURE FULFILLMENT:

Literature Distribution Center for ON Semiconductor P.O. Box 5163, Denver, Colorado 80217 USA Phone: 303–675–2175 or 800–344–3860 Toll Free USA/Canada Fax: 303–675–2176 or 800–344–3867 Toll Free USA/Canada Email: orderlit@onsemi.com

N. American Technical Support: 800-282-9855 Toll Free USA/Canada Europe, Middle East and Africa Technical Support:

ON Semiconductor Website: www.onsemi.com

Order Literature: http://www.onsemi.com/orderlit

Phone: 421 33 790 2910 Japan Customer Focus Center Phone: 81-3-5817-1050

For additional information, please contact your local Sales Representative