## **Features**


- 1-channel
- DC version, positive polarity
- Working voltage 26.5 V at 10 μA
- Series resistance max. 327  $\Omega$
- · Fuse rating 50 mA
- · DIN rail mounting

## **Function**

The Zener Barrier prevents the transfer of unacceptably high energy from the safe area into the hazardous area.


The zener diodes in the Zener Barrier are connected in the reverse direction. The breakdown voltage of the diodes is not exceeded in normal operation. If this voltage is exceeded, due to a fault in the safe area, the diodes start to conduct, causing the fuse to blow. The Zener Barrier has a positive polarity, i. e. the anodes of the zener diodes are grounded.


## **Assembly**





## Connection





General specific	cations	
Туре		DC version, positive polarity
Electrical specif	fications	
Nominal resistance		300 Ω
Series resistance		max. 327 $\Omega$
Fuse rating		50 mA
Hazardous area	connection	
Connection		terminals 1, 2
Safe area connection		
Connection		terminals 7, 8
Rated voltage		28 V
Supply voltage		max. 28 V
Working voltage		26.5 V at 10 μA
Conformity		20.0 ν αι το μπ
Protection degree		IEC 60529
-		IEC 00029
Ambient conditions		20
Ambient temperature		-20 60 °C (253 333 K)
Storage temperature		-25 70 °C (248 343 K)
Relative humidity		max. 75 %, without moisture condensation
Mechanical spe		
Protection degree		IP54
Connection		self-opening connection terminals, max. core cross-section 2 x 2.5 mm <sup>2</sup>
Mass		approx. 150 g
Dimensions		12.5 x 115 x 110 mm (0.5 x 4.5 x 4.3 in)
Construction type		modular terminal housing , see system description
Mounting		mounting on 35 mm DIN rail acc. to DIN EN 60715
Data for applica with hazardous	tion in conjunction areas	
EC-Type Examination Certificate		BAS 01 ATEX 7005, for additional certificates see www.pepperl-fuchs.com
Group, category, type of protection		$\textcircled{k}$ II (1)GD [EEx ia] IIC (-20 °C $\leq$ T <sub>amb</sub> $\leq$ 60 °C)
Voltage	U <sub>o</sub>	28 V
Current	I <sub>o</sub>	93 mA
Power	P <sub>o</sub>	650 mW
Supply	U	
Safety maximu	ım voltage U	250 V
Series resistance		min. 301 $\Omega$
Statement of conformity		TÜV 99 ATEX 1484 X , observe statement of conformity
Group, category, type of protection, temperature classification		ⓑ II 3G EEx nA II T4 X
Directive conform		
Directive 94/9 EC		EN 50014, EN 50020, EN 50021
International approvals		333, 30020, 30021
FM approval		
Control drawing		116-0118
UL approval		110 0110
Control drawing		116-0139
· · · · · · · · · · · · · · · · · · ·		110-0100
CSA approval		116 0110
Control drawing		116-0119
General informa		FOT F 1 1 0 1 1 1 1 1 1 1 1 1 1 1 1 1 1 1 1
Supplementary in	ntormation	EC-Type Examination Certificate, Statement of Conformity, Declaration of Conformity and instructions have to be observed where applicable. For information see www.pepperl-fuchs.com.