TRIDONIC

I-SELECT 2 PLUG PRE / EXC

Resistors for current selection



Product description

- _ Ready-for-use resistor to set output current value
- _ Compatible with LED driver featuring I-select 2 interface; not compatible with I-SELECT (generation 1)
- _ Resistor is base insulated
- _ Resistor power 0.25 W
- _ Current tolerance ± 2 % additional to output current tolerance
- _ Compatible with LED driver series PRE and EXC

Example of calculation

- $R[k\Omega] = 5 V / I_out[mA] x 1000$
- _ E96 resistor value used
- _ Resistor value tolerance ≤ 1 %; resistor power ≥ 0.1 W; base insulation necessary
- _ When using a resistor value beyond the specified range, the output current will automatically be set to the minimum value (resistor value too big), respectively to the maximum value (resistor value too small)

Website

http://www.tridonic.com/28001135




Accessories

TRIDONIC

I-SELECT 2 PLUG PRE / EXC

Resistors for current selection



Ordering data

Туре	Article number	Colour	Marking	Current	Resistor value	Packaging, bag	Weight per pc.
I-SELECT 2 PLUG 1700MA BL	28001135	Blue	1700 mA	1,700 mA	2.94 kΩ	10 pc(s).	0.001 kg