HALOGEN

FREE



Vishay General Semiconductor

Surface Mount Schottky Barrier Rectifier



SMC (DO-214AB)

PRIMARY CHARACTERISTICS					
I _{F(AV)}	4.0 A				
V_{RRM}	20 V, 30 V, 40 V				
I _{FSM}	150 A				
V _F	0.31 V, 0.35 V				
T _J max.	125 °C				
Package	SMC (DO-214AB)				
Circuit configuration	Single				

FEATURES

- Low profile package
- · Ideal for automated placement
- · Guardring for overvoltage protection
- Low power losses, high efficiency
- Very low forward voltage drop
- High surge capability
- Meets MSL level 1, per J-STD-020, LF maximum peak of 260 °C
- AEC-Q101 qualified
 - Automotive ordering code: base P/NHE3 or P/NHM3
- Material categorization: for definitions of compliance please see <u>www.vishav.com/doc?99912</u>

TYPICAL APPLICATIONS

For use in low voltage high frequency inverters, freewheeling, DC/DC converters, and polarity protection applications.

MECHANICAL DATA

Case: SMC (DO-214AB)

Molding compound meets UL 94 V-0 flammability rating Base P/N-E3 - RoHS-compliant, commercial grade Base P/N-M3 - halogen-free, RoHS-compliant, commercial

grade

Base P/NHE3_X - RoHS-compliant and AEC-Q101 qualified Base P/NHM3_X - halogen-free, RoHS-compliant, and AEC-Q101 qualified

("_X" denotes revision code e.g. A, B,)

Terminals: matte tin plated leads, solderable per J-STD-002 and JESD 22-B102

E3, M3, HE3, and HM3 suffix meets JESD 201 class 2 whisker test

Polarity: color band denotes the cathode end

MAXIMUM RATINGS (T _A = 25 °C unless otherwise noted)					
PARAMETER	SYMBOL	SL42	SL43	SL44	UNIT
Device marking code		SL2	SL3	SL4	
Maximum repetitive peak reverse voltage	V _{RRM}	20	30	40	V
Maximum RMS voltage	V _{RMS}	14	21	28	V
Maximum DC blocking voltage	V _{DC}	20	30	40	V
Maximum average forward rectified current ⁽¹⁾ at T _L (fig. 1)	I=	4.0			A
	I _{F(AV)}				
Peak forward surge current 8.3 ms single half sine-wave superimposed on rated load	I _{FSM}	150			А
Operating junction temperature range	TJ	-55 to +125			°C
Storage temperature range	T _{STG}	-55 to +150			

Note

⁽¹⁾ PCB mounted 0.55" x 0.55" (14 mm x 14 mm) copper pad areas, $T_L = 90$ °C



Vishay General Semiconductor

ELECTRICAL CHARACTERISTICS (T _A = 25 °C unless otherwise noted)							
PARAMETER	TEST CONDITIONS		SYMBOL	SL42	SL43	SL44	UNIT
Maximum instantaneous forward voltage at ⁽¹⁾	I _F = 4.0 A	T _A = 125 °C T _A = 25 °C	V _F	0.31		0.35	V
		T _A = 25 °C		0.42		0.44	
	I _F = 8.0 A	T _A = 125 °C		0.	37	0.41	V
		T _A = 25 °C		0.	47	0.50	
Maximum DC reverse current at rated DC	T _A = 25 °C			0.5		mA	
blocking voltage (1)		T _A = 100 °C	IR	35			IIIA

Note

 $^{^{(1)}\,}$ Pulse test: 300 μs pulse width, 1 % duty cycle

THERMAL CHARACTERISTICS (T _A = 25 °C unless otherwise noted)						
PARAMETER	SYMBOL	SL42	SL43	SL44	UNIT	
Typical thermal resistance (1)	$R_{\theta JA}$	50		°C/W		
Typical thermal resistance (**			14		C/VV	

Note

 $^{^{(1)}\,}$ PCB mounted 0.55" x 0.55" (14 mm x 14 mm) copper pad areas, T_L = 90 °C

ORDERING INFORMATION (Example)							
PREFERRED P/N	UNIT WEIGHT (g)	PREFERRED PACKAGE CODE	BASE QUANTITY	DELIVERY MODE			
SL44-E3/57T	0.235	57T	850	7" diameter plastic tape and reel			
SL44-E3/9AT	0.235	9AT	3500	13" diameter plastic tape and reel			
SL44HE3_B/H (1)	0.235	Н	850	7" diameter plastic tape and reel			
SL44HE3_B/I (1)	0.235	I	3500	13" diameter plastic tape and reel			
SL44-M3/57T	0.235	57T	850	7" diameter plastic tape and reel			
SL44-M3/9AT	0.235	9AT	3500	13" diameter plastic tape and reel			
SL44HM3_A/H (1)	0.235	Н	850	7" diameter plastic tape and reel			
SL44HM3_A/I (1)	0.235	I	3500	13" diameter plastic tape and reel			

Note

RATINGS AND CHARACTERISTICS CURVES ($T_A = 25$ °C unless otherwise noted)




Fig. 1 - Forward Current Derating Curve




Fig. 2 - Maximum Non-Repetitive Peak Forward Surge Current

⁽¹⁾ AEC-Q101 qualified



Vishay General Semiconductor




Fig. 3 - Typical Instantaneous Forward Characteristics




Fig. 5 - Typical Junction Capacitance





Fig. 4 - Typical Reverse Characteristics

PACKAGE OUTLINE DIMENSIONS in inches (millimeters)

SMC (DO-214AB)



0.126 (3.20) MIN. -- 0.320 (8.13) REF. --



Legal Disclaimer Notice

Vishay

Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Vishay:

SL42/57T SL42/59T SL42/9AT SL42/9CT SL42/9T SL42-E3/57T SL42-E3/59T SL42-E3/57T SL42-E3/7T SL42-E3/7T SL42-E3/9AT SL42-E3/9CT SL42HE3/57T SL42HE3/59T SL42HE3/9AT SL42HE3/9CT SL43/57T SL43/59T SL43/57T SL43/59T SL43/7T SL43/9AT SL43/9T SL43-E3/57T SL43-E3/59T SL43-E3/59T SL43-E3/57T SL43HE3/57T SL43HE3/59T SL43HE3/9AT SL44/57T SL44/59T SL44/7T SL44/9AT SL44/9CT SL44/9T SL44-E3/57T SL44-E3/59T SL44-E3/9AT SL44-E3/57T SL44-E3/57T SL44-E3/57T SL44-E3/9AT SL44-E3/9CT SL44HE3/57T SL44HE3