## MMBD2837LT1G, MMBD2838LT1G, SMMBD2837LT1G

# Monolithic Dual Switching Diodes

### **Features**

- S Prefix for Automotive and Other Applications Requiring Unique Site and Control Change Requirements; AEC-Q101 Qualified and PPAP Capable
- These Devices are Pb–Free, Halogen Free/BFR Free and are RoHS Compliant

### **MAXIMUM RATINGS (EACH DIODE)**

Rating	Symbol	Value	Unit
Peak Reverse Voltage	$V_{RM}$	75	Vdc
D.C. Reverse Voltage MMBD2837LT1G, SMMBD2837LT1G MMBD2838LT1G	V <sub>R</sub>	30 50	Vdc
Peak Forward Current	I <sub>FM</sub>	450 300	mAdc
Average Rectified Current	I <sub>O</sub>	150 100	mAdc

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.

### THERMAL CHARACTERISTICS

Rating	Symbol	Value	Unit
Total Device Dissipation FR-5 Board (Note 1) T <sub>A</sub> = 25°C	P <sub>D</sub>	225	mW
Derate above 25°C		1.8	mW/°C
Thermal Resistance,	$R_{\theta JA}$		°C/W
Junction-to-Ambient		556	
Total Device Dissipation Alumina Substrate, (Note 2) T <sub>A</sub> = 25°C	P <sub>D</sub>	300	mW
Derate above 25°C		2.4	mW/°C
Thermal Resistance, Junction-to-Ambient	$R_{\theta JA}$	417	°C/W
Junction-to-Ambient		417	
Junction and Storage Temperature	T <sub>J</sub> , T <sub>stg</sub>	-55 to +150	°C

- 1. FR-5 =  $1.0 \times 0.75 \times 0.062$  in.
- 2. Alumina =  $0.4 \times 0.3 \times 0.024$  in. 99.5% alumina.




### ON Semiconductor®

### www.onsemi.com



SOT-23 (TO-236AB) CASE 318 STYLE 9



### **MARKING DIAGRAM**



M = Date Code\* = Pb-Free Package

(Note: Microdot may be in either location)
\*Date Code orientation and/or overbar may
vary depending upon manufacturing location.

### **ORDERING INFORMATION**

Device	Package	Shipping <sup>†</sup>	
Device	1 ackage	Omphing	
MMBD2837LT1G	SOT-23	3,000 /	
	(Pb-Free)	Tape & Reel	
SMMBD2837LT1G	SOT-23	3,000 /	
	(Pb-Free)	Tape & Reel	
MMBD2838LT1G	SOT-23	3,000 /	
	(Pb-Free)	Tape & Reel	


†For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specifications Brochure, BRD8011/D.

### MMBD2837LT1G, MMBD2838LT1G, SMMBD2837LT1G

ELECTRICAL CHARACTERISTICS (EACH DIODE) (T<sub>A</sub> = 25°C unless otherwise noted)

Characteristic	Symbol	Min	Max	Unit
OFF CHARACTERISTICS				
Reverse Breakdown Voltage (I <sub>(BR)</sub> = 100 μAdc)	V <sub>(BR)</sub>			Vdc
MMBD2837LT1G, SMMBD2837LT1G MMBD2838LT1G		35 75	-	
Reverse Voltage Leakage Current (Note 3.) (V <sub>B</sub> = 30 Vdc)	I <sub>R</sub>			μAdc
MMBD2837LT1G, SMMBD2837LT1G (V <sub>B</sub> = 50 Vdc)		-	0.1	
MMBD2838LT1G		_	0.1	
Diode Capacitance (V <sub>R</sub> = 0 V, f = 1.0 MHz)	C <sub>T</sub>	-	4.0	pF
Forward Voltage	V <sub>F</sub>			Vdc
$(I_F = 10 \text{ mAdc})$		_	1.0	
(I <sub>F</sub> = 50 mAdc)		_	1.0	
(I <sub>F</sub> = 100 mAdc)		_	1.2	
Reverse Recovery Time ( $I_F = I_R = 10 \text{ mAdc}$ , $I_{R(REC)} = 1.0 \text{ mAdc}$ ) (Figure 1)	t <sub>rr</sub>	_	4.0	ns

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions.



Notes: 1. A 2.0  $k\Omega$  variable resistor adjusted for a Forward Current (IF) of 10 mA.

Notes: 2. Input pulse is adjusted so  $I_{R(peak)}$  is equal to 10 mA.

Notes: 3. tp » trr

Figure 1. Recovery Time Equivalent Test Circuit

<sup>3.</sup> For each individual diode while the second diode is unbiased.

### MMBD2837LT1G, MMBD2838LT1G, SMMBD2837LT1G

### **CURVES APPLICABLE TO EACH CATHODE**




Figure 2. Forward Voltage




Figure 3. Leakage Current





Figure 4. Capacitance

### MMBD2837LT1G, MMBD2838LT1G, SMMBD2837LT1G

### PACKAGE DIMENSIONS

SOT-23 (TO-236) CASE 318-08 **ISSUE AR** 



#### NOTES


- 1. DIMENSIONING AND TOLERANCING PER ASME Y14.5M, 1994.
- CONTROLLING DIMENSION: MILLIMETERS.
  MAXIMUM LEAD THICKNESS INCLUDES LEAD FINISH. MINIMUM LEAD THICKNESS IS THE MINIMUM THICKNESS OF THE BASE MATERIAL.
- 4. DIMENSIONS D AND E DO NOT INCLUDE MOLD FLASH, PROTRUSIONS, OR GATE BURRS.

	MILLIMETERS			INCHES			
DIM	MIN	NOM	MAX	MIN	NOM	MAX	
Α	0.89	1.00	1.11	0.035	0.039	0.044	
A1	0.01	0.06	0.10	0.000	0.002	0.004	
b	0.37	0.44	0.50	0.015	0.017	0.020	
С	0.08	0.14	0.20	0.003	0.006	0.008	
D	2.80	2.90	3.04	0.110	0.114	0.120	
E	1.20	1.30	1.40	0.047	0.051	0.055	
е	1.78	1.90	2.04	0.070	0.075	0.080	
L	0.30	0.43	0.55	0.012	0.017	0.022	
L1	0.35	0.54	0.69	0.014	0.021	0.027	
HE	2.10	2.40	2.64	0.083	0.094	0.104	
Т	0°		10 °	0 °		10 °	

#### STYLE 9:

- PIN 1. ANODE
  - 2. ANODE
  - CATHODE

### RECOMMENDED SOLDERING FOOTPRINT\*



\*For additional information on our Pb-Free strategy and soldering details, please download the ON Semiconductor Soldering and Mounting Techniques Reference Manual, SOLDERRM/D.

ON Semiconductor and III) are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of ON Semiconductor's product/patent coverage may be accessed at <a href="www.onsemi.com/site/pdf/Patent-Marking.pdf">www.onsemi.com/site/pdf/Patent-Marking.pdf</a>. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages.

Buyer is responsible for its products and applications using ON Semiconductor products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by ON Semiconductor. "Typical" parameters which may be provided in ON Semiconductor data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. ON Semiconductor does not convey any license under its patent rights nor the rights of others. ON Semiconductor products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use ON Semiconductor products for any such unintended or unauthorized application, Buyer shall indemnify and hold ON Semiconductor and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that ON Semiconductor was negligent regarding the design or manufacture of the part. ON Semiconductor is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

### **PUBLICATION ORDERING INFORMATION**

### LITERATURE FULFILLMENT:

Literature Distribution Center for ON Semiconductor 19521 E. 32nd Pkwy, Aurora, Colorado 80011 USA Phone: 303-675-2175 or 800-344-3860 Toll Free USA/Canada Fax: 303-675-2176 or 800-344-3867 Toll Free USA/Canada Email: orderlit@onsemi.com

N. American Technical Support: 800-282-9855 Toll Free USA/Canada

Europe, Middle East and Africa Technical Support: Phone: 421 33 790 2910 Japan Customer Focus Center

ON Semiconductor Website: www.onsemi.com

Order Literature: http://www.onsemi.com/orderlit

For additional information, please contact your local Sales Representative

Phone: 81-3-5817-1050

# **Mouser Electronics**

**Authorized Distributor** 

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

**ON Semiconductor:** 

MMBD2837LT1G MMBD2838LT1G SMMBD2837LT1G