

## Han 70A axial module, male 6-16mm<sup>2</sup>



Image is for illustration purposes only. Please refer to product description.

Part number	09 14 002 2641
Specification	Han 70A axial module, male 6-16mm <sup>2</sup>
HARTING eCatalogue	<a href="https://b2b.harting.com/09140022641">https://b2b.harting.com/09140022641</a>

### Identification

Category	Modules
Series	Han-Modular <sup>®</sup>
Type of module	Han <sup>®</sup> 70 A module
Size of the module	Single module

### Version

Termination method	Axial screw termination
Gender	Male
Number of contacts	2
Details	Finger safe

### Technical characteristics

Conductor cross-section	6 ... 16 mm <sup>2</sup>
Rated current	70 A
Rated voltage	1,000 V
Rated impulse voltage	8 kV
Pollution degree	3
Insulation resistance	>10 <sup>10</sup> Ω
Contact resistance	≤0.5 mΩ
Stripping length	11 ... 12 mm
Tightening torque	2 Nm @ 6 mm <sup>2</sup> 3 Nm @ 10 mm <sup>2</sup> 4 Nm @ 14 mm <sup>2</sup> 4 Nm @ 16 mm <sup>2</sup>

Page 1 / 3 | Creation date 2024-02-10 | Please note that the data specified here were taken as extracts from the online catalogue. Please refer to the user documentation for the complete and up-to-date information and data. Please also note that the user is responsible for validating functionality, conformity with applicable laws and directives, as well as for the electrical safety in the particular application.

HARTING Electric Stiftung & Co. KG | Wilhelm-Harting-Straße 1 | 32339 Espelkamp | Germany  
Phone +49 5772 47-97100 | [electric@HARTING.com](mailto:electric@HARTING.com) | [www.HARTING.com](http://www.HARTING.com)



Pushing Performance  
Since 1945

## Technical characteristics

Limiting temperature	-40 ... +125 °C
Mating cycles	≥500

## Material properties

Material (insert)	Polycarbonate (PC)
Colour (insert)	RAL 7032 (pebble grey)
Material (contacts)	Copper alloy
Surface (contacts)	Silver plated
Material flammability class acc. to UL 94	V-0
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Potassium 1,1,2,2,3,3,4,4,4-nonafluorobutane-1-sulphonate Lead
ECHA SCIP number	1e38d35d-d1be-4585-8e03-95faccd739bf
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead Nickel
Fire protection on railway vehicles	EN 45545-2 (2020-08)
Requirement set with Hazard Levels	R22 (HL 1-3) R23 (HL 1-3)

## Specifications and approvals

Specifications	IEC 60664-1 IEC 61984
UL / CSA	UL 1977 ECBT2.E235076 UL 2237 PVVA2.E318390 CSA-C22.2 No. 182.3 PVVA8.E318390
Approvals	DNV GL

## Commercial data

Packaging size	2
----------------	---



**Pushing Performance**  
Since 1945

## Commercial data

Net weight	32.6 g
Country of origin	Germany
European customs tariff number	85389099
GTIN	5713140019638
ETIM	EC000438
eCl@ss	27440217 Module for industrial connectors (power/signals)