



## TLR Metal Plate Chip Type Low Resistance Resistors



Coating color : Black (2BN(1mΩ,1.5mΩ), 2B(1mΩ,1.5mΩ), 3AW(0.5m~1.5mΩ))

### Construction



### Features

- Ultra low resistances (0.5mΩ ~), suitable for large current sensing.
- Ultra low height with a thickness of 0.6mm, suitable for use of small equipment.
- Excellent high-frequency characteristics.
- Automatic mounting machines are applicable.
- Suitable for reflow soldering. (Not suitable for flow soldering)
- Products meet EU-RoHS requirements.
- AEC-Q200 Tested.

### Applications

- Current sensing for CPU
- Inverter power supplies
- DC-DC converters
- Mobile device etc.

### Reference Standards

IEC 60115-1  
JIS C 5201-1

### Dimensions

Type (Inch Size Code)	Resistance (Ω)	Dimensions (mm)			
		L	W	d	t
2B 2BN (1206)	1m, 1.5m	3.2±0.2	1.6±0.2	1.1±0.2	0.6±0.2
	2m, 3m, 4m, 5m, 6m, 7m, 8m, 9m, 10m, 11m, 12m, 13m, 15m, 16m, 18m, 20m			0.5±0.2	
2H (2010)	1m	5.0±0.2	2.5±0.2	1.8±0.2	0.65±0.2
	2m, 3m, 4m, 5m, 6m			1.5±0.2	
	7m, 8m, 9m, 10m			0.5±0.2	
3AW (2512)	0.5m	6.35±0.25	3.18±0.25	2.725±0.25	0.6±0.25
	0.68m, 0.75m, 0.82m			2.675±0.25	
	1m, 1.5m, 2m, 3m, 4m			2.20±0.25	
	5m, 6m, 7m, 8m			1.20±0.25	
	9m, 10m			0.77±0.25	

### Type Designation

Example

TLR	2B	D	TD	10L0	F	75
Product Code	Power Rating	Termination Surface Material	Taping	Nominal Resistance	Resistance Tolerance	T.C.R. (×10 <sup>-6</sup> /K)
	2BN: 0.5W 2B: 0.5W 2H: 1.0W 3AW: 2.0W	D: SnAgCu	TD: 4mm pitch punch paper TE: Plastic embossed BK: Bulk	F: 4 digits	F: ±1%	Nil: ±150 50: ±50 75: ±75

Resistance Value (Ω)	4 digits
0.5m~0.82m	L500~L820
1m~9m	1L00~9L00
10m~20m	10L0~20L0

Contact us when you have control request for environmental hazardous material other than the substance specified by EU-RoHS.

For further information on taping, please refer to APPENDIX C on the back pages.


### Ratings

Type	Power Rating	Rated Ambient Temp.	Rated Terminal Part Temp.	T.C.R. (×10 <sup>-6</sup> /K)	Resistance Range (Ω)	Resistance Tolerance	Operating Temp. Range	Taping & Q'ty/Reel (pcs)	
								TD	TE
TLR2B	0.5W	+70°C	+105°C	± 50	2m,3m,4m,5m,6m,7m,8m,9m,10m, 11m,12m,13m,15m,16m,18m,20m	F: ±1%	-65°C~+155°C	5,000	-
TLR2BN				± 75	1m,1.5m,2m,3m,4m,5m,6m,7m,8m,9m, 10m,11m,12m,13m,15m,16m,18m,20m				
TLR2H	1.0W			± 150	1m,1.5m,2m,3m,4m,5m,6m,7m,8m, 10m,11m,12m,13m,15m,16m,18m,20m				
				± 50	1m,2m,3m,4m,5m,6m,7m,8m,9m,10m				
				± 75					
TLR3AW	2.0W			± 150	2m,3m,4m,5m,6m,7m,8m,9m,10m				
		± 50	0.5m,0.68m,0.75m,0.82m,1m,1.5m, 2m*,3m,4m,5m,6m,7m,8m,9m,10m						
		± 75	0.5m,0.68m,0.75m,0.82m,1m,1.5m, 2m,3m,4m,5m,6m,7m,8m,9m,10m						
				± 150			-65°C~+155°C	-	2,000


\*1 Please ask separately us about dimensions of 2mΩ.

If any questions arise whether to use the "Rated Ambient Temperature" or the "Rated Terminal Part Temperature" in your usage conditions, please give priority to the "Rated Terminal Part Temperature". For more details, please refer to "Introduction of the derating curves based on the terminal part temperature" on the beginning of our catalog.

## Derating Curve



For resistors operated at an ambient temperature of 70°C or higher, the power shall be derated in accordance with the above derating curve.





When the terminal part temperature of the resistor exceeds the rated terminal part temperature shown above, the power shall be derated according to the derating curve.

※Please refer to "Introduction of the derating curves based on the terminal part temperature" on the beginning of our catalog before use.

## One-Pulse Limiting Electric Power

Please ask us about the resistance characteristic of continuous applied pulse.

The pulse endurance values are not assured values, so be sure to check the products on actual equipment when you use them.




## Thermal Resistance

Type	Size	Resistance (Ω)	Rth (°C/W)
TLR	2B 2BN	1m	11.8
		2m	18.3
		20m	116
	2H	1m	17
		10m	61.1
	3AW	0.5m	6
10m		62	

$$R_{th} = (H_s - t_s) / \text{Power}$$

Regarding the temperature rise, the value of the temperature varies per conditions and board for use since the temperature is measured under our measuring conditions. Please refer to us before use.

The temperature of the resistor will increase the same  $\Delta T$  from the standard terminal part temperature regardless of the ambient temperature when the same power is applied. This is because there is hardly any heat dissipation from the resistor surface to the ambient air.



## Performance

Test Items	Performance Requirements $\Delta R\%$		Test Methods
	Limit	Typical	
Resistance	Within specified tolerance	—	25°C
T.C.R.	Within specified T.C.R.	—	+25°C / +125°C
Resistance to soldering heat	0.5	0.3	260°C ± 5°C, 10s ± 0.5s
Rapid change of temperature	0.5	0.4	-55°C (15min.) / +150°C (15min.) 1000 cycles
Moisture resistance	0.5	0.1	MIL-STD-202, 106, 0% power, 7a and 7b not required
Biased humidity	0.5	0.1	85°C ± 2, 85%RH, 1000h, 10% Bias
Endurance at 70°C	1	0.3	70°C ± 2°C, 1000h, 1.5h ON/0.5h OFF cycle
High temperature exposure	1	0.6	+155°C (2B, 2B, 2H, 3AW), +170°C (3A), 1000h

## Precautions for Use

- In case of using the low ohm resistors as shunt resistors, please lay out a pattern considering the electromagnetic induction with surrounding inductors.
- In the resistance values of TLR the resistance value after soldering may change depending on the size of pad pattern or solder amount. Make sure the effect of decline/increase of resistance value before designing.