



Recommended P.C.B. Layout
Layout Tolerance = ± 0.05 mm

NOTE:

- MATERIAL:
HOUSING: HIGH TEMP PLASTIC, UL94-V0, BLACK
TERMINAL: COPPER ALLOY, T=0.15MM
CAP: STAINLESS STEEL, T=0.1MM
- FINISH:
TERMINAL: GOLD AT CONTACT,
G/F OVER 1um(40u") MIN Ni OVER ALL
- SPEC.:
PRODUCT SPEC: GS-12-629
PACKING SPEC: GS-14-1420
- THE HSG. WILL WITHSTAND EXPOSURE TO 260°C
PEAK TEMP. FOR 10 SEC. IN A CONVECTION INFRA-RED
OR VAPOR PHASE REFLOW OVEN.
- PRODUCT NUMBERING:
20021311 - 0 0 0 XX X X LF

LEAD FREE

PLATING:

1: GOLD FLASH ALL OVER

4: 0.25um(10U") GOLD AT CONTACT

8: 0.76um(30U") GOLD AT CONTACT

9: 1u" GOLD OVER 30u" PdNi AT CONTACT

PACKING

T: TUBE

PIN COUNT

06, 08, 10, ..., 98, A0

(EVERY EVEN PIN)

mat'l. code		surface ISO1302 ✓		tolerance ISO1101 ISO406		projection ④ ①		product family MINITEK	
l tr ecn nodr		date		tolerances unless otherwise specified		MM		title	
A	T09-1117	S.LIN	09/15/09	0.X±0.38		scale 8:1		1.27X1.27MM BTB RECEPTACLE VERTICAL TH	
B	T10-0018	S.LIN	01/20/10	0.XX±0.25				dwg no 20021311 sheet 1 of 1 size A4	
C	BX-N-010368	ZK	01/18/12	0'±2'	0.XXX±0.10			type Product Customer Drawing	
		dir		STERLING LIN 09/15/09		FCI		sheet 1 of 1 size A4	
		engr		STERLING LIN 09/15/09					
		chr		GRAY HSIEH 09/15/09					
		appd		JOSEPH 09/15/09					
sheet index	revision	sheet 1							