

# **RS PRO Photoelectric Sensor**

RS Stock No.: 2043984, 2043985, 2043987, 2043988, 2043989

## **FEATURES**

- Retro reflection working principle;
- Excellent anti-interference performance;
- High detection accuracy.



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.



### Part Number Description

Part number	Sensing distance	Light source	Output	Connection
2043984	3m (non adjustable)	Infrared LED (880nm)	NPN NO+NC	2m PVC cable
2043985	3m (non adjustable)	Infrared LED (880nm)	PNP NO+NC	2m PVC cable
2043987	3m (non adjustable)	Infrared LED (880nm)	PNP NO+NC	M12 connector
2043989	3m (non adjustable)	Infrared LED (880nm)	NPN NO+NC	M12 connector
2043988	3m (non adjustable)	Infrared LED (880nm)	PNP NO	M12 connector

#### **General Specifications**

Detection Type	Retro reflection sensor
Rated distance	3m non adjustable
Standard target	TD-09 reflector
Detected target	Opaque object
Repeat accuracy [R]	≦5%
Response Time	≤8.2ms
Output Indicator	Yellow LED
Ambient temperature	-15ºC55 ºC
Ambient humidity	3585 %RH (non-condensing)

#### **Electrical Specifications**

Operating Supply Voltage	1030 VDC
Current Consumption	≤25mA
Residual voltage	≤2.5V
Load Current	≤200mA
Hysteresis	
<b>Reverse Polarity Protection</b>	YES
Overload Protection	YES
Short Circuit Protection	YES
Voltage withstand	1000V/AC 50/60Hz 60s
Insulation resistance	≥50MΩ(500VDC)
Vibration resistance	1050Hz (0.5mm)

## **Photoelectric Sensors**




**Mechanical Specifications** 


Body Style	Barrel
Mounting Type	Screw Nut
Housing Material	PBT
Dimensions	M18*68mm (connector type) / M18*53.5mm (cable type)
Weight	65g (connector type) / 170g (cable type)


Protection Category		
IP Rating	IP67	

Additional Information				
Custom Tariff Number/HS code	903180			
Approvals				
Compliance/Certifications	CE			


#### **Dimension and Wiring**









Cable type







Connection type