## NOTES:

I. MATERIALS AND FINISHES:

FERRULE - BRASS, GOLD PLATING BODY - BRASS, GOLD PLATING CONTACT - BeCu, GOLD PLATING

INSULATOR - PTFE, NATURAL

2. ELECTRICAL:

A. IMPEDANCE: 50 OHM B. FREQUENCY RANGE: 0-12.4 GHz C. D.W.V: 1000 VRMS, MIN.


3. MECHANICAL:

A. DURABILITY: 500 CYCLES MIN. B. TEMPERATURE RANGE: -65°C TO +165°C


4. CRIMPED FERRULE HEX CRIMP SIZE .255"


5. CONTACT PIN TO SOLDER


6> SHOWS CABLE ENTRY DIMENSIONS.




RECOMMENDED CABLE STRIPPING DIM'S









## **CUSTOMER OUTLINE DRAWING**

ALL OTHER SHEETS ARE FOR INTERNAL USE ONLY

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN METRIC AND TOLERANCES ARE:
<pre></pre>
$\pm$ 0.05mm $\pm$ 0.1mm $\pm$ 0.2mm $\pm$ 0.3mm $\pm$ 1°
NOTICE - These drawings, specifications, or other data (I) are, and remain the
property of Amphenol corp.' (2) must be returned upon request; and (3) are
confidential and not to be disclosed to any person other than those to whom they
are given by Amphenol Corp. the furnishing of these drawings, specifications, or
other data by Amphenol Corp., or to any other person to anyone for any purpose is not to be regarded by implication or otherwise in any manner licensing, granting
rights to permitting such holder or any other person to manufacture, use or sell any
product, process or design, patented or otherwise, that may in any way be related to
or disclosed by said drawings, specifications, or other data.

	MATERIAL	DRAWN M.ZHANG	DATE 18-0ct-16	TITLE SMA ( (FOR	
CON	-	ENGINEER MARK.C	DATE 06 - Jul - 99		
	REFERENCE AND CONFIGURATION LEVEL:	APPROVED S.HSIEH	DATE 18-0c+-16	SCALE: 6.	
		CAD FILE		DV	

IIILE			
SMA	CRIMP	JACK	
_	RG-8/		?240)

SCALE:	6.0:1.0	SHEET	2	OF 2	
DWG SIZE				REV	
				$\cap$	

Amphenol	RF
----------	----

www.amphenolrf.com

DRAWI	NG NO.	SMA6111A5-3GT50G-8X-50
ITEM	NO.	6       AAH89GA5F
PART	NO.	132240

## **Mouser Electronics**

**Authorized Distributor** 

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

 $\frac{\text{Amphenol}}{\frac{132240}{}}$