

# Varnished Chokes

## Special Features

- High Q, high self-resonant frequency
- High voltage application on phenolic components
- Low cost
- Varnish coated
- Operating temperature:  
-55 to +125 °C

## Notes

\* Current to cause 35 °C max. temperature rise

4600 Series									
Part Number	L (μH) ±20 %	Q Min.	Test Freq. (MHz)	SRF (MHz) Min.	DCR Ω Max.	I, DC* (mA)	Coil Diam. Max.	Core Matl.	Fig.
4602-RC	1.0	60	7.96	190	0.05	2000	0.27	Phenolic	A
	±10 %								
4604-RC	1.5	58	7.96	149	0.093	1800	0.27	Phenolic	A
4606-RC	2.4	56	7.96	120	0.19	1500	0.27	Phenolic	A
4608-RC	3.9	60	7.96	93	0.45	1000	0.27	Phenolic	A
4609-RC	5.5	57	7.96	80	0.67	850	0.27	Phenolic	A
4610-RC	6.2	57	7.96	76	0.83	700	0.27	Phenolic	A
4611-RC	8.2	57	7.96	65	1.2	600	0.27	Phenolic	A
4612-RC	10	36	2.52	61	1.5	500	0.27	Phenolic	A

"-RC" suffix indicates RoHS compliance.

† RoHS Directive 2002/95/EC Jan 27 2003 including Annex.




Fig. A

Dimensions: Inches

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

## Bourns:

[4602](#) [4604](#) [4606](#) [4608](#) [4609](#) [4610](#) [4611](#) [4612](#) [4622](#) [4624](#) [4626](#) [4628](#) [4629](#) [4630](#) [4631](#) [4632](#) [4642](#) [4644](#)  
[4646](#) [4648](#) [4649](#) [4650](#) [4651](#) [4652](#) [4662](#) [4664](#) [4666](#) [4668](#) [4669](#) [4670](#) [4671](#) [4672](#) [4609-RC](#) [4602-RC](#) [4649-RC](#)  
[4671-RC](#) [4672-RC](#) [4662-RC](#) [4644-RC](#) [4626-RC](#) [4630-RC](#) [4646-RC](#) [4608-RC](#) [4650-RC](#) [4632-RC](#) [4651-RC](#)  
[4631-RC](#) [4664-RC](#) [4612-RC](#) [4631-E](#) [4610-RC](#) [4668-RC](#) [4622-RC](#) [4669-RC](#) [4611-RC](#) [4652-RC](#) [4624-RC](#) [4642-RC](#)  
[4629-RC](#) [4670-RC](#) [4648-RC](#) [4666-RC](#) [4628-RC](#) [4606-RC](#) [4604-RC](#)