



		Conditions	
<b>cell type:</b>		NiMH	
<b>cell size:</b>		D	
<b>nominal voltage:</b>	1.2	V	
<b>max. charge voltage:</b>	1.5	V	at standard charge (0.1C / 20°C)
<b>capacity</b>			
nominal:	8500	mAh	discharge at 0.2C
minimum:	8500	mAh	discharge at 0.2C
	8000	mAh	discharge at 1C
			1.0V end discharge voltage
			ta: 20°C
<b>max. continuous discharge current:</b>	8500	mA	ta: 0...45°C
<b>charge</b>			
standard charge:	850	mA	14....16hrs
quick charge:	2550	mA	4hrs
fast charge:	4250	mA	2.3hrs
recommended charge termination control parameters:	0...5	mV	- ΔV (-deltaV)
	0.8...1	°C	temperature rise per minute
	45...50	°C	TCO (temperature cut off)
trickle charge current:	50...250	mA	(recommended)
continuous overcharge: (less than 1 year)	≤ 850	mA	no conspicuous deformation no leakage
<b>internal resistance:</b> (impedance)	≤ 12	mΩ	at 1KHz battery fully charged
<b>life expectancy:</b>	≥ 500	cycles	acc. IEC standard
<b>self discharge</b>			
charge retention:	≥ 80	%	after 12 months storage at 20°C
<b>initial capacity:</b>	≥ 5500	mAh	within 30 days after delivery discharge at 0.2C
<b>ambient temperature range:</b>	0...45	°C	standard charge
	10...40	°C	fast charge
	0...45	°C	discharge (≥1C)
	- 20...65	°C	discharge (<1C)
	- 20...50	°C	storage (≤3months)
	- 20...40	°C	storage (≤6months)
	- 20...30	°C	storage (≤24months)
QCT1:	20/8000/15		
QCT2:	30/7800/15		



<b>mechanical specifications</b>			
cell dimensions			
diameter d1:	32.8 - 1.0	mm	
diameter d2:	max. 9.5	mm	
height h1:	61.5 - 2.0	mm	
height h2:	min. 1.5	mm	
weight:	145 ± 7	g	
blister card dimensions:	123 x 85	mm	
blister card weight (incl. batteries):	300	g	



	<b>ANSMANN Specifications for model:</b>	<b>D - 8500mAh low self discharge 2pcs blister package</b>
	data sheet no. / part no.	5035362
	supplier no.	701364
	author / date	TG / 20.07.2016