



preci-dip

PCB CONNECTORS


SERIES
892

892-PP-NNN-10-XXX101

Double row

2.54 mm, Straight solder tail, Square pin diam. 0.635 mm

Square pin headers, solder tail



TECHNICAL SPECS.:

| | |
|----------------------------|---|
| Insulator | Black glass filled polyester PA-GF30-FR |
| Flammability | UL 94V-O |
| Contact | Brass |
| Connecting pin | Square 0.635 mm |
| Mechanical life | Min. 100 cycles |
| Rated current | 3 A |
| Dielectric strength | Min. 1000 V RMS |

ORDERING INFORMATION:

| PP Plating code | Termination | Connecting pin |
|-----------------|-------------|-------------------|
| 70 | Gold flash | Gold flash |
| 80 | Tin | Tin |
| 18 | Tin | Gold 0.25 μ m |

NNN number of poles. Replace NNN with the requested number of poles, e.g. 890-70-NNN-10-001101 for a single row version with 8 pins becomes 890-70-008-10-001101.

TECHNICAL ASSISTANCE

GENERAL SPECIFICATIONS:

The values listed below are general specs applying for PRECI-DIP socket and pin connectors. Please see individual catalog page for additional and product specific technical data.

| | |
|-----------------------------|---------------------------------|
| Operating temperature range | -55 ... +125 °C |
| Climatic category (IEC) | 55/125/21 |
| Operating humidity range | annual mean 75 % |
| Max working voltage | 100 VRMS/150 VDC (2.54 mm grid) |

PRECI-DIP sockets are recognized by Underwriters Laboratories Inc. and listed under "Connectors for Use in Data, Signal, Control and Power Applications", File Nr. E174442

MECHANICAL CHARACTERISTICS:

| | |
|-----------------------------------|---|
| Clip retention | Min. 40 N (no displacement under axial force applied) |
| Contact (sleeve / clip) retention | Min. 3.3 N acc. to MIL-DTL-83734, pt 4.6.4.2 |

ELECTRICAL CHARACTERISTICS:

| | |
|---|---------------------------|
| Insulation resistance between any two adjacent contacts | Min. 10'000 M at 500 V AC |
| Capacitance between any two adjacent contacts | Max. 1 pF |

Air and creepage distances between any two adjacent contacts :

| SERIES | 3xx/4xx/7xx | 80x | 83x | 85x | 86x |
|--------|-------------|------------|-----|-----------|-----|
| mm | 0.7 | 0.85 / 0.7 | 0.5 | 0.4 / 0.5 | 0.5 |

ENVIRONMENTAL CHARACTERISTICS:

The sockets withstand the following environmental tests without mechanical and electrical defects:

- Dry heat steady state IEC 60512-11-9.11i / 60068-2-2.Bb: 125 °C, 16h
- Damp heat cyclic IEC 60512-11-12.11m / 60068-2-30.Db: 25/55 °C, 90 – 100 %rH, 1 cycle of 24 h
- Cold steady state IEC 60512-11-10.11j / 60068-2-1.A: -55 °C, 2 h
- Thermal shock IEC 60512-11-4.11d / 60068-2-14.Na: -55/125 °C, 5 cycles 30 min
- Sinusoidal vibrations IEC 60512-6-4.6d / 60068-2-6.Fc: 10 to 500 Hz, 10 g, 1 octave/min, 10 cycles for each axis
- Shock IEC 60512-6-3.6c / 60068-2-27.Ea: 50 g, 11 ms, 3 shocks in three axis

During the above two tests no contact interruption >50 ns does appear.

- Solderability J-STD-002A, Test A, 245°C, 5 s solder alloy SnAg3.8Cu0.7
- Resistance to soldering heat J-STD-0020C, 260°C, 20 s
- Moisture sensitivity J-STD-020C level 1
- Resistance to corrosion :
 - 1) Salt spray test IEC 60068-2-11.Ka: 48 h
 - 2) Sulfur dioxide (SO₂) test IEC 60068-2-42 Kc: 96 h at 25 ppm SO₂, 25 °C, 75 %rH
 - 3) Hydrogen sulfide (H₂S) test IEC 60068-2-43 Kd: 96 h at 12 ppm H₂S, 25 °C, 75 %rH

SOLDERLESS COMPLIANT PRESS-FIT CHARACTERISTICS:

PRESS-FIT CHARACTERISTICS MEASURED ACC. TO IEC 60352-5

- Press-in force: 90 N max. (at min. hole dia.) / 65 N typ.
- Push-out force: 30 N min. (at max. hole dia.) / 50 N typ.
- Push-out 3rd cycle: 20 N min. (at max. hole dia.)

PCB HOLE DIMENSIONS

- 2 mm grid: Finished hole \varnothing : $0.7 + 0.09/-0.06$ mm | Drilled hole \varnothing : 0.8 ± 0.02 mm
- 2.54 mm grid: Finished hole \varnothing : $1 + 0.09/-0.06$ mm | Drilled hole \varnothing : 1.15 ± 0.02 mm

PCB HOLE PLATING

- PCB surface finish: Hole plating
- Tin: 5-15 μm tin over min. 25 μm copper
- Copper: min. 25 μm copper
- Gold over nickel: 0.05-0.2 μm gold over 2.5-5 μm nickel over min. 25 μm copper

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Preci-dip:

[892-18-072-10-001101](#) [892-18-072-10-004101](#) [892-18-030-10-001101](#) [892-18-052-10-001101](#) [892-18-050-10-001101](#) [892-18-048-10-001101](#) [892-70-062-10-003101](#) [892-70-064-10-003101](#) [892-70-066-10-003101](#) [892-70-024-10-003101](#) [892-70-044-10-003101](#) [892-70-050-10-003101](#) [892-70-052-10-003101](#) [892-70-054-10-003101](#) [892-70-056-10-003101](#) [892-70-058-10-003101](#) [892-70-060-10-003101](#) [892-70-038-10-003101](#) [892-70-040-10-003101](#) [892-70-042-10-003101](#) [892-70-072-10-003101](#) [892-70-046-10-003101](#) [892-70-070-10-003101](#) [892-70-068-10-004101](#) [892-70-028-10-003101](#) [892-70-030-10-003101](#) [892-70-032-10-003101](#) [892-70-034-10-003101](#) [892-70-036-10-003101](#) [892-80-030-10-003101](#) [892-80-032-10-003101](#) [892-80-034-10-003101](#) [892-80-036-10-003101](#) [892-80-014-10-003101](#) [892-70-048-10-003101](#) [892-70-068-10-003101](#) [892-80-020-10-003101](#) [892-80-022-10-003101](#) [892-80-024-10-003101](#) [892-80-026-10-003101](#) [892-80-028-10-003101](#) [892-80-006-10-003101](#) [892-80-008-10-003101](#) [892-80-010-10-003101](#) [892-80-012-10-003101](#) [892-70-022-10-003101](#) [892-80-016-10-003101](#) [892-80-018-10-003101](#) [892-70-074-10-003101](#) [892-70-076-10-003101](#) [892-70-078-10-003101](#) [892-70-080-10-003101](#) [892-80-004-10-003101](#) [892-18-044-10-003101](#) [892-18-046-10-003101](#) [892-18-048-10-003101](#) [892-18-050-10-003101](#) [892-18-052-10-003101](#) [892-18-030-10-003101](#) [892-18-032-10-003101](#) [892-70-026-10-003101](#) [892-18-036-10-003101](#) [892-18-038-10-003101](#) [892-18-040-10-003101](#) [892-18-042-10-003101](#) [892-18-020-10-003101](#) [892-18-022-10-003101](#) [892-18-024-10-003101](#) [892-18-026-10-003101](#) [892-18-028-10-003101](#) [892-18-058-10-003101](#) [892-18-076-10-003101](#) [892-18-034-10-003101](#) [892-18-012-10-003101](#) [892-18-014-10-003101](#) [892-18-018-10-003101](#) [892-70-010-10-003101](#) [892-70-012-10-003101](#) [892-70-014-10-003101](#) [892-70-016-10-003101](#) [892-70-018-10-003101](#) [892-70-020-10-003101](#) [892-18-056-10-003101](#) [892-18-078-10-003101](#) [892-18-054-10-003101](#) [892-70-004-10-003101](#) [892-70-006-10-003101](#) [892-70-008-10-003101](#) [892-18-064-10-003101](#) [892-18-066-10-003101](#) [892-18-068-10-003101](#) [892-18-070-10-003101](#) [892-18-072-10-003101](#) [892-18-074-10-003101](#) [892-18-054-10-004101](#) [892-18-074-10-004101](#) [892-18-080-10-003101](#) [892-80-042-10-003101](#) [892-18-060-10-003101](#) [892-18-062-10-003101](#)